



Ref. Certif. No.

FR_723813

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlet for fixed-electrical installations
Socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001,
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

13A 250V~
See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25120017

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/02/2026

Signature:



ANNEX

Name and address of the factories:**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001,
Guangdong - CHINA

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK - 422113, MAHARASHTRA - INDIA



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 25/02/2026

Signature: 

Certification Officer

ANNEX

RATING AND MAIN CHARACTERISTICS

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, -IN ... In this case, the products are technically the same.

Reference	Product description	Color of enclosure
MEC31033WH	2G BS 13A UNSWITCHED SOCKET	White
MEC31033SL	2G BS 13A UNSWITCHED SOCKET	Silver
MEC31033CH	2G BS 13A UNSWITCHED SOCKET	Champagne
MEC31033BL	2G BS 13A UNSWITCHED SOCKET	Black
MEC31033RG	2G BS 13A UNSWITCHED SOCKET	Rose Gold

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated load (W)	-
rated voltage (V)	250V
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
colour	See table above
socket-outlets	
multiple socket-outlets	13A : 2
number of socket-outlets	
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
plugs:	
class of equipment	-
entry of cable	-



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/02/2026

Signature

