

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Switched socket outlet, flush type

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.  
Bldg. B1-B3, East No.39 Hechang 6th Rd.,  
HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong  
CHINA

Name and address of the manufacturer

LEGRAND FRANCE  
128, Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
FRANCE

Name and address of the factory

See page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

13A 250V~ 50/60Hz, IP20, Class I

Trademark (if any)

 , tenby

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

617\*58A, 28\*\*34A, 832\*78A, 833\*78A, 282441A\*\*\*,  
K8/15/13/UA\*\*\*-HK, 57\*\*\*\*A, 281134A\*\*, 730078A, 738141A,  
618058, 838141

Additional information (if necessary may also be reported on page 2)

See page 2-4

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2  
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

210801260SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB  
Torshamnsgatan 43  
Box 1103  
SE-164 22 Kista, Sweden

Signature:

Hyden Li



Date: 13 July, 2022

**Factories**

Legrand Electric Ltd  
 Unit 12 No.1 Industrial Estate Medomsley Road, DH8 6SR Consett County Durham  
 UNITED KINGDOM

Legrand Intelligent Electrical (Huizhou) Co., Ltd.  
 Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong  
 CHINA




**Additional information**



for all types except 838141, 738141A  
 tenby for type 838141, 738141A

Standard sheet: type G (Configuration of BS 1363-2)  
 National differences: BS 1363-2:2016+A1:2018







13A 250V~ 50/60Hz, flush type, IP20, Class I, rewirable, with one way Type G outlets (configuration of BS 1363-2), with shutters, with single pole switch, with USB charger which evaluated according to IEC 62368-1: 2018 which in conjunction with IEC 62368-3:2017 with report no 210801261SHA-001/002, with metal cover, or with plastic cover plate or plastic lining combined with metal sheet cover plate, or without cover, with or without metal frame, with design A or design B construction, see below for details:

617*58A	617658A	design A construction, with plastic cover with angle chamfer, with front cover with embossing pattern, with trademark 	White colour
	617758A		Anthracite colour
	617858A		Ivory colour
28**34A	281134A	design A construction, plastic cover, with trademark 	White colour
	282134A		Matt black colour
	283134A		Silver colour
	283334A		Pearl colour
	283534A		Dark silver colour
	283934A		Champagne colour
832*78A	832078A	design A construction, metal cover, with trademark 	Flat BSS color
	832278A		Flat PSS color
	832478A		Flat gold color

Date: 13 July, 2022

Signature:



833*78A	833078A	design B construction, metal cover, with trademark 	Trad BSS color
	833278A		Trad PSS color
	833478A		Trad Gold color
282441A***	282441A	design A construction, plastic cover, with trademark 	White colour
	282441A-C		Matt black colour
	282441A-C1		Rose gold colour
	282441A-C2		Champagne colour
	282441A-C3		Dark silver colour
K8/15/13/UA***-HK	K8/15/13/UA-HK	design A construction, plastic cover, with trademark 	White colour
	K8/15/13/UA-C-HK		Matt black colour
	K8/15/13/UA-C1-HK		Rose gold colour
	K8/15/13/UA-C2-HK		Champagne colour
	K8/15/13/UA-C3-HK		Dark silver colour
	K8/15/13/UA-C4-HK		Pink colour
57****A	572156A	design A construction, without cover, with trademark 	White colour
	572656A		Magnesium colour
	570080A		Soft ALU colour
	571080A		Champagne colour
281134A**	281134AMW	design A construction, plastic cover, metal frame, with trademark 	Matt White
	281134AMG		Matt Grey
	281134AMB		Matt Black
	281134ADS		Dark Sliver
	281134ACH		Champagne
	281134ADB		Dark Bronze
	281134ABA	design A construction, plastic lining combined with metal sheet cover plate, metal frame, with trademark 	BRUSHED ALUMINIUM
	281134ABB		BRUSHED BLACK

Date: 13 July, 2022

Signature:



Note:

730078A: design B construction, white colour, with trademark

738141A: same as 730078A except with different enclosure shape and trademark "tenby".

For 282441A\*\*\* series and K8/15/13/UA\*\*\*-HK series, they with total same construction, only different type designation according to client's request.

For 57\*\*\*A series, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.

618058: with plastic cover, white colour, with trademark



838141: same as 618058 except with different enclosure shape, with trademark "tenby".

Date: 13 July, 2022

Signature:

A handwritten signature in blue ink, appearing to be 'M. J. ...'.