

# Test Verification of Conformity

Verification Number: 2401B1480SHA-V2

On the basis of the tests undertaken, the sample(s) of the below product have been found to comply with the requirements of the referenced specification(s)/standard(s) at the time the tests were carried out. This verification is part of the full test report(s) and should be read in conjunction with it <them>.

Applicant Name & Address:	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, P. R. China
Product Description:	Fixed socket-outlet (flush-type)
Ratings & Principle Characteristics:	13A 250V~, flush type, IP20, Class I, rewirable, with screw-type terminals, with 2 gang socket outlets comply with BS 1363-2, with shutters, with plastic or metal cover plate, with or without metal frame., refer to appendix for details.
Models/Type References:	6 170 45, 6 172 45, 6 173 45, 6 174 45, 6 176 45, 6 177 45, 6 178 45, 281112MW, 281112MG, 281112MB, 281112DS, 281112CH, 281112DB, 281112BA, 281112BB, 6 180 45, 8 380 27, MEC31033WH, MEC31033SL, MEC31033CH, MEC31033BL, MEC31033RG (totally 22 models)
Brand Names:	 or  for 8 380 27,  for other models
Specification(s)/Standards:	BS 1363-2:2023
Verification Issuing Office Name & Address:	Intertek Testing Services Shanghai Building No.86, 1198 Qinzhou Road (North), Shanghai 200233, China
Date of Tests:	Jan.25, 2024 to Apr.16, 2024
Test Report Number(s):	2401B1480SHA-002

  
Signature

**Name:** Oliver Wei  
**Position:** Manager  
**Date:** 13 June 2024

This Verification is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Verification. Only the Client is authorized to permit copying or distribution of this Verification. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test/inspection results referenced in this Verification are relevant only to the sample tested/inspected. This Verification by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.

## APPENDIX: Test Verification of Conformity

This is an Appendix to Test Verification of Conformity Number: 2401B1480SHA-V2

Total 22 models:

Mounting plate (style 1) with removable cover plate for model 6 170 45, 6 172 45, 6 173 45 and 6 174 45;

Mounting plate (style 2) with removable cover plate for model 6 176 45, 6 177 45 and 6 178 45;

6 170 45, 6 176 45: with white plastic front cover and white plastic cover plate, without metal frame;

6 173 45: with dark plastic front cover and dark plastic cover plate, without metal frame;

6 174 45: with brown plastic front cover and brown plastic cover plate, without metal frame;

6 177 45: with anthracite plastic front cover and anthracite plastic cover plate, without metal frame;

6 172 45, 6 178 45: with ivory plastic front cover and ivory plastic cover plate, without metal frame;

281112MW: with dark plastic front cover and matt white plastic cover plate, with metal frame;

281112MG: with dark plastic front cover and matt grey plastic cover plate, with metal frame;

281112MB: with dark plastic front cover and matt black plastic cover plate, with metal frame;

281112DS: with dark plastic front cover and dark silver plastic cover plate, with metal frame;

281112CH: with dark plastic front cover and champagne plastic cover plate, with metal frame;

281112DB: with dark plastic front cover and dark bronze plastic cover plate, with metal frame;

281112BA: with dark plastic front cover and plastic lining & brushed aluminium metal sheet cover plate, with metal frame;

281112BB: with dark plastic front cover and plastic lining & brushed black metal sheet cover plate, with metal frame.

6 180 45: "White" plastic front cover and cover plate, without metal frame.

8 380 27: "White" plastic front cover and cover plate, without metal frame.

Note: 6 180 45 and 8 380 27 are similar to 6 176 45 except the shape of cover plate.

MEC31033WH: with white plastic front cover and white plastic cover plate, without metal frame.

MEC31033SL: with white plastic front cover and silver plastic cover plate, without metal frame.

MEC31033CH: with white plastic front cover and champagne plastic cover plate, without metal frame.

MEC31033BL: with white plastic front cover and black plastic cover plate, without metal frame.

MEC31033RG: with white plastic front cover and rose gold plastic cover plate, without metal frame.



Signature

Name: Oliver Wei

Position: Manager

Date: 13 June 2024

This Verification is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Verification. Only the Client is authorized to permit copying or distribution of this Verification. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test/inspection results referenced in this Verification are relevant only to the sample tested/inspected. This Verification by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.