

IEC**IECEE**

®

TM

Ref. Certif. No.

FR_719321/M1**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME****CB TEST CERTIFICATE**

Product

Switches for fixed electrical installations combined with switched socket-outlet

Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, 516001 Huizhou
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

 Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

- 1)  (for all models exclude 838052, 838055)
- 2) tenby (for model 838052, 838055)

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719321 dated 21/06/2024.
Addition of product references Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25030320

This CB Test Certificate is issued by the National Certification Body

**LCIE**

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCEwww.lcie.fr

Date: 09/05/2025

Signature: 
Julien CAUTHIER
Certification Officer

ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

 Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, 516001
 Guangdong - CHINA

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK 422113 MAHARASHTRA - INDIA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - United Arab Emirates

References, ratings and main characteristics:

Reference	Description	Insert type	
618054	1 GANG BS 5A SINGLE POLE SWITCHED SOCKET	Totally the same except the shape of enclosure 5A 250V~	
MEC32044WH			
MEC32044SL			
MEC32044CH			
MEC32044BL			
MEC32044RG			
AA3204MW			
AA3204MT			
AA3204MB			
AA3204CH			
AA3204DB			
AA3204RS	AG13283		
838052		1 GANG BS 5A SINGLE POLE SWITCHED SOCKET	
618051		1 GANG BS 15A SINGLE POLE SWITCHED SOCKET	Totally the same except the shape of enclosure 15A 250V~
618053		2 GANG BS 15A SINGLE POLE SWITCHED SOCKET	
618052		1 GANG BS 15A SINGLE POLE SWITCHED SOCKET + NEON	
MEC32042WH		1 GANG BS 15A SINGLE POLE SWITCHED SOCKET	
MEC32042SL			
MEC32042CH			
MEC32042BL			
MEC32042RG			
838055		1 GANG BS 15A SINGLE POLE SWITCHED SOCKET	

Additional information for factories and accessories for AA3204 series:**

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature:



LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A.S au capital de 15.745.984 €
 RCS Nanterre B 494 521 400
 33 AVENUE DU GENERAL LECLERC
 92260 FONTENAY-AUX-ROSES
 Certification Officer

ANNEX

References

	Matt White	Matt Titanium	Matt Black	Champa gne	Dark Bronze	Rose				
Type referenc e	Commer cial ref	Rat ed val ues	Swi tch	Actua ting	Mod ule					
T003591	AA3204 MW	AA3204 MT	AA3204 MB	AA3204C H	AA3204D B	AA3204R S	5A - 250 V~	Sin gle pol e	Rock er	3

Blank

Commercial ref						Designation
Matt White	Matt Titanium	Matt Black	Champagne	Drak Bronze	Rose	
AC150MW	AC150MT	AC150MB	AC150CH	AC150DB	AC150RS	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	AC153CH	AC153DB	AC153RS	2 BLANK MODULES

Frame

Commercial ref	Designation
A1404	1G 3M HORIZOVERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1417	6M BS FRAME
A1411	8M BS FRAME
A1406	4M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1405	3M IT/US FRAME
A1414	2X6M FR/B/SCH HOR SCREW FRAME
A1410	4"X4" FRAME
A1416	2X3M 4"X4" FRAME



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature


 LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A.S au capital de 15.745.984 €
 RCS Nanterre B 408 363 174
Julien GAUTHIER
 F - 92266 FONTENAY AUX ROSES
 Certification Officer

ANNEX

Cover plates

Commercial ref										Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
Classic										
AC1104MW	AC1104MT	AC1104MB	AC1104FW	AC1104FB	AC1104DA	AC1104BS	AC1104NB	AC1104SA	1G 3M BS HORIZVERT PLATE	
AC1105MW	AC1105MT	AC1105MB	AC1105FW	AC1105FB	AC1105DA	AC1105BS	AC1105NB	AC1105SA	3M BS PLATE FOR 2G BOX	
AC1110MW	AC1110MT	AC1110MB	AC1110FW	AC1110FB	AC1110DA	AC1110BS	AC1110NB	AC1110SA	4M IT/FR/SCH PLATE	
AC1111MW	AC1111MT	AC1111MB	AC1111FW	AC1111FB	AC1111DA	AC1111BS	AC1111NB	AC1111SA	6M IT/FR/SCH PLATE	
AC1107MW	AC1107MT	AC1107MB	AC1107FW	AC1107FB	AC1107DA	AC1107BS	AC1107NB	AC1107SA	3M IT/US PLATE	
Hybrid										
			AB1201FW	AB1201FB	AB1201DA	AB1201BS	AB1201NB	AB1201SA	6M HYBRID PLATE 3M + 2M SWITCH	
			AB1204FW	AB1204FB	AB1204DA	AB1204BS	AB1204NB	AB1204SA	6M HYBRID PLATE 4M + 1M SWITCH	
			AB1200FW	AB1200FB	AB1200DA	AB1200BS	AB1200NB	AB1200SA	6M HYBRID PLATE 3M + 2M DIMMER	
			AB1206FW	AB1206FB	AB1206DA	AB1206BS	AB1206NB	AB1206SA	8M HYBRID PLATE 5M +2M DIMMER	
Commercial ref										Designation
Champagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
Classic										
AC1104CH	AC1104DB	AC1104RS	AC1104BB	AC1104AB	AC1104SZ	AC1104SD	AC1104SB	AC1104SR	AC1104SC	1G 3M BS HORIZ/VERT PLATE
AC1105CH	AC1105DB	AC1105RS	AC1105BB	AC1105AB	AC1105SZ	AC1105SD	AC1105SB	AC1105SR	AC1105SC	3M BS PLATE FOR 2G BOX
Hybrid										
			AB1201BB	AB1201AB	AB1201SZ	AB1201SD	AB1201SB	AB1201SR	AB1201SC	6M HYBRID PLATE 3M+2M SWITCH
			AB1204BB	AB1204AB	AB1204SZ	AB1204SD	AB1204SB	AB1204SR	AB1204SC	6M HYBRID PLATE 4M+1M SWITCH
			AB1200BB	AB1200AB	AB1200SZ	AB1200SD	AB1200SB	AB1200SR	AB1200SC	6M HYBRID PLATE 3M+2M DIMMER
			AB1206BB	AB1206AB	AB1206SZ	AB1206SD	AB1206SB	AB1206SR	AB1206SC	8M HYBRID PLATE 5M+2M DIMMER



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature:



ANNEX

Frame + cover plates

Commercial ref										Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
Classic										
AC1204M W	AC1204M T	AC1204M B	AC1204 FW	AC1204 FB	AC1204DA	AC1204BS	AC1204N B	AC120 4SA	6M BS PLATE+FRA ME	
AC1209M W	AC1209M T	AC1209M B	AC1209 FW	AC1209 FB	AC1209DA	AC1209BS	AC1209N B	AC120 9SA	2 X 6M BS PLATE+FRA ME	
AC1206M W	AC1206M T	AC1206M B	AC1206 FW	AC1206 FB	AC1206DA	AC1206BS	AC1206N B	AC120 6SA	8M PLATE+FRA ME	
Commercial ref										Designation
Champagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
Classic										
AC1204CH	AC1204DB	AC1204RS	AC1204BB	AC1204AB	AC1204SZ	AC1204SD	AC1204SB	AC1204SR	AC1204SC	6M BS PLATE+FRA ME
AC1209CH	AC1209DB	AC1209RS	AC1209BB	AC1209AB	AC1209SZ	AC1209SD	AC1209SB	AC1209SR	AC1209SC	2 X 6M BS PLATE+FRA ME
AC1206CH	AC1206DB	AC1206RS	AC1206BB	AC1206AB	AC1206SZ	AC1206SD	AC1206SB	AC1206SR	AC1206SC	8M PLATE+FRA ME



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

 Signature: 


ANNEX

standard Sheet:	standard sheet of BS 546
rated current (A)	15A or 5A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	See table above
socket-outlets	
multiple socket-outlets	15A : 1 or 2
number of socket-outlets	5A: 1
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
Switched socket-outlets without interlock	
According to the method of actuating the switch	rocker
According to the switching of the neutral	Unswitched neutral



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 09/05/2025

Signature:



LABORATOIRE CENTRAL DES
 INDUSTRIES ELECTRIQUES
 S.A.S au capital de 15.745.984 €
 R.C.S. Nanterre 538 700 100
 L.E. 1 33 avenue du Général Leclerc
 92260 FONTENAY-AUX-ROSES

Julien GAUTHIER
 Certification Officer