

LICENCE

No. 16515 - Issue No 2

Issued to: Applicant:

Legrand Group Belgium N.V. Kouterveldstraat 9, Ind. Zone 1831 DIEGEM Belgium

Licensee:

Legrand Group Belgium N.V. Kouterveldstraat 9, Ind. Zone 1831 DIEGEM Belgium

Product : socket-outlets, portable- (2-pole)

Trade name(s) : LEGRAND

Type(s)/model(s) : HE06

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex
- an inspection of the production location
- a certification agreement with the number 178

SGS CEBEC hereby grants the right to use the CEBEC certification mark

The CEBEC certification mark may be applied to the product as specified in
this licence for the duration of the CEBEC certification agreement and under the
conditions of the CEBEC certification agreement.

This licence is issued on :

29/07/2015

ir. C. Lana,

Certification Manager

© Only integral publication of this certificate, including the annex, is allowed This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee





SGS Belgium NV-Division SGS CEBEC Business Riverside Park Bid Internationalelaan 55 Build, D B-1070 Brussels Tel.+32(0)2 556 00 20 Fax.+32(0)2 556 00 36 This certificate is issued by the company under its General Conditions for Certification Services accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitations of liability defined therein and in the Test Report herein mentioned which findings are reflected in this Certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.



ANNEX TO CEBEC LICENCE No. 16515 - Issue No 2 Page 1 of 3

SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product : socket-outlets, portable- (2-pole)

Trade name(s) : LEGRAND

Type(s)/Model(s) : HE06

rated current (In) : 2,5 A

rated voltage (Un) : 250 Vac

earthing : without earthing contact

class : for class II appliances

colour(s) : black or white (see additional information)

design : rewirable

standard sheet : XXIII

terminals : screw type

certification mark : complies with the requirements

description : body of thermoplastic material

markings : are shown on the body

Additional information

Commercial references:

Black model: 050307 White model: 050311

TESTS

Test requirements

NBN C 61-112-1 based on IEC 60884-1:2002 + A1:2006

Test results

The test results are laid down in certification file ref.585773/04

Remarks

This certificate is based on test report ref. 585773.02

ANNEX TO CEBEC LICENCE No. 16515 - Issue No 2 Page 2 of 3

Conclusion

The examination proved that all test requirements were met.

Checked by, project leader

Zanutto Luigi - 29/07/2015

2015-07-29

Department Manager, Product Certification

Certification Manager



ANNEX TO CEBEC LICENCE No. 16515 - Issue No 2 Page 3 of 3

FACTORY LOCATION(S)

Ningbo Banmen Electric Co., Ltd. Guanhaiwei East Industrial Zone, Cixi, Ningbo Province, China