

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Dimmer switch

Name and address of the applicant

LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
France

Name and address of the manufacturer

LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
France

Name and address of the factory

Note: When more than one factory, please report on page 2

See additional page(s) for the listing of 6 factories

Ratings and principal characteristics

110 V ~ 75 W max or 230 V ~ 125 W max  
0,68 A max  
50/60 Hz  
IP 20

Trademark / Brand (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

CXM22  
For detailed Type Reference List see Additional page(s).

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information.  
For accessories (cover plates, covers and frames)  
see CB Test Report.

A sample of the product was tested and found to be in conformity with

IEC 60669-2-1:2021  
IEC 60669-1:2017  
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

HU24F679 001

This CB Test Certificate is issued by the National Certification Body

TÜV Rheinland InterCert Kft., MEEI Division  
H-1143 Budapest, Gizella út 51-57., Hungary  
Web: www.tuv.com

Date: 2024-11-22

Signature:



Tötös Tamás László

**Additional information :**

## Type Reference List

Range	Reference	Designation - PRO/DIY - Description
CELIANE	0 670 83A	DIMMER 2 WIRES 125W - PRO - MO
CELIANE	CM0060	ECODIMMER 2 WIRES WITHOUT NEUTRAL - PRO - MO
	CX0060	ECODIMMER 2 WIRES WHITE - DIY - WCP
	CY0060	ECODIMMER 2 WIRES TITANIUM - DIY - WCP
	CZ0060	ECODIMMER 2 WIRES BLACK - DIY - WCP
	CB9060	ECODIMMER 2 WIRES WHITE - PRO - CP
	CG0060	ECODIMMER 2 WIRES WHITE - DIY - CP
MOSAIC	0 784 07A	DIMMER 2 WIRES 125W WHITE - PRO - WFCP
	0 996 86A	DIMMER 2 WIRES 125W WHITE - DIY - WFCP
	0 488 70LA	DIMMER 2 WIRES 125W WHITE - PRO - CP
	0 992 13A	DIMMER 2 WIRES 125W WHITE - DIY - CP
	0 792 07A	DIMMER 2 WIRES 125W ALU - PRO - WFCP
	0 791 07LA	DIMMER 2 WIRES 125W BLACK - PRO - WFCP
DOOXIE	6 000 60A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	6 001 60A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	6 002 60A	DIMMER 2 WIRES 125W BLACK - PRO - WCP
	0 952 10A	DIMMER 2 WIRES 125W WHITE - DIY - WCP
	0 950 13A	DIMMER 2 WIRES 125W WHITE - DIY - CP
	0 952 70A	DIMMER 2 WIRES 125W BLACK - DIY - WCP
	0 952 40A	DIMMER 2 WIRES 125W ALU - DIY - WCP
	0 950 33A	DIMMER 2 WIRES 125W ALU - DIY - CP
	0 950 53A	DIMMER 2 WIRES 125W WHITE - DIY - CP
	0 950 73A	DIMMER 2 WIRES 125W ALU - DIY - CP
NILOE	3 966 35A	DIMMER 2 WIRES 125W WHITE - DIY - WCP
	3 966 20A	DIMMER 2 WIRES 125W CREAM - DIY - WCP
	0 488 71A	DIMMER 2 WIRES 125W PUR WHITE - PRO - CP
	3 971 27A	DIMMER 2 WIRES 125W ALU - DIY - WCP
	3 976 27A	DIMMER 2 WIRES 125W BLACK - DIY - WCP
	6 651 14A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	6 652 14A	DIMMER 2 WIRES 125W IVORY - PRO - WCP
	6 653 14A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	6 654 14A	DIMMER 2 WIRES 125W ANTHRACITE - PRO - WCP
	6 657 14A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	6 658 14A	DIMMER 2 WIRES 125W ALU - PRO - WCP
NILOE STEP	3 983 12A	DIMMER 2 WIRES 125W WHITE - DIY - WCP
	3 983 13A	DIMMER 2 WIRES 125W ALU - DIY - WCP
	3 983 14A	DIMMER 2 WIRES 125W BLACK - DIY - WCP
	8 631 53A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	8 633 53A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	8 634 53A	DIMMER 2 WIRES 125W GREY - PRO - WCP
	8 635 53A	DIMMER 2 WIRES 125W BLACK - PRO - WCP



Date: 2024-11-22

Signature:

as on page 1

**Additional information :**

NILOE STEP	8 640 18A	DIMMER 2 WIRES 125W - PRO - WCCP
VALENA	6 942 89A	DIMMER 2 WIRES 125W WHITE - DIY - WCP
	7 700 74A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
VALENA	7 521 62A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
LIFE	7 522 62A	DIMMER 2 WIRES 125W IVORY - PRO - WCP
	7 523 62A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	7 524 62A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	7 525 62A	DIMMER 2 WIRES 125W IVORY - PRO - WCP
	7 526 62A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	7 563 82A	DIMMER 2 WIRES 125W BLACK - PRO - WCP
VALENA	7 415 63A	DIMMER 2 WIRES 125W WHITE - PRO - WCP-FwC
NEXT	7 416 63A	DIMMER 2 WIRES 125W ALU - PRO - WCP-FwC
	7 417 63A	DIMMER 2 WIRES 125W BLACK - PRO - WCP-FwC
	7 412 54A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	7 413 54A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	7 414 54A	DIMMER 2 WIRES 125W BLACK - PRO - WCP
	1 965 05A	DIMMER 2 WIRES 125W WHITE -DIY - WCP
	1 965 25A	DIMMER 2 WIRES 125W ALU - DIY - WCP
	1 965 45A	DIMMER 2 WIRES 125W BLACK - DIY - WCP
VALENA	7 527 62A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
ALLURE	7 528 62A	DIMMER 2 WIRES 125W IVORY - PRO - WCP
	7 529 62A	DIMMER 2 WIRES 125W ALU - PRO - WCP
VALENA	7 520 62A	DIMMER 2 WIRES 125W - PRO - WCCP
INMATIC		
ARTEOR	5 722 39A	DIMMER 2 WIRES 125W WHITE - PRO - WFCP
	5 727 39A	DIMMER 2 WIRES 125W MAGNESIUM - PRO - WFCP
	5 729 36A	DIMMER 2 WIRES 125W ALU - PRO - WFCP
	5 729 37A	DIMMER 2 WIRES 125W CHAMPAGNE - PRO - WFCP
ARTEOR	AC24104MW	2M PUSH DIM 125W W/O NEUTRAL MW - PRO - WFCP
ADVANCE	AC24104MB	2M PUSH DIM 125W W/O NEUTRAL MB - PRO - WFCP
	AC24104MT	2M PUSH DIM 125W W/O NEUTRAL MT - PRO - WFCP
SUNO	7 211 78A	DIMMER 2 WIRES 125W WHITE - PRO - WCP
	7 212 78A	DIMMER 2 WIRES 125W IVORY - PRO - WCP
	7 213 78A	DIMMER 2 WIRES 125W ALU - PRO - WCP
	7 214 78A	DIMMER 2 WIRES 125W BLACK - PRO - WCP

CP means Complete Product                      WCP means Without Cover Plate  
MO means Mechanism Only                      WFCP means Without Frame/Cover Plate  
FwC means FwC                                      WCCP means Without Cover/Cover Plate

All the commercial references listed above may be supplemented with a prefix of type "LG-" and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...



Date: 2024-11-22

Signature:

as on page 1

**Factories :**

1. LEGRAND France  
128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex  
France
2. LEGRAND Magyarország Villamossági Rendszerek ZRt.  
Ipartelepi út 14. 6600 Szentés  
Hungary
3. LEGRAND Elektrik Sanayi A.S.  
Gebze Organize Sanayi Bolgesi, Ihsan Dede Caddesi 112 41480 Kocaeli  
Türkiye
4. CARDONAPLAST SAU  
Pol. Ind. la Cort C/Forn 4-5 08261 Cardona  
Spain
5. NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PRIVATE LTD  
A-2, SINNAR - MALEGAON VILLAGE MIDC, NASHIK PUNE ROAD, NASHIK district,  
MAHARASHTRA. 422113  
India
6. NP Hungária Kft.  
Ipari park 07/54 hrsz. 5440 Kunszentmárton  
Hungary