EÚ Vyhlásenie o zhode

vydané podľa zákona 56/2018 Z.z. o technických požiadavkách na výrobky a o posudzovaní zhody

Názov organizácie: **LEGRAND Slovensko, s.r.o.**
Adresa: **Panónska cesta 7, 851 04 BRATISLAVA**
IČO: **35835907**
IČ DPH: **SK2020287192**

Výrobca: **Legrand France, 128 Avenue du Marechal de Lattre de Tassigny 87045 Limoges Cedex**

Výrobok: **Plexo IP55 silové zásuvky 2P+T + príslušenstvo**
- obj.č.: - viď.príloha

Výrobca vyhlasuje, že

- uvedený výrobok je pri určenom použití bezpečný a prijaté opatrenia, ktorými je zabezpečená zhoda všetkých výrobkov uvádzaných na trh s technickou dokumentáciou, so základnými požiadavkami nariadení vlády, ktoré sa na ne vzťahujú a požiadavkami technických predpisov

- vlastnosti tohto výrobku spĺňajú technické požiadavky, ktoré sa na tento výrobok vzťahujú a ktoré sú uvedené v príslušných nariadeniach vlády, príp. v iných technických predpisoch

Posúdenie zhody bolo vykonané podľa:

európskych smerníc

- 2014/35/EU
o harmonizácii právnych predpisov členských štátov týkajúcich sa sprístupnenia elektrického zariadenia určeného na používanie v rámci určitých limitov napätia na trhu
- 2014/30/EU
o harmonizácii právnych predpisov členských štátov vzťahujúcich sa na elektromagnetickú kompatibilitu
- 2011/65/EU modifikované 2015/863 (ROHS 2)
o obmedzení používania určitých nebezpečných látok v elektrických a elektronických zariadeniach

a nariadení vlády SR

- č.325/2019 Z.z.
o sprístupňovaní elektrického zariadenia určeného na používanie v rámci určitých limitov napätia na trhu
- č.331/2019 Z.z.
o elektromagnetickej kompatibilite zariadení

Pri posudzovaní zhody boli použité tieto normy:

STN IEC 60884-1:2002(ed.3) + A1:2006 + A2:2013

Identifikácia: LCIE - Laboratoire Central des Industries Electriques
33, avenue du Général Leclerc, 92260 Fontenay-aux-Roses, France

Číslo certifikátu: FR_711319

Vyhlasovateľ: Meno: Emmanuel Regent
Funkcia: Country Manager Czech Republic & Slovak Republic
Adresa: Panónska cesta 7, 851 04 Bratislava 5
Dátum: 19.1.2022

Podpis:

legrand
LEGRAND Slovensko, s.r.o.
Panónska cesta 7, 851 04 Bratislava
IČO: 35835907 IČ DPH: SK2020287192

Screwless terminals

Type references	References						Designation
	Composable			Complete product			
	Grey	*White*	*Artic white*	*Grey*	*White*	*Artic white*	
TFA	0 695 51	0 696 21	0 707 21	0 697 31			*2P+E*
TFA	0 695 55						*2P+E automatic opening of lid*
TFA2H	0 695 62	0 696 42					*2P+T two gang horizontal, pre-wired*
TFA2V	0 695 63	0 696 43					*2P+E two gang vertical, pre-wired*
TFA3H	0 695 64	0 696 44					*2P+E three gang horizontal, pre-wired*
TFA2H				0 697 49			*Garden piquet*

Screw-type terminals

Type references	References						Designation
	Composable			Complete product			
	Grey	White	Artic white	Grey	White	Artic white	
TFV	0 695 52	0 696 22					2P+E
TFV2H	0 695 65						2P+E two gang horizontal, pre-wired
	0 695 53	0 696 23					2P+E tamperproof

Box

References			Designation
Grey	White	Artic white	
0 696 51	0 696 89	0 707 41	1 gang with cable gland (1 entry – 1 exit)
0 696 55			1 gang with cable gland (1 entry – 2 exits)
0 696 61	0 696 91	0 707 43	2 gang vertical with cable gland
0 696 79			3 gang vertical with cable gland
0 696 72	0 696 90	0 707 42	2 gang horizontal with cable gland
0 696 80			3 gang horizontal with cable gland
0 695 96	0 696 46		membrane cable gland
0 695 99			membrane cable gland 2 entries
0 695 98			set of 4 covers
0 696 52			1 gang with screw gland gaz pitch (1 at the top)
0 696 64			2 gang vertical with screw gland gaz pitch (2 at the top)
0 696 74			2 gang horizontal with screw gland gaz pitch (2 at the top)
0 696 53			screw gland gaz pitch
0 696 56			1 gang with screw gland ISO 20 (1 at the top)
0 696 57			1 gang with screw gland ISO 20 (1 at the top 1 at the bottom)
0 696 58			1 gang with screw gland ISO 20 (2 at the top)
0 696 59			1 gang with screw gland ISO 20 (2 at the top – 1 at the bottom)
0 696 66			2 gang vertical with screw gland ISO 20 (1 at the top)
0 696 67			2 gang vertical with screw gland ISO 20 (1 at the top 1 at the bottom)
0 696 68			2 gang vertical with screw gland ISO 20 (2 at the top)
0 696 69			2 gang vertical with screw gland ISO 20 (2 at the top – 1 at the bottom)
0 696 78			2 gang horizontal with screw gland ISO 20 (2 at the top)
0 980 03			screw gland ISO 20
0 695 79			Mosaic adaptor with lockable smoked lid
0 695 80		0 707 25	Mosaic adaptor with smoked lid
0 695 84	0 696 84		Mosaic adaptor with lid
0 695 82			Mosaic adaptor without lid