



Ref. Certif. No.

HU-005160

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Connected roller shutter switch

Name and address of the applicant

LEGRAND France
128 Avenue du Maréchal de Lattre de Tassigny
87045 Limoges Cedex
France

Name and address of the manufacturer

LEGRAND France
128 Avenue du Maréchal de Lattre de Tassigny
87045 Limoges Cedex
France

Name and address of the factory

Note: When more than one factory, please report on page 2

See additional page(s) for the listing of 3 factories

Ratings and principal characteristics

110-240 V~, 50/60 Hz, IP20
Current (In).....: 2 A max.
Power.....: 500 W max.
Inrush current.....: 3 x In max.
Standby consumption....: 0,1 mA

Trademark / Brand (if any)

LEGRAND

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

ZLSH15
For detailed list of Type references see Additional page(s).

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information.

For the accessories (cover plates and covers) and for the places of production for types and accessories see CB Test Report.

A sample of the product was tested and found to be in conformity with

IEC 60669-2-1:2021
IEC 60669-1:2017
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

HU24SMKU 001

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2024-11-07

Signature:

Tötös Tamás

Tötös Tamás László

10/061SMD 2022-07 rke-fix

Additional information :

Detailed list of Type references

Trademark	Design	Colour	Reference	Additional information
LEGRAND	CELIANE	White DIY	1 991 64	Complete product
		White PRO	0 677 26A	Without cover plate
			1 000 64A	Pack: 10 x 0 677 26A
			0 676 36	Pack: Complete prod. + ZLE20
		Titanium DIY	1 991 74	Complete product
		Titanium PRO	0 677 76A	Without cover plate
			0 676 37	Pack: Complete prod. + ZLE20
		Graphite DIY	1 991 84	Complete product
		Graphite PRO	0 648 96A	Without cover plate
			0 676 26	Pack: Complete prod. + ZLE20
		White PRO	CB0431	Without cover plate
		White DIY	CB9431	Complete product
		Titanium PRO	CT0431	Without cover plate
Titanium DIY	CT9431	Complete product		
Graphite PRO	CN0431	Without cover plate		
Graphite DIY	CN9431	Complete product		
MOSAIC	White PRO		0 777 06LA	Without cover plate
			0 777 36L	Pack: Complete prod. + ZLE20

< List continues next page. >



Date: 2024-11-07

Signature:

as on page 1

Additional information :

Trademark	Design	Colour	Reference	Additional information
LEGRAND	DOOXIE	White DIY	1 992 34	Complete product
		Titanium DIY	1 992 54	Complete product
		White PRO	6 000 86A	Without Cover Plate
			1 000 84A	Pack: 10 x 6 000 86A
			6 006 96	Pack: Complete prod. + ZLE20
		Aluminium PRO	6 001 86A	Without cover plate
VALENA LIFE	White PRO		7 521 90A	Complete product
			7 521 57	Pack: Complete prod. + ZLE20
		Ivory PRO	7 522 90A	Complete product
		Aluminium PRO	7 523 90A	Complete product
		Black PRO	7 563 90A	Complete product
VALENA ALLURE	White PRO		7 525 90A	Complete product
		Ivory PRO	7 526 90A	Complete product
		Aluminium PRO	7 527 90A	Complete product
		Black PRO	7 528 90A	Complete product
		Pearl PRO	7 529 90A	Complete product
VALENA NEXT	White PRO		7 418 07A	Complete product
		Aluminium PRO	7 418 37A	Complete product
		Black PRO	7 418 67A	Complete product

< List continues next page. >



Date: 2024-11-07

Signature:

as on page 1

Additional information :

Trademark	Design	Colour	Reference	Additional information
LEGRAND	SUNO	White PRO	7 221 78	Without cover plate
		Ivory PRO	7 222 78	Without cover plate
		Aluminium PRO	7 223 78	Without cover plate
		Black PRO	7 224 78	Without cover plate
NILOE STEP		White PRO	8 636 44	Without cover plate
		Aluminium PRO	8 637 44	Without cover plate
		Black PRO	8 638 44	Without cover plate
		Sand PRO	8 639 44	Without cover plate

< For further details see CB Test Report.>

Factories :

1. LEGRAND France
128 Avenue du Maréchal de Lattre de Tassigny
87045 Limoges Cedex
France
2. LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepi út 14.
6600 Szentés
Hungary
3. LEGRAND Elektrik Sanayi A.S.
Gebze Organize Sanayi Bolgesi, Ihsan Dede Caddesi 112
41480 Kocaeli
Türkiye