

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Fixed socket-outlet (Flush type)
Name and address of the applicant	TCL-Legrand International Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	See page 2
Ratings and principal characteristics	13A, 250V~ 50/60Hz, IP20, Class I
Trademark (if any)	legrand
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	617*57, 28**33, K8/426/13/U***-HK, 57****, 282440***, 678146
Additional information (if necessary may also be reported on page 2)	See page 2-3
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2002+A1+A2, Standard sheet: type G (Configuration of BS 1363-2) National differences: BS 1363-2:2016+A1
As shown in the Test Report Ref. No. which forms part of this Certificate	200302045SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

intertek
Signature: 

Hyden Li

Date: 22 July, 2020



Ref. Certif. No.

SE-101851**Factories**

Legrand (Beijing) Electrical Company Ltd.
No. 4, Chaoqian Road, Changping Kejiyuanqu, Beijing,
China

TCL-Legrand International Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong,
China

LEGRAND Magyarország Villamossági Rendszerek Zrt.
Ipartelepi út 14, H-6600, SZENTES, Csongrád,
Hungary

Additional information

13A 250V~ 50/60Hz, flush type, IP20, Class I, rewirable, with one way Type G outlets (configuration of BS 1363-2), with shutters, with USB charger which evaluated according to IEC 62368-1: 2018 which in conjunction with IEC 62368-3:2017 with report no 200302050SHA-001, with or without plastic cover or metal cover, with design A construction, all type with same construction, only a little different outer enclosure shape and different cover plate painting colour.

Explanation of the symbol "*" in type designation 617*57, 28**33, K8/426/13/U***-HK, 57**** and 282440***.
The symbol can be:

617*57	617057	with plastic cover with arc transition chamfer, with front cover without embossing pattern	white colour
	617257		ivory colour
	617357		dark grey colour
	617457		brown colour
	617657	with plastic cover with angle chamfer, with front cover with embossing pattern	white colour
	617757		anthracite colour
	617857		ivory colour

28**33	281133	plastic cover	White colour
	283133		silver colour
	283333		pearl colour
	283533		dark silver colour
	283933		champagne colour

K8/426/13/U***-HK	K8/426/13/U-HK	plastic cover	White colour
	K8/426/13/U-C-HK		Matt black colour
	K8/426/13/U-C1-HK		rose gold colour
	K8/426/13/U-C2-HK		champagne colour
	K8/426/13/U-C3-HK		dark silver colour
	K8/426/13/U-C4-HK		Pink colour

Date: 22 July, 2020

Signature: 

57****	572158	design A construction, without cover, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.	White colour
	572658		Magnesium colour
	570082		Soft ALU colour
	571082		Champagne colour

282440***	282440	design A construction, plastic cover	White colour
	282440-C		Matt black colour
	282440-C1		rose gold colour
	282440-C2		champagne colour
	282440-C3		dark silver colour

678146: design A construction, without cover, white colour, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible

For 282440*** series and K8/426/13/U***-HK series, they with total same construction, only different type designation according to client's request

Date: 22 July, 2020

Signature: 