

# Tanúsítvány *Certificate*



Tanúsítvány szám *Certificate No.* Oldal *Page*  
UP 69267307 0003

Jegyzőkönyv szám *Test Report No.* Kiadás dátuma *Date of Issue*  
HU24PLEX 001 2024-09-03

Tanúsítvány Tulajdonos *Certificate Holder* Gyártóhely *Manufacturing Plant*  
**HELLINIKI LEGRAND SA** **ADAPEI Charente ESAT de St CLAUD**  
184A Kifissias Avenue, 54 rue du Farnaud,  
15231 Athens, 16450 Saint Claud,  
Greece France

Vizsgálati Jel *Test Mark* Tanúsítás alapjául szolgáló előírások *Tested according to*  
 IEC 60884-1:2022

Tanúsított Termék (Termék azonosítás)  
*Certified Product (Product Identification)*

Socket-outlet with side earthing contacts  
"PLEXO"

Model / Type reference  
**MISV (T002393), A024570AA, A025122AA, A026347AA, A024570AA**  
(For further details see Annex of this certificate)

Ratings  
250 V~, 16 A, IP55

Trademark  


A tanúsítvány a fenti termék típusra vonatkozik. A tanúsítvány a TÜV Rheinland InterCert Kft. Vizsgálati, Ellenőrzési és Tanúsítási Szabályzatán alapszik. A tanúsított termék megfelel a fenti vizsgálati előírásoknak, a sorozatgyártása ellenőrzött. A MEEI megfeleléségi jel használatának joga engedélyezett a tanúsított terméken.

*This certificate refers to the above mentioned product type. The certificate is based on the Testing, Inspection and Certification Regulation of TÜV Rheinland InterCert Kft. The certified product fulfils the above listed requirements and its manufacturing is subject to surveillance. The right to use the MEEI conformity mark is permitted on the certified product.*

Tanúsító Szervezet  
*Certification Body*

TÜV Rheinland InterCert Kft., MEEI Division – Product Certification  
H-1143 Budapest, Gizella út 51-57., Hungary  
www.tuv.com

  
Tamás László Tötös

Validity of certificate can be checked on [www.CERTIPEDIA.com](http://www.CERTIPEDIA.com)

**Annex to certificate No. UP 69267307 0003**

Page 1/1

Type variants and reference numbers

Type	Reference (s)	Colour	Description
<b>MISV, T002393</b>	0 697 33L	grey	Surface type socket-outlet with side earthing contacts (2P+E) and with screw-type terminals Complete product
	0 697 71L	white	
	0 697 83L	anthracite	
	0 698 34L	grey	Flush type socket-outlet with side earthing contacts (2P+E) and with screw-type terminals Complete product with claws
	0 698 68L	white	
	0 695 71L	grey	Socket-outlet with side earthing contacts (2P+E) and with screw-type terminals Mechanism with cover
	0 696 39L	white	
	0 698 39L	anthracite	
<b>A024570AA</b>	0 695 76L	grey	Socket-outlet with side earthing contacts (2X2P+E) and with screwless terminals Mechanism with cover
	0 696 75L	white	
	0 698 79L	anthracite	
<b>A025122AA</b>	0 695 77L	grey	Socket-outlet with side earthing contacts (2X2P+E) and with screwless terminals Mechanism with cover
<b>A026347AA</b>	0 695 78L	grey	Socket-outlet with side earthing contacts (3X2P+E) and with screwless terminals Mechanism with cover
<b>A024570AA</b>	0 697 42L	grey	Surface type socket-outlet with side earthing contacts (2X2P+E) and with screwless terminals and horizontal position Complete product
	0 697 72L	white	

Accessories

References grey	References white	References anthracite	Designation
069651L	069689L	069601L	Box 1 gang with membrane cable gland
069672L	069690L	069602L	Box 2 gangs with membrane cable gland
069680L	069688L	069603L	Box 3 gangs with membrane cable gland
069681L	069692L	069606L	Frame 1 gang
069683L	069694L	069607L	Frame 2 gangs
069687L	069698L	069608L	Frame 3 gangs
069682L	069693L	069609L	Frame 1 gang with claws

**Certification Body**
**Date of issue:**

Budapest, 2024-09-03


  
.....
  
Tamás László Tötös