



Ref. Certif. No.

FR_719885/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Combined socket-outlet and switch
Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong - CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719885 dated 23/08/2024.
Update the list of components

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25041822

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr



Signature: Julien GAUTHIER
Certification Officer

Date: 25/06/2025

ANNEX

Reference	Range*	Product description	Color of enclosure	USB module	Base different	
570015	Arteor	2G BS 13A DP SWITCHED + USB A + USB C 27 W POWER DELIVERY	WHITE	B005398DA, B005398FA, B006854AA, B006854BA	Without cooling holes	
570016			MAGNESIUM			
570017			CHAMPAGNE			
570018			SOFT ALU			
MEC33076WH	New milo BS	2G BS 13A SP SWITCHED + USB A + USB C 27 W POWER DELIVERY	WHITE		With cooling holes	
MEC33076SL			SILVER			
MEC33076CH			CHAMPAGNE			
MEC33076BL			BLACK			
MEC33076RG			ROSE GOLD			
MEC33079WH			WHITE			
MEC33079SL		SILVER				
MEC33079CH		CHAMPAGNE				
MEC33079BL		BLACK				
MEC33079RG		ROSE GOLD				
			2G BS 13A DP SWITCHED + USB A + USB C 27 W POWER DELIVERY			

*The "range" denotes applicant's categorization

CLASSIFICATION

standard Sheet:	BS 1363-2
rated current (A)	13A
rated load (W)	-
rated voltage (V)	250V~
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
socket-outlets	
multiple socket-outlets	
number of socket-outlets	13A: 2
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
plugs:	
class of equipment	-
entry of cable	-



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/06/2025

Signature: 
 Julien GAUTHIER
 Certification Officer



ANNEX

type of components	manufacturer	Certification
USB charger	LEGRAND FRANCE	LCIE test report No. ARLI-ESH-P24042364
Alternative	LEGRAND FRANCE	LCIE test report No. ARLI-ESH-P25030145-R1



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
 33 avenue du Général Leclerc
 92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 25/06/2025



Signature: **Julien GAUTHIER**
 Certification Officer