



Ref. Certif. No.

FR_719741/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Combined socket-outlet and switch
Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001,
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719741 dated 31/07/2024.
Addition of product references

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-2-3:2006
IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25030324

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/05/2025

Signature: Julien GAUTHIER



ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

Model list

Matt White	Matt Titanium	Matt Black	Champagne	Drak Bronze	Rose					
Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Switch	Actuating	Gang	Specificities
AA3201 MW	AA3201 MT	AA3201 MB	AA3201 CH	AA3201 DB	AA3201 RS	13A - 250V~	Single pole	Rockerr	1	
AA3202 MW	AA3202 MT	AA3202 MB	AA3202 CH	AA3202 DB	AA3202 RS	13A - 250V~	Double pole	Rockerr	1	
AA3203 MW	AA3203 MT	AA3203 MB	AA3203 CH	AA3203 DB	AA3203 RS	13A - 250V~	Single pole	Rockerr	1	Pilot light
AA3207 MW	AA3207 MT	AA3207 MB	AA3207 CH	AA3207 DB	AA3207 RS	13A - 250V~	Single pole	Rockerr	2	
AA3208 MW	AA3208 MT	AA3208 MB	AA3208 CH	AA3208 DB	AA3208 RS	13A - 250V~	Double pole	Rockerr	2	
AA3209 MW	AA3209 MT	AA3209 MB	AA3209 CH	AA3209 DB	AA3209 RS	13A - 250V~	Single pole	Rockerr	2	Pilot light



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc

92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 27/05/2025

Signature:



ANNEX

Cover plates

Commercial ref										Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
AA1100MW	AA1100MT	AA1100MB	AA1100FW	AA1100FB	AA1100DA	AA1100BS	AA1100NB	AA1100SA		1G PLATE BS 5/13A SWITCHED SKT
AA1101MW	AA1101MT	AA1101MB	AA1101FW	AA1101FB	AA1101DA	AA1101BS	AA1101NB	AA1101SA		2G BS PLATE 2X13A SWITCHED SKT
Commercial ref										Designation
Champagne	Dark Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
AA1100CH	AA1100DB	AA1100RS	AA1100BB	AA1100AB	AA1100SZ	AA1100SD	AA1100SB	AA1100SR	AA1100SC	1G PLATE BS 5/13A SWITCHED SKT
AA1101CH	AA1101DB	AA1101RS	AA1101BB	AA1101AB	AA1101SZ	AA1101SD	AA1101SB	AA1101SR	AA1101SC	2G BS PLATE 2X13A SWITCHED SKT

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	See the table above
socket-outlets	
multiple socket-outlets	
number of socket-outlets	13A : 1 or 2
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
Switched socket-outlets without interlock	
According to the method of actuating the switch	rocker
According to the switching of the neutral	Switched neutral (Double pole) / unswitched neutral (Single pole)



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/05/2025

Signature: 
