

Test Verification of Conformity

Verification Number: 220300363SHA-V1

On the basis of the referenced test reports, samples tested of the below product have been found to comply with the standards harmonized with the directives listed on this verification at the time the tests were carried out. Other standards and Directives may be relevant to the product. This verification is part of the full test reports and should be read in conjunction with them.

Once compliance with all product relevant **CE** mark directives are verified, including any relevant e.g. risk assessment and production control, the manufacturer may indicate compliance by signing a Declaration of Conformity themselves and applying the mark to products identical to the tested sample(s).

Applicant Name & Address:	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd.,HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China
Product Description:	Switched socket-outlet (Flush type)
Ratings & Principle Characteristics:	AC INPUT:220-250V~50-60Hz/300mA, DC OUTPUT:5V,3A
Models/Type References:	617*44, 28**36, 832*79, 833*79, 282443***, K8/15/13/U2***-HK, 57****, 730079, 738143,281136**,838143,618044
Brand Name(s):	Legrand, Tenby
Relevant Standard(s) / Specification(s) / Directive(s)	EN 55032:2015+A11:2020; EN 55035:2017+A11:2020; EN IEC 61000-6-1:2019; EN IEC 61000-6-3:2021; the EMC directive 2014/30/EU
Report Number(s)	220300363SHA-001
Verification Issuing Office Name & Address:	Intertek Testing Services Shanghai Building No.86, 1198 Qinzhou Road (North), Caohejing Development Zone, Shanghai 200233, China

Additional information in Appendix.



Signature

Name: Jonny Jing

Position: Operation Director

Date: April 13, 2022

This Verification is for the exclusive use of Intertek's client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this Verification. Only the Client is authorized to permit copying or distribution of this Verification. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test/inspection results referenced in this Verification are relevant only to the sample tested/inspected. This Verification by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.