



Ref. Certif. No.

SE-113822

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed socket-outlet (flush-type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045
LIMOGES Cedex-FRANCE

Name and address of the factory

Same as applicant

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

13A 250V~, IP20

Trademark / Brand (if any)

See page 2

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See page 2

Additional information (if necessary may also be reported on page 2)

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

2401B1480SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamngatan 43
Box 1103
SE-164 22 Kista, Sweden

Date: 23 April, 2024

intertek

Signature: Hyden Li



Ref. Certif. No.

SE-113822

Trademark / Brand (if any)



or **tenby** for 8 380 27



for other models

Model / Type Ref.

6 170 45, 6 172 45, 6 173 45, 6 174 45, 6 176 45, 6 177 45, 6 178 45, 281112MW, 281112MG, 281112MB, 281112DS, 281112CH, 281112DB, 281112BA, 281112BB, 6 180 45, 8 380 27, MEC31033WH, MEC31033SL, MEC31033CH, MEC31033BL, MEC31033RG

Additional information

13A 250V~, flush type, IP20, Class I, rewirable, with screw-type terminals, with 2 gang socket outlets comply with type G (configuration of BS 1363-2), with shutters, with plastic or metal cover plate, with or without metal frame.

Total 22 models:

Mounting plate (style 1) with removable cover plate for model 6 170 45, 6 172 45, 6 173 45 and 6 174 45;

Mounting plate (style 2) with removable cover plate for model 6 176 45, 6 177 45 and 6 178 45;

6 170 45, 6 176 45: with white plastic front cover and white plastic cover plate, without metal frame;

6 173 45: with dark plastic front cover and dark plastic cover plate, without metal frame;

6 174 45: with brown plastic front cover and brown plastic cover plate, without metal frame;

6 177 45: with anthracite plastic front cover and anthracite plastic cover plate, without metal frame;

6 172 45, 6 178 45: with ivory plastic front cover and ivory plastic cover plate, without metal frame;

281112MW: with dark plastic front cover and matt white plastic cover plate, with metal frame;

281112MG: with dark plastic front cover and matt grey plastic cover plate, with metal frame;

281112MB: with dark plastic front cover and matt black plastic cover plate, with metal frame;

281112DS: with dark plastic front cover and dark silver plastic cover plate, with metal frame;

281112CH: with dark plastic front cover and champagne plastic cover plate, with metal frame;

281112DB: with dark plastic front cover and dark bronze plastic cover plate, with metal frame;

281112BA: with dark plastic front cover and plastic lining & brushed aluminium metal sheet cover plate, with metal frame;

281112BB: with dark plastic front cover and plastic lining & brushed black metal sheet cover plate, with metal frame.

6 180 45: "White" plastic front cover and cover plate, without metal frame.

8 380 27: "White" plastic front cover and cover plate, without metal frame.

Note: 6 180 45 and 8 380 27 are similar to 6 176 45 except the shape of cover plate.

MEC31033WH: with white plastic front cover and white plastic cover plate, without metal frame.

MEC31033SL: with silver plastic front cover and silver plastic cover plate, without metal frame.

MEC31033CH: with champagne plastic front cover and champagne plastic cover plate, without metal frame.

MEC31033BL: with black plastic front cover and black plastic cover plate, without metal frame.

MEC31033RG: with rose gold plastic front cover and rose gold plastic cover plate, without metal frame.

Date: 23 April, 2024

Signature: