



Ref. Certif. No.

CN52793-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Flush-type Rocker Single-pole Momentary Contact Switch; Flush-type Rocker Single-pole Momentary Contact Switch(Doorbell Switch)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, P.R. China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES Cedex-FRANCE

Name and address of the factory

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, P.R. China

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

See appendix

Trademark / Brand (if any)

Graphic Trademark, See the report

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

See appendix

Additional information (if necessary may also be reported on page 2)

IEC 60669-1:2017

A sample of the product was tested and found to be in conformity with

CVC2020-1394-M1

As shown in the Test Report Ref. No. which forms part of this Certificate

This CB Test Certificate is issued by the National Certification Body

CHINA QUALITY CERTIFICATION CENTRE

Section 9, No. 188 Nansihuan Xilu, Beijing 100070 P. R. China

Tel: +86-10-83886666 Fax: +86-10-83886282

website: http://www.cqc.com.cn



Date: Nov.22,2021

Signature:

谢肇旭

Xie ZhaoXu

CB 0065075

1. Flush-type Rocker Single-pole Momentary Contact Switch
2. Flush-type Rocker Single-pole Momentary Contact Switch
(Doorbell Switch)

Model/Type reference

1. 281041MW, 281041MG, 281041MB, 281041DS, 281041CH, 281041DB,
281041BA, 281041BB, 281042MW, 281042MG,
281042MB, 281042DS, 281042CH, 281042DB, 281042BA,
281042BB, 281047MW, 281047MG, 281047MB, 281047DS,
281047CH, 281047DB, 281047BA, 281047BB,
281041MWSG, 281041MGSG, 281041MBSG, 281041DSSG,
281041CHSG, 281041DBSG, 281041BASG, 281041BBSG,
281042MWSG, 281047MWSG, 281042MGSG,
281047MGSG, 281042MBSG, 281047MBSG, 281042DSSG,
281047DSSG, 281042CHSG, 281047CHSG, 281042DBSG,
281047DBSG, 281042BASG, 281047BASG, 281042BBSG,
281047BBSG

2. 281040MW, 281040MG, 281040MB, 281040DS, 281040CH,
281040DB, 281040BA, 281040BB, 281040MWSG,
281040MGSG, 281040MBSG, 281040DSSG, 281040CHSG,
281040DBSG, 281040BASG, 281040BBSG


Ratings : 10A 250V~

Page 1 of 1

Additional information (if necessary)

Date: Nov.22,2021

Signature:



Xie ZhaoXu