



Ref. Certif. No.

SE-91831

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Circuit breakers
Name and address of the applicant	LEGRAND SNC. 128 avenue du Maréchal de Lattre, de Tassigny, FR-87045 Limoges cedex, FRANCE
Name and address of the manufacturer	Same as applicant
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	See page 2.
Ratings and principal characteristics	$U_e = 240-690V$ AC, $I_n = 250-630A$, 50-60Hz $U_i = 800V$, $U_{imp} = 8kV$, Pattern No. 3-4 See also page 2.
Trademark (if any)	Legrand SNC
Customer's Testing Facility (CTF) Stage used	CTF Stage 2.
Model / Type Ref.	DPX ³ 630 (electronic release)
Additional information (if necessary may also be reported on page 2)	-
A sample of the product was tested and found to be in conformity with	IEC 60947-2:2016
As shown in the Test Report Ref. No. which forms part of this Certificate	1812377STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Box 1103
SE-164 22 Kista, Sweden
Int +46 8 750 00 00

Date: 6 September 2018

intertek

Signature:

Bo Berglöf

Factories

Bticino S.P.A.

Via Folzoni 5, IT-24052 Azzano San Paolo, Bergamo
ITALYWuxi TCL Legrand, Low Voltage Electrical Co., Ltd.
No. 88, Ximei Road, New Zone Wuxi, Jiangsu Province.
P.R.CHINA**Additional information (if necessary)**DPX³ 630 (Traffic Red label) Electronic release

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
220-240	154,0	70,0	70,0	*
380-415	75,6	36,0	36,0	*
440-460	63,0	30,0	30,0	*
480-500	52,5	25,0	25,0	*
690	28,0	14,0	14,0	*

DPX³ 630 (Blue Lilac label) - Electronic release

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
220-240	220,0	100,0	100,0	*
380-415	105,0	50,0	50,0	*
440-460	84,0	40,0	40,0	*
480-500	63,0	30,0	30,0	*
690	36,0	18,0	18,0	*

DPX³ 630 (Light Blue label) - Electronic release

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
220-240	231,0	105,0	105,0	*
380-415	154,0	70,0	70,0	*
440-460	132,0	60,0	60,0	*
480-500	84,0	40,0	40,0	*
690	40,0	20,0	20,0	*

DPX³ 630 (Sapphire Blue label) - Electronic release

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
220-240	330,0	150,0	105,0	*
380-415	220,0	100,0	70,0	*
440-460	154,0	70,0	49,0	*
480-500	105,0	50,0	35,0	*
690	46,2	22,0	15,4	*

* = 5kA for 0,5s at rated current up to 400A
N/A for rated current from 500A to 630A

Date: 6 September 2018

Signature: 