



Ref. Certif. No.

SE-107650

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Three and Four poles Moulded Case Circuit Breaker

Name and address of the applicant

LEGRAND SNC
128, AVENUE DU MARECHAL DE LATTRE DE TASSIGNY,
FR87045 LIMOGES CEDEX, FRANCE

Name and address of the manufacturer

BTICINO SpA - Legrand Group
Viale Borri 231, 21100 Varese,
Italy

Name and address of the factory

Note: When more than one factory, please report on page 2

See page 2

Ratings and principal characteristics

U_e=240-690Vac (50.0-60.0Hz)
I_n=16-125A
U_i=800V
U_{imp}=8.00kV, Pattern No.3 and 4

Trademark (if any)

Legrand

Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

DPX³ 125 HP

Additional information (if necessary may also be reported on page 2)

See page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016+A1

As shown in the Test Report Ref. No. which forms part of this Certificate

2026727STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

intertek

Signature: 

Leif Mattsson

Date: 01 April, 2022

Factories

Bticino S.p.a.
Via dei Folzoni, 5 – 24052, Azzano, San Paolo, Bergamo, ITALY

Legrand Low Voltage Electrical (Wuxi) CO., LTD
No. B-15 National Hi-tech Industrial Development, Zone, Wuxi, Jiangsu Province, P.R.CHINA

Novateur Electrical & Digital Systems Private
Limited, D-4, MIDC Area, Jalgaon-425003, Maharashtra

ОАО КОХТАКТОР. 12, Karl Marx str., Ulyanovsk, 432001, RUSSIAN FEDERATION

Additional information

DPX3 125 HP (Thermal-magnetic release)

Common characteristics:

Voltage ratings	$U_e=240-690V$ (50-60Hz)
Rated current	$I_n=16-125A$
Current setting	Adjustable $(0.8-1) \times I_n$ —Overload Fixed 400A up to 40A—Short Circuit Fixed $10 \times I_n$ up to 125A—Short Circuit

DPX³ 125 HP (Traffic Red label)

U_e (V)	I_{cm} (kA)	I_{cu} (kA)	I_{cs} (kA)	I_{cw} (kA)
240	154	70,0	70,0	N/A
415	75,6	36,0	36,0	N/A
500	24,0	12,0	12,0	N/A
690	7,70	5,00	5,00	N/A

DPX³ 125 HP (Blue Lilac label)

U_e (V)	I_{cm} (kA)	I_{cu} (kA)	I_{cs} (kA)	I_{cw} (kA)
240	198	90,0	90,0	N/A
415	105	50,0	50,0	N/A
500	32,0	16,0	16,0	N/A
690	9,20	6,00	6,00	N/A

Date: 01 April, 2022

Signature: 