



Ref. Certif. No.
SE-104548

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switched socket-outlet (flush-type)
Name and address of the applicant	Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, P. R. China
Name and address of the manufacturer	LEGRAND FRANCE 128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES Cedex- France
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	Same as applicant
Ratings and principal characteristics	13A 250V~, IP20
Trademark (if any)	legrand
Customer's Testing Facility (CTF) Stage used	-
Model / Type Ref.	See page 2
Additional information (if necessary may also be reported on page 2)	See page 2
A sample of the product was tested and found to be in conformity with	IEC 60884-1:2002+A1+A2, IEC 60884-2-3:2006
As shown in the Test Report Ref. No. which forms part of this Certificate	201201702SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden



Signature:

Date: 15 April, 2021

Hyden Li

Model / Type Ref.

6 176 48, 6 177 48, 6 178 48, 281117MW, 281117MG, 281117MB, 281117DS, 281117CH, 281117DB, 281117BA, 281117BB, 281119MW, 281119MG, 281119MB, 281119DS, 281119CH, 281119DB, 281119BA, 281119BB

Additional information

13A 250V~, flush type, IP20, Class I, rewirable, with screw-type terminals, with 2 gang switched socket outlets comply with type G (configuration of BS 1363-2), with shutters, with one double pole switch for each socket-outlet, with plastic cover plate or plastic lining combined with metal sheet cover plate, with or without metal frame, with or without indicator lamp.

Total 19 models:

6 176 48: with white front cover and plastic white cover plate, without metal frame;

6 177 48: with dark front cover and plastic dark cover plate, without metal frame;

6 178 48: with ivory front cover and plastic ivory cover plate, without metal frame;

281117MW: with dark front cover and matt white plastic cover plate, with metal frame;

281117MG: with dark front cover and matt grey plastic cover plate, with metal frame;

281117MB: with dark front cover and matt black plastic cover plate, with metal frame;

281117DS: with dark front cover and dark silver plastic cover plate, with metal frame;

281117CH: with dark front cover and champagne plastic cover plate, with metal frame;

281117DB: with dark front cover and dark bronze plastic cover plate, with metal frame;

281117BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame;

281117BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame;

281119MW: with dark front cover and matt white plastic cover plate, with metal frame, with indicator lamp;

281119MG: with dark front cover and matt grey plastic cover plate, with metal frame, with indicator lamp;

281119MB: with dark front cover and matt black plastic cover plate, with metal frame, with indicator lamp;

281119DS: with dark front cover and dark silver plastic cover plate, with metal frame, with indicator lamp;

281119CH: with dark front cover and champagne plastic cover plate, with metal frame, with indicator lamp;

281119DB: with dark front cover and dark bronze plastic cover plate, with metal frame, with indicator lamp;

281119BA: with dark front cover and plastic lining combined with brushed aluminium metal sheet cover plate, with metal frame, with indicator lamp;

281119BB: with dark front cover and plastic lining combined with brushed black metal sheet cover plate, with metal frame, with indicator lamp.

Date: 15 April, 2021

Signature:

