



Ref. Certif. No.

CNCVC1892-M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

1. Functional Module of Rocker two-way switches with one off-position
2. Functional Module of Rocker Momentary two-way switches with one off-position

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East NO. 39 Hechang 6th Rd., HZZK hi-tech
Industrial Development Zone, Huizhou, Guangdong, P. R. China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES
Cedex-FRANCE

Name and address of the factory

Refer to page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

1. 10AX 250V~ m
2. 6A 250V~ m

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Refer to page 2

Additional information (if necessary may also be reported on page 2)

National Difference: Europe
Model Differences refer to the test reports
Modification Contents Summary refer to page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

CVC0012024-0132, CVC0012024-0132-M1

This CB Test Certificate is issued by the National Certification Body

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn

Date: 2025-04-21

Signature:

Luo Junbo



Name and address of the factory:

1. Legrand Intelligent Electrical (Huizhou) Co.,Ltd.

Bldg. B1-B3, East No.39 Hechang 6th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA

2. NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK- 422113. MAHARASHTRA. INDIA

3. LEGRAND

Avenue du Parc Alata - 60550 Verneuil en Halatte – FRANCE

4. RAIS HASSAN SAADI Logistics Dubai

Jebal Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

5. LEGRAND France

128, Avenue du Marechal de Lattre de Tassigny 87045 LIMOGES Cedex FRANCE

Model:

1. AA26101MW, AA26101MT, AA26101MB (The main device part of function module No. is A027539AA), AC26101MW, AC26101MT, AC26101MB, AC26101CH, AC26101DB, AC26101RS (The main device part of function module No. is A027516AA)

2. AC26102MW, AC26102MT, AC26102MB, AC26102CH, AC26102DB, AC26102RS (The main device part of function module No. is A027515AA)

Modification Contents Summary: This certificate is a technical modification to CNCVC1892, which was issued on 2024-6-26. Modification contents refer to the test report.

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone, Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn

Date: 2025-04-21



Signature: _____

Luo Junbo

Luo Junbo

Bottom Colours are indicated to show the factory locations for each reference and accessories in the table.

Factories	Address
LEGRAND Intelligent ELECTRICAL (HUIZHOU) CO, LTD	Bldg. B1-B3, East No.39 Hechang 6th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA
LEGRAND Intelligent ELECTRICAL (HUIZHOU) CO, LTD	Bldg. B1-B3, East No.39 Hechang 6th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA
NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD	A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK- 422113. MAHARASHTRA. INDIA
LEGRAND	Avenue du Parc Alata - 60550 Verneuil en Halatte - FRANCE
RAIS HASSAN SAADI Logistics Dubai	Jebal Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES
LEGRAND France	128, Avenue du Marechal de Lattre de Tassigny 87045 LIMOGES Cedex FRANCE
NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD	A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK- 422113. MAHARASHTRA. INDIA

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ...(to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...In this case, the products are technically the same.

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2025-04-21



Signature: 
Luo Junbo



Ref. Certif. No.

CNCVC1892-M1

CLASSIC references

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose				
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Pattern	Actuating	Module
A0275 15AA	AC2610 2MW	AC2610 2MT	AC2610 2MB	AC2610 2CH	AC2610 2DB	AC2610 2RS	6A - 250V~	1	RM	1
A0275 16AA	AC2610 1MW	AC2610 1MT	AC2610 1MB	AC2610 1CH	AC2610 1DB	AC2610 1RS	10AX - 250V~	1	R	1

ELITE references

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose				
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Pattern	Actuating	Module
A0275 39AA	AA2610 1MW	AA2610 1MT	AA2610 1MB				10AX - 250V~	1	R	1

Blank

Commercial ref						Designation
Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose	
AC150MW	AC150MT	AC150MB	AC150CH	AC150DB	AC150RS	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	AC153CH	AC153DB	AC153RS	2 BLANK MODULES

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2025-04-21

Signature:

Luo Junbo



Frame

Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W EARTH
A1404	1G 3M HORIZOVERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1417	6M BS FRAME
A1411	8M BS FRAME
A1406	4M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1400	1M PANEL MOUNTING SUPPORT
A1401	2M PANEL MOUNTING SUPPORT
A1405	3M IT/US FRAME
A1412	2M FR/B/SCH CLAW FRAME
A1413	1 & 2M FR/B/SCH SCREW FRAME
A1414	2X6M FR/B/SCH HOR SCREW FRAME
A1410	4"X4" FRAME
A1415	1&2M 2"X4" FRAME
A1416	2X3M 4"X4" FRAME

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2025-04-21



Signature: 
Luo Junbo

Cover plates

Commercial ref									Designation
Matt White	Matt Titanium m	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
Classic									
AC1100 MW	AC1100 MT	AC1100 MB	AC1100 FW	AC1100 FB	AC1100 DA	AC1100 BS	AC1100 0NB	AC1100S A	1G 1M BS PLATE
AC1101 MW	AC1101 MT	AC1101 MB	AC1101 FW	AC1101 FB	AC1101 DA	AC1101 BS	AC1101 1NB	AC1101S A	1M ITALIANUS PLATE
AC1102 MW	AC1102 MT	AC1102 MB	AC1102 FW	AC1102 FB	AC1102 DA	AC1102 BS	AC1102 2NB	AC1102S A	1G 2M BS PLATE
AC1103 MW	AC1103 MT	AC1103 MB	AC1103 FW	AC1103 FB	AC1103 DA	AC1103 BS	AC1103 3NB	AC1103S A	2M ITALIANUS PLATE
AC1104 MW	AC1104 MT	AC1104 MB	AC1104 FW	AC1104 FB	AC1104 DA	AC1104 BS	AC1104 4NB	AC1104S A	1G 3M BS HORIZVERT PLATE
AC1105 MW	AC1105 MT	AC1105 MB	AC1105 FW	AC1105 FB	AC1105 DA	AC1105 BS	AC1105 5NB	AC1105S A	3M BS PLATE FOR 2G BOX
AC1107 MW	AC1107 MT	AC1107 MB	AC1107 FW	AC1107 FB	AC1107 DA	AC1107 BS	AC1107 7NB	AC1107S A	3M IT/US PLATE
AC1108 MW	AC1108 MT	AC1108 MB	AC1108 FW	AC1108 FB	AC1108 DA	AC1108 BS	AC1108 8NB	AC1108S A	2 X 2M BS PLATE

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn

Date: 2025-04-21



Signature:

Luo Junbo

Luo Junbo



Ref. Certif. No.

CNCVC1892-M1

AC111 1MW	AC111 1MT	AC11 11M B	AC1111 FW	AC1111 FB	AC1111 DA	AC1111 BS	AC111 1NB	AC1111 SA	6M IT/FR/SCH PLATE
AC111 8MW	AC111 8MT	AC11 18M B	AC111 8FW	AC111 8FB	AC1118 DA	AC1118 BS	AC111 8NB	AC1118 SA	4X4 US PLATE FOR 2M
Elite									
			AA110 4FW	AA110 4FB	AA1104 DA	AA1104 BS	AA110 4NB	AA1104 SA	1G PLATE FOR 1M SWITCH
			AA110 5FW	AA110 5FB	AA1105 DA	AA1105 BS	AA110 5NB	AA1105 SA	1G PLATE FOR 2X1M SWITCHES
			AA110 9FW	AA110 9FB	AA1109 DA	AA1109 BS	AA110 9NB	AA1109 SA	2G PLATE 2M SWITCH +2M SWITCH
			AA110 8FW	AA110 8FB	AA1108 DA	AA1108 BS	AA110 8NB	AA1108 SA	2G PLATE FOR 3X1M SWITCHES
			AA1112 FW	AA1112 FB	AA1112 DA	AA1112 BS	AA111 2NB	AA1112 SA	2 X 4 PLATE FOR 3M
Hybrid									
			AB110 0FW	AB110 0FB	AB1100 DA	AB1100 BS	AB110 0NB	AB1100 SA	4M HYBRID PLATE 2M + 2M SWITCH
			AB120 1FW	AB120 1FB	AB1201 DA	AB1201 BS	AB120 1NB	AB120 1SA	6M HYBRID PLATE 3M + 2M SWITCH
			AB120 4FW	AB120 4FB	AB1204 DA	AB1204 BS	AB120 4NB	AB120 4SA	6M HYBRID PLATE 4M + 1M SWITCH
			AB120 0FW	AB120 0FB	AB1200 DA	AB1200 BS	AB120 0NB	AB120 0SA	6M HYBRID PLATE 3M + 2M DIMMER
			AB120 6FW	AB120 6FB	AB1206 DA	AB1206 BS	AB120 6NB	AB120 6SA	8M HYBRID PLATE 5M + 2M DIMMER

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2025-04-21

Signature:



Luo Junbo



Cover plates**Commercial ref**

Champane	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	Designation
----------	-------------	------	----------------	-----------------------	-------------------	------------	-------------	------------	-----------------	-------------

Classic

AC1100CH	AC1100DB	AC1100RS	AC1100BB	AC1100AB	AC1100SZ	AC1100SD	AC1100SB	AC1100SR	AC1100SC	1G 1M BS PLATE
AC1102CH	AC1102DB	AC1102RS	AC1102BB	AC1102AB	AC1102SZ	AC1102SD	AC1102SB	AC1102SR	AC1102SC	1G 2M BS PLATE
AC1104CH	AC1104DB	AC1104RS	AC1104BB	AC1104AB	AC1104SZ	AC1104SD	AC1104SB	AC1104SR	AC1104SC	1G 3M BS HORIZ/VERT PLATE
AC1105CH	AC1105DB	AC1105RS	AC1105BB	AC1105AB	AC1105SZ	AC1105SD	AC1105SB	AC1105SR	AC1105SC	3M BS PLATE FOR 2G BOX
AC1108CH	AC1108DB	AC1108RS	AC1108BB	AC1108AB	AC1108SZ	AC1108SD	AC1108SB	AC1108SR	AC1108SC	2 X 2M BS PLATE

Elite

			AA1104BB	AA1104AB	AA1104SZ	AA1104SD	AA1104SB	AA1104SR	AA1104SC	1G PLATE FOR 1M SWITCH
			AA1105BB	AA1105AB	AA1105SZ	AA1105SD	AA1105SB	AA1105SR	AA1105SC	1G PLATE FOR 2X1M SWITCHES
			AA1108BB	AA1108AB	AA1108SZ	AA1108SD	AA1108SB	AA1108SR	AA1108SC	2G PLATE FOR 3X1M SWITCHES

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn

Date: 2025-04-21



Signature: _____

Luo Junbo

Luo Junbo

			AA110 9BB	AA110 9AB	AA11 09SZ	AA110 9SD	AA110 9SB	AA110 9SR	AA110 9SC	2G PLATE 4 x 1M SWITCH
			AA111 8BB	AA111 8AB	AA111 8SZ	AA111 8SD	AA111 8SB	AA111 8SR	AA111 8SC	2 X 4 PLATE FOR 3M SLENDER
Hybrid										
			AB110 0BB	AB110 0AB	AB11 00SZ	AB110 0SD	AB110 0SB	AB110 0SR	AB110 0SC	4M HYBRID PLATE 2M +2M SWITCH
			AB12 00BB	AB12 00AB	AB12 00SZ	AB12 00SD	AB12 00SB	AB12 00SR	AB120 0SC	6M HYBRID PLATE 3M+2M DIMMER
			AB12 01BB	AB12 01AB	AB12 01SZ	AB12 01SD	AB12 01SB	AB12 01SR	AB120 1SC	6M HYBRID PLATE 3M+2M SWITCH
			AB12 04BB	AB12 04AB	AB12 04SZ	AB12 04SD	AB12 04SB	AB12 04SR	AB120 4SC	6M HYBRID PLATE 4M+1M SWITCH
			AB12 06BB	AB12 06AB	AB12 06SZ	AB12 06SD	AB12 06SB	AB12 06SR	AB120 6SC	8M HYBRID PLATE 5M+2M DIMMER

Cover plates + Frame

Commercial ref									Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
Classic									
AC1204M W	AC12 04MT	AC1 204 MB	AC12 04FW	AC12 04FB	AC120 4DA	AC1204BS	AC1 204 NB	AC120 4SA	6M BS PLATE+FRAME
AC1209M W	AC12 09MT	AC1 209 MB	AC12 09FW	AC12 09FB	AC120 9DA	AC1209BS	AC1 209 NB	AC120 9SA	2 X 6M BS PLATE+FRAME
AC1206M W	AC12 06MT	AC1 206 MB	AC12 06FW	AC12 06FB	AC120 6DA	AC1206BS	AC1 206 NB	AC120 6SA	8M PLATE+FRAME

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn

Date: 2025-04-21



Signature: _____

Luo Junbo

Luo Junbo

IEC

IECEE

®

TM

Ref. Certif. No.

CNCVC1892-M1

			AB120 8FW	AB120 8FB	AB1208 DA	AB1208BS	AB1 208 NB	AB1208 SA	4M HYBRID PLATE+FRAME 2M + 2M SWITCH
--	--	--	--------------	--------------	--------------	----------	------------------	--------------	--

Cover plates + Frame

Commercial ref										Designation
Cham pagne	Drak Bron ze	Ro se	Brush ed Bronz e	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
Classic										
AC12 04CH	AC 120 4D B	AC1 204 RS	AC12 04BB	AC1204A B	AC1204 SZ	AC12 04SD	AC12 04SB	AC12 04SR	AC1204SC	6M BS PLATE+FRAM E
AC12 09CH	AC 120 9D B	AC1 209 RS	AC12 09BB	AC1209A B	AC1209 SZ	AC12 09SD	AC12 09SB	AC12 09SR	AC1209SC	2 X 6M BS PLATE+FRAM E
AC12 06CH	AC 120 6D B	AC1 206 RS	AC12 06BB	AC1206A B	AC1206 SZ	AC12 06SD	AC12 06SB	AC12 06SR	AC1206SC	8M PLATE+FRAM E

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2025-04-21

Signature:

Luo Junbo

Luo Junbo

