



Ref. Certif. No.

FR_719318/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed switched socket-outlet
Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001,
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)

 (for all model exclude 838081)
2) Tenby (for model 838081)

Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719318 dated 21/06/2024.
Addition of product references

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25061449

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/10/2025

Signature: 
Certification Officer



ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou
516001, Guangdong - CHINA

Homelan (Huizhou)electrical Co., Ltd.

Jinhu Industrial Park, Baitang Town, Boluo County, Huizhou City, Guang Dong Province - CHINA

References, ratings and main characteristics:

Reference	Description	Color of enclosure	Insert type
618043	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET	White	AG13112
618073	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET 2 EARTH TERMINAL	White	
282486		White	
282486-C		Matt black	
282486-C1		Rosegold	
282486-C2		Champagne	
282486-C3		Dark silver	
838081	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET	White	
617643	1G BS 13A DP SW SOCKET for Lindbergh	Gloss White	
617743		Gloss Grey	
617843		Gloss Ivory	
MEC32038WH	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET	White	
MEC32038SL		Silver	
MEC32038CH		Champange	
MEC32038BL		Black	
MEC32038RG		Rose Gold	
MEC32039WH	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET 2 EARTH TERMINAL	White	
MEC32039SL		Silver	
MEC32039CH		Champange	
MEC32039BL		Black	
MEC32039RG		Rose Gold	
E4/D/UBS-C1-E	1 GANG BS 13A DOUBLE POLE SWITCHED SOCKET	Sliver Black	
E5/D/UBS-J2-E		Brushed Black	
K9R/D/UBS-C2-E		Champagne	
K9R/D/UBS-J2-E		Brushed Black	



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/10/2025

Signature:  **Jérôme REYSSON**
Certification Officer



ANNEX

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	See the table above
socket-outlets	
multiple socket-outlets	13A : 1
number of socket-outlets	
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
Switched socket-outlets without interlock	
According to the method of actuating the switch	rocker
According to the switching of the neutral	Switched neutral



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 27/10/2025

Signature:  **Jérôme REYSSON**
Certification Officer

