



Ref. Certif. No.

FR_719744/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Combined socket-outlet and switch
Switched socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001, Guangdong -
CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719744 dated 01/08/2024.
Update the list of product references

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022
IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25030327

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/05/2025

Signature:



ANNEX

Name and address of the factories:**Legrand Intelligent Electrical (Huizhou) Co., Ltd.**

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong – CHINA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE – FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA – INDIA

References, ratings and main characteristics:

LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 21/05/2025

Signature: 
Julien GAUTHIER
Certification Officer



ANNEX

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

Frame			
Commercial ref	Designation		
A1404	1G 3M HORIZOVERTICAL BS FRAME		
A1408	2G 3M BS FRAME		
A1417	6M BS FRAME		
A1411	8M BS FRAME		
A1406	4M IT/FR/SCH FRAME		
A1407	6M IT/FR/SCH FRAME		
A1405	3M IT/US FRAME		
A1414	2X6M FR/B/SCH HOR SCREW FRAME		
A1410	4"X4" FRAME		
A1416	2X3M 4"X4" FRAME		

Model list

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose				
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Switch	Actuating	Module
T003599	AC3205MW	AC3205MT	AC3205MB	AC3205CH	AC3205DB	AC3205RS	13A - 250V~	Single pole	R	3

Blank

Commercial ref						Designation
Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose	
AC150MW	AC150MT	AC150MB	AC150CH	AC150DB	AC150RS	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	AC153CH	AC153DB	AC153RS	2 BLANK MODULES



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/05/2025

Signature: **JULIEN GAUTHIER**



ANNEX

Cover plates

Commercial ref										Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
Classic										
AC1104M W	AC1104 MT	AC1104 MB	AC1104 FW	AC1104 FB	AC1104DA	AC1104BS	AC1104 NB	AC1104S A	1G 3M BS HORIZVERT PLATE	
AC1105M W	AC1105 MT	AC1105 MB	AC1105 FW	AC1105 FB	AC1105DA	AC1105BS	AC1105 NB	AC1105S A	3M BS PLATE FOR 2G BOX	
AC1110M W	AC1110 MT	AC1110 MB	AC1110 FW	AC1110 FB	AC1110DA	AC1110BS	AC1110 NB	AC1110S A	4M IT/FR/SCH PLATE	
AC1111M W	AC1111 MT	AC1111 MB	AC1111 FW	AC1111 FB	AC1111DA	AC1111BS	AC1111 NB	AC1111S A	6M IT/FR/SCH PLATE	
AC1107M W	AC1107 MT	AC1107 MB	AC1107 FW	AC1107 FB	AC1107DA	AC1107BS	AC1107 NB	AC1107S A	3M IT/US PLATE	
Hybrid										
			AB120 1FW	AB120 1FB	AB1201D A	AB1201B S	AB120 1NB	AB1201S A	6M HYBRID PLATE 3M + 2M SWITCH	
			AB120 4FW	AB120 4FB	AB1204D A	AB1204B S	AB120 4NB	AB1204S A	6M HYBRID PLATE 4M + 1M SWITCH	
			AB120 0FW	AB120 0FB	AB1200D A	AB1200B S	AB120 0NB	AB1200S A	6M HYBRID PLATE 3M + 2M DIMMER	
			AB120 6FW	AB120 6FB	AB1206D A	AB1206B S	AB120 6NB	AB1206S A	8M HYBRID PLATE 5M +2M DIMMER	
Commercial ref										Designation
Cham pagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
Classic										
AC11 04CH	AC11 04DB	AC11 04RS	AC1104 BB	AC1104 AB	AC11 04SZ	AC11 04SD	AC11 04SB	AC1104 SR	AC1104SC	1G 3M BS HORIZ/VERT PLATE
AC11 05CH	AC11 05DB	AC11 05RS	AC1105 BB	AC1105 AB	AC11 05SZ	AC11 05SD	AC11 05SB	AC1105 SR	AC1105SC	3M BS PLATE FOR 2G BOX
Hybrid										
			AB1201 BB	AB1201 AB	AB12 01SZ	AB120 1SD	AB12 01SB	AB1201S R	AB1201SC	6M HYBRID PLATE 3M+2M SWITCH
			AB1204 BB	AB1204 AB	AB12 04SZ	AB120 4SD	AB12 04SB	AB1204S R	AB1204SC	6M HYBRID PLATE 4M+1M SWITCH
			AB1200 BB	AB1200 AB	AB12 00SZ	AB120 0SD	AB12 00SB	AB1200S R	AB1200SC	6M HYBRID PLATE 3M+2M DIMMER
			AB1206 BB	AB1206 AB	AB12 06SZ	AB120 6SD	AB12 06SB	AB1206S R	AB1206SC	8M HYBRID PLATE 5M+2M DIMMER



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/05/2025

Signature: **JULIEN GAUTHIER**


ANNEX

Frame cover plates

Commercial ref									Designation	
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium		
Classic										
AC120 4MW	AC1204 MT	AC12 04MB	AC1204 FW	AC120 4FB	AC1204D A	AC1204BS	AC12 04NB	AC1204SA	6M BS PLATE+FRA ME	
AC120 9MW	AC1209 MT	AC12 09MB	AC1209 FW	AC120 9FB	AC1209D A	AC1209BS	AC12 09NB	AC1209SA	2 X 6M BS PLATE+FRA ME	
AC120 6MW	AC1206 MT	AC12 06MB	AC1206 FW	AC120 6FB	AC1206D A	AC1206BS	AC12 06NB	AC1206SA	8M PLATE+FRA ME	
Commercial ref									Designation	
Champagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose		Solid Champagne
Classic										
AC120 4CH	AC1 204D B	AC12 04RS	AC12 04BB	AC12 04AB	AC12 04SZ	AC12 04SD	AC12 04SB	AC1204SR	AC1204SC	6M BS PLATE+FRA ME
AC120 9CH	AC1 209D B	AC12 09RS	AC12 09BB	AC12 09AB	AC12 09SZ	AC12 09SD	AC12 09SB	AC1209SR	AC1209SC	2 X 6M BS PLATE+FRA ME
AC120 6CH	AC1 206D B	AC12 06RS	AC12 06BB	AC12 06AB	AC12 06SZ	AC12 06SD	AC12 06SB	AC1206SR	AC1206SC	8M PLATE+FRA ME



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/05/2025

Signature: **Julien GAUTHIER**


ANNEX

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated voltage (V)	250V
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
colour	See the table above
socket-outlets	
multiple socket-outlets	13A : 1
number of socket-outlets	
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
Intended for circuits where	a single earthing circuit provides protective earthing
Switched socket-outlets without interlock	
According to the method of actuating the switch	rocker
According to the switching of the neutral	Unswitched neutral



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 21/05/2025

Signature: **Julien GAUTHIER**
Certification Officer