

SE-104797

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switched socket-outlet (Flush type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd. Bldg. B1-B3, East No.39 Hechang 6th Rd.,HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE 128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES Cedex-FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

See page 2

Ratings and principal characteristics

13A 250V~ 50/60Hz, IP20, Class I

Trademark (if any)

legrand (for all types except 738141), tenby (for type 738141)

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

617*58, 28**34, 832*78, 833*78, 282441***, K8/15/13/U***-HK, 730078, 738141, 57****, 281134**

Additional information (if necessary may also be reported on page 2)

See page 2-3

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2, IEC 60884-2-3:2006

As shown in the Test Report Ref. No. which forms part of this Certificate

201201699SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB Torshamnsgatan 43 Box 1103 SE-164 22 Kista, Sweden

intertek

Signature:

Date: 10 May, 2021

Hyden Li

U .

1/3 YUM



SE-104797

Factories

Legrand (Beijing) Electrical Co., Ltd No.4, Chaoqian Road, Changping Kejiyuanqu, Beijing, China

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China

Legrand Electric Ltd

Unit 12 No.1 Industrial Estate Medomsley Road, Consett County Durham, DH8 6SR United Kingdom

Additional information

13A 250V~ 50/60Hz, flush type, IP20, Class I, rewirable, with one way Type G outlets (configuration of BS 1363-2), with shutters, with single pole switch, with USB charger which evaluated according to IEC 62368-1: 2018 which in conjunction with IEC 62368-3:2017 with report no 200302050SHA-001, with metal cover, or with plastic cover plate or plastic lining combined with metal sheet cover plate, or without cover, with or without metal frame, with design A or design B construction, see below for details:

617*58	617058	design A construction,	White colour
	617358	with plastic cover with	Grey colour
	617458	arc transition chamfer,	Brown colour
		with front cover without	
		embossing pattern, with	
		trademark "legrand"	
	617658	design A construction,	White colour
	617758	with plastic cover with	Anthracite colour
	617858	angle chamfer, with front	Ivory colour
		cover with embossing	
		pattern, with trademark	
		"legrand"	
28**34	281134	design A construction,	White colour
	282134	plastic cover, with	Matt black colour
	283134	trademark "legrand"	Silver colour
	283334		Pearl colour
	283534		Dark silver colour
	283934		Champagne colour
	<u> </u>		
832*78	832078	design A construction,	Flat BSS color
	832278	metal cover, with	Flat PSS color
	832478	trademark "legrand"	Flat gold color
833*78	833078	design B construction,	Trad BSS color
	833278	metal cover, with	Trad PSS color
	833478	trademark "legrand"	Trad Gold color

Date: 10 May, 2021 Signature:

2/3 YUM

Cuple



SE-104797

Additional information				
282441***	282441	design A construction,	White colour	
	282441-C	plastic cover, with	Matt black colour	
	282441-C1	trademark "legrand"	Rose gold colour	
	282441-C2		Champagne colour	
	282441-C3		Dark silver colour	
K8/15/13/U***-HK	K8/15/13/U-HK	design A construction,	White colour	
	K8/15/13/U-C-HK	plastic cover, with	Matt black colour	
	K8/15/13/U-C1-HK	trademark "legrand"	Rose gold colour	
	K8/15/13/U-C2-HK		Champagne colour	
	K8/15/13/U-C3-HK		Dark silver colour	
	K8/15/13/U-C4-HK		Pink colour	
57****	572156	design A construction,	White colour	
	572656	without cover, with	Magnesium colour	
	570080	trademark "legrand"	Soft ALU colour	
	571080		Champagne colour	
281134**	281134MW	design A construction,	Matt White	
	281134MG	plastic cover, metal	Matt Grey	
	281134MB	frame, with trademark	Matt Black	
	281134DS	"legrand"	Dark Sliver	
	281134CH		Champagne	
	281134DB		Dark Bronze	
	281134BA	design A construction,	BRUSHED ALUMINIUM	
	281134BB	plastic lining combined	BRUSHED BLACK	
		with metal sheet cover		
		plate, metal frame,		
		with trademark "legrand"		

730078: design B construction, white colour, with trademark "legrand";

738141: same as 730078 except with different enclosure shape and trademark "tenby".

For 282441*** series and K8/15/13/U***-HK series, they with total same construction, only different type designation according to client's request.

For 57**** series, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.

3/3

Standard sheet: type G (Configuration of BS 1363-2)

National differences: BS 1363-2:2016+A1

Date: 10 May, 2021 Signature:

