



Ref. Certif. No.

FR_719743/M1

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlet for fixed-electrical installations
Socket-outlets for fixed installations

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou 516001,
Guangdong - CHINA

Name and address of the manufacturer

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX - FRANCE

Name and address of the factory

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

See Annex

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

See Annex

Additional information (if necessary may also be reported on page 2)

Supersedes CBTC FR_719743 dated 01/08/2024.
Addition of product references

☐ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

ARLI-ESH-P25030326

This CB Test Certificate is issued by the National Certification Body



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 22/05/2025

Signature:  JULIEN GAUTHIER

Certification Officer
LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
33 avenue du Général Leclerc
92260 FONTENAY AUX ROSES

ANNEX

Name and address of the factories:

Legrand Intelligent Electrical (Huizhou) Co., Ltd.

Bldg. B1-B3, East No. 39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong - CHINA

LEGRAND

AVENUE DU PARC ALATA - 60550 VERNEUIL EN HALATTE - FRANCE

RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - United Arab Emirates

NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. NASHIK - 422113, MAHARASHTRA - INDIA

LEGRAND FRANCE

128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY 87045 LIMOGES CEDEX - FRANCE

References, ratings and main characteristics:

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ... In this case, the products are technically the same.

Model list

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose			
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Module	Specificities
T003598	AC3142 MW	AC3142 MT	AC3142 MB	AC3142 CH	AC3142 DB	AC3142 RS	13A - 250V~	2	

Blank

Commercial ref						Designation
Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose	
AC150MW	AC150MT	AC150MB	AC150CH	AC150DB	AC150RS	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	AC153CH	AC153DB	AC153RS	2 BLANK MODULES



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE

33 avenue du Général Leclerc

92260 Fontenay-aux-Roses, FRANCE

www.lcie.fr

Date: 22/05/2025

Signature: **JULIEN GAUTHIER**



ANNEX

Frame

Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W EARTH
A1404	1G 3M HORIZOVERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1417	6M BS FRAME
A1411	8M BS FRAME
A1406	4M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1401	2M PANEL MOUNTING SUPPORT
A1405	3M IT/US FRAME
A1412	2M FR/B/SCH CLAW FRAME
A1413	1 & 2M FR/B/SCH SCREW FRAME
A1414	2X6M FR/B/SCH HOR SCREW FRAME
A1410	4"X4" FRAME
A1415	1&2M 2"X4" FRAME
A1416	2X3M 4"X4" FRAME

Cover plates

Commercial ref									
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	Designation
Classic									
AC1102 MW	AC1102 MT	AC1102 MB	AC1102 FW	AC1102 FB	AC1102 DA	AC1102B S	AC1102 NB	AC1102SA	1G 2M BS PLATE
AC1104 MW	AC1104 MT	AC1104 MB	AC1104 FW	AC1104 FB	AC1104 DA	AC1104B S	AC1104 NB	AC1104SA	1G 3M BS HORIZVERT PLATE
AC1105 MW	AC1105 MT	AC1105 MB	AC1105 FW	AC1105 FB	AC1105 DA	AC1105B S	AC1105 NB	AC1105SA	3M BS PLATE FOR 2G BOX
AC1108 MW	AC1108 MT	AC1108 MB	AC1108 FW	AC1108 FB	AC1108 DA	AC1108B S	AC1108 NB	AC1108SA	2 X 2M BS PLATE
AC1110 MW	AC1110 MT	AC1110 MB	AC1110 FW	AC1110 FB	AC1110 DA	AC1110B S	AC1110 NB	AC1110SA	4M IT/FR/SCH PLATE
AC1111 MW	AC1111 MT	AC1111 MB	AC1111 FW	AC1111 FB	AC1111 DA	AC1111B S	AC1111 NB	AC1111SA	6M IT/FR/SCH PLATE
AC1103 MW	AC1103 MT	AC1103 MB	AC1103 FW	AC1103 FB	AC1103 DA	AC1103B S	AC1103 NB	AC1103SA	2M ITALIANUS PLATE
AC1107 MW	AC1107 MT	AC1107 MB	AC1107 FW	AC1107 FB	AC1107 DA	AC1107B S	AC1107 NB	AC1107SA	3M IT/US PLATE



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 22/05/2025

Signature: 
 LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES
S.A.S au capital de 150 000 000 €
RCS Nanterre 440 000 124
N° SIRET 440 000 124 000 12
F - 92266 FONTENAY AUX ROSES

ANNEX

Hybrid										
			AB1100 FW	AB1100 FB	AB1100 DA	AB1100B S	AB1100 NB	AB1100SA	4M HYBRID PLATE 2M + 2M SWITCH	
			AB1201 FW	AB1201 FB	AB1201 DA	AB1201B S	AB1201 NB	AB1201SA	6M HYBRID PLATE 3M + 2M SWITCH	
			AB1204 FW	AB1204 FB	AB1204 DA	AB1204B S	AB1204 NB	AB1204SA	6M HYBRID PLATE 4M + 1M SWITCH	
			AB1200 FW	AB1200 FB	AB1200 DA	AB1200B S	AB1200 NB	AB1200SA	6M HYBRID PLATE 3M + 2M DIMMER	
			AB1206 FW	AB1206 FB	AB1206 DA	AB1206B S	AB1206 NB	AB1206SA	8M HYBRID PLATE 5M +2M DIMMER	
Commercial ref									Designation	
Champagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose		
Classic										
AC1102 CH	AC110 2DB	AC110 2RS	AC110 2BB	AC110 2AB	AC110 2SZ	AC110 2SD	AC110 2SB	AC110 2SR	AC1102 SC	1G 2M BS PLATE
AC1104 CH	AC110 4DB	AC110 4RS	AC110 4BB	AC110 4AB	AC110 4SZ	AC110 4SD	AC110 4SB	AC110 4SR	AC1104 SC	1G 3M BS HORIZ/VERT PLATE
AC1105 CH	AC110 5DB	AC110 5RS	AC110 5BB	AC110 5AB	AC110 5SZ	AC110 5SD	AC110 5SB	AC110 5SR	AC1105 SC	3M BS PLATE FOR 2G BOX
AC1108 CH	AC110 8DB	AC110 8RS	AC110 8BB	AC110 8AB	AC110 8SZ	AC110 8SD	AC110 8SB	AC110 8SR	AC1108 SC	2 X 2M BS PLATE
Hybrid										
			AB110 0BB	AB110 0AB	AB110 0SZ	AB110 0SD	AB110 0SB	AB110 0SR	AB1100 SC	4M HYBRID PLATE 2M +2M SWITCH
			AB120 1BB	AB120 1AB	AB120 1SZ	AB120 1SD	AB120 1SB	AB120 1SR	AB1201 SC	6M HYBRID PLATE 3M+2M SWITCH
			AB120 4BB	AB120 4AB	AB120 4SZ	AB120 4SD	AB120 4SB	AB120 4SR	AB1204 SC	6M HYBRID PLATE 4M+1M SWITCH
			AB120 0BB	AB120 0AB	AB120 0SZ	AB120 0SD	AB120 0SB	AB120 0SR	AB1200 SC	6M HYBRID PLATE 3M+2M DIMMER
			AB120 6BB	AB120 6AB	AB120 6SZ	AB120 6SD	AB120 6SB	AB120 6SR	AB1206 SC	8M HYBRID PLATE 5M+2M DIMMER

Cover plates + Frame

Commercial ref									Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
Classic									
AC1204 MW	AC120 4MT	AC120 4MB	AC120 4FW	AC1204 FB	AC1204DA	AC1204 BS	AC1204NB	AC1204SA	6M BS PLATE+FRAME
AC1209 MW	AC120 9MT	AC120 9MB	AC120 9FW	AC1209 FB	AC1209DA	AC1209 BS	AC1209NB	AC1209SA	2 X 6M BS PLATE+FRAME
AC1206 MW	AC120 6MT	AC120 6MB	AC120 6FW	AC1206 FB	AC1206DA	AC1206 BS	AC1206NB	AC1206SA	8M PLATE+FRAME
			AB120 8FW	AB1208 FB	AB1208DA	AB1208 BS	AB1208NB	AB1208SA	4M HYBRID PLATE+FRAME 2M + 2M SWITCH



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 22/05/2025

Signature: Julien GAUTHIER



ANNEX

Commercial ref										Designation
Champagne	Drak Bronze	Rose	Brushed Bronze	Brushed Antique Brass	Solid Dark Bronze	Solid Sand	Solid Black	Solid Rose	Solid Champagne	
Classic										
AC1204 CH	AC120 4DB	AC12 04RS	AC120 4BB	AC120 4AB	AC12 04SZ	AC1204 SD	AC1204 SB	AC1204 SR	AC1204SC	6M BS PLATE+FRAME
AC1209 CH	AC120 9DB	AC12 09RS	AC120 9BB	AC120 9AB	AC12 09SZ	AC1209 SD	AC1209 SB	AC1209 SR	AC1209SC	2 X 6M BS PLATE+FRAME
AC1206 CH	AC120 6DB	AC12 06RS	AC120 6BB	AC120 6AB	AC12 06SZ	AC1206 SD	AC1206 SB	AC1206 SR	AC1206SC	8M PLATE+FRAME

CLASSIFICATION

standard Sheet:	standard sheet of BS 1363-2
rated current (A)	13A
rated load (W)	-
rated voltage (V)	250V
household voltage (V)	-
degree of protection	IP20
provision for earthing	with earthing contact
method of connecting the cable	rewirable
type of terminals	screw-type
type of connections	-
colour	See above
socket-outlets	
multiple socket-outlets	
number of socket-outlets	13A : 1
degree of protection against electric shock	normal protection
existence of shutters	with shutters
method of application - mounting	flush-type
method of installation	design A
plugs:	
class of equipment	-
entry of cable	-



LABORATOIRE CENTRAL DES INDUSTRIES ELECTRIQUES - LCIE
33 avenue du Général Leclerc
92260 Fontenay-aux-Roses, FRANCE
www.lcie.fr

Date: 22/05/2025

Signature: **Julien GAUTHIER**
