

## IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

## CB TEST CERTIFICATE

Product

Fixed socket-outlet (Flush type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.  
Bldg. B1-B3, East No.39 Hechang 6th Rd.,  
HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong  
CHINA

Name and address of the manufacturer

LEGRAND FRANCE  
128, Avenue du Maréchal de Lattre de Tassigny  
87045 Limoges Cedex  
FRANCE

Name and address of the factory

See page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

13A 250V~ 50/60Hz, IP20, Class I

Trademark (if any)

 , tenby

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

617\*57A, 28\*\*33A, K8/426/13/UA\*\*-HK, 57\*\*\*\*A, 282440A\*\*\*,  
678146A, 281133A\*\*, 618057,838140

Additional information (if necessary may also be reported on page 2)

See page 2-3

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

210801259SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB  
Torshamnsgatan 43  
Box 1103  
SE-164 22 Kista, Sweden

Signature:

Hyden Li



Date: 13 July, 2022


**Factories**

Legrand Intelligent Electrical (Huizhou) Co., Ltd.  
 Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong  
 CHINA

Legrand Magyarország Villamossági Rendszerek Zrt.  
 Ipartelepi út 14, H-6600 Szentés, Csongrád  
 HUNGARY

**Additional information**

Trademark:

 (for all types except 838140),  
 tenby (for 838140)

Standard sheet: type G (Configuration of BS 1363-2)

National differences: BS 1363-2:2016+A1

13A 250V~ 50/60Hz, flush type, IP20, Class I, rewirable, with one way Type G outlets (configuration of BS 1363-2), with shutters, with USB charger which evaluated according to IEC 62368-1:2018 which in conjunction with IEC 62368-3:2017 with report no. 210801261SHA-001/002, with metal cover, or with plastic cover plate or plastic lining combined with metal sheet cover plate, or without cover plate, with or without metal frame, all type with same construction, only with different cover plate.

617*57A	617657A	with plastic cover with angle chamfer, with front cover with embossing pattern	white colour
	617757A		anthracite colour
	617857A		Ivory colour

28**33A	281133A	plastic cover	White colour
	283133A		silver colour
	283333A		pearl colour
	283533A		dark silver colour
	283933A		champagne colour

K8/426/13/UA**-HK	K8/426/13/UA-HK	plastic cover	White colour
	K8/426/13/UA-C-HK		Matt black colour
	K8/426/13/UA-C1-HK		rose gold colour
	K8/426/13/UA-C2-HK		champagne colour
	K8/426/13/UA-C3-HK		dark silver colour
	K8/426/13/UA-C4-HK		Pink colour

Date: 13 July, 2022

Signature:



57****A	572158A	without cover	White colour
	572658A		Magnesium colour
	570082A		Soft ALU colour
	571082A		Champagne colour

282440A**	282440A	plastic cover	White colour
	282440A-C		Matt black colour
	282440A-C1		rose gold colour
	282440A-C2		champagne colour
	282440A-C3		dark silver colour

281133A**	281133AMW	plastic cover	Matt White
	281133AMG		Matt Grey
	281133AMB		Matt Black
	281133ADS		Dark Sliver
	281133ACH		Champagne
	281133ADB		Dark Bronze
	281133ABA		plastic lining combined with metal sheet cover plate, metal frame
	281133ABB	BRUSHED BLACK	

## Note:

678146A: design A construction, without cover, white colour, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.

For 282440A\*\*\* series and K8/426/13/UA\*\*-HK series, they with total same construction, only different type designation according to client's request.

For 57\*\*\*\*A series, all test evaluated when with mated plastic cover or metal cover which provided by the manufacturer as far as possible.



618057: with plastic cover, white colour, with trademark

838140: same as 618057 except with different enclosure shape, with trademark "tenby".

Date: 13 July, 2022

Signature:

