

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Socket-outlets with side earthing contacts

Name and address of the applicant

LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14. 6600 Szentes
Hungary

Name and address of the manufacturer

LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14. 6600 Szentes
Hungary

Name and address of the factory

Note: When more than one factory, please report on page 2

See additional page(s) for the listing of 2 factories

Ratings and principal characteristics

250 V~, 16 A, IP 20 or IP 21 or IP 44

Trademark / Brand (if any)

legrand

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

A027724, A027725, A027726, A027787, A031641

For Type variants and reference numbers see additional
page of this CB Test CertificateAdditional information (if necessary may also be
reported on page 2)See additional page(s) for further Additional information.
This CB Test Certificate is Modification No.1 to HU-005134,
issued 2024-09-04, due to new added models.A sample of the product was tested and found
to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which
forms part of this Certificate

HU24RUBS 002

This CB Test Certificate is issued by the National Certification Body

TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2025-03-04

Signature:


Tötös Tamás László

Additional information :

Type variants and reference numbers, "Niloé" design

Type	References	Colour	Description
A027724	NP3199WH	white	Socket-outlet (IP20) without earthing contact (2P) and with screw-type terminals and shutters
	NP3199MG	medium grey	
	NP3199BK	black	
A027726	NP3122WH	white	Socket-outlet (IP20) with earthing contact (2P+E) and screw-type terminals and shutters
	NP3122MG	medium grey	
	NP3122BK	black	
	NP3129WH	white	Socket-outlet (IP21) with earthing contact (2P+E) and screw-type terminals and shutters and lid
	NP3129MG	medium grey	
	NP3129BK	black	
A027725	NP3121WH	white	Socket-outlet (IP20) with earthing contact (2P+E) and screw-type terminals and without shutters
	NP3121MG	medium grey	
	NP3121BK	black	
A027787	NP3120WH	white	Socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters
	NP3120MG	medium grey	
	NP3120BK	black	
	NP3128WH	white	Socket-outlet (IP44) with earthing contact (2P+E) and screwless terminals and shutters and flap lid
	NP3128MG	medium grey	
	NP3128BK	black	



Date: 2025-03-04

Signature:

as on page 1

Additional information :

Type variants and reference numbers, "Niloé step" design

Type	References	Colour	Description
A027724	8 631 19B	white	Socket-outlet (IP20) without earthing contact (2P) and with screw-type terminals and shutters
	8 633 19B	aluminium	
	8 634 19B	medium grey	
	8 635 19B	black	
A031641	8 640 19B	-	Socket-outlet without earthing contact (2P) and with screwless terminals and shutters (mechanism only)
A027726	8 640 21B	-	Socket-outlet with earthing contact (2P+E) and screw-type terminals and shutters (mechanism only)
A027725	8 631 21B	white	Socket-outlet (IP20) with earthing contact (2P+E) and screw-type terminals and without shutters
	8 633 21B	aluminium	
	8 634 21B	medium grey	
	8 635 21B	black	
A027787	3 982 07B	white	Socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters
	3 982 50B	white	
	3 982 51B	aluminium	
	3 982 52B	black	
	8 631 20B	white	
	8 633 20B	aluminium	
	8 634 20B	medium grey	
	8 635 20B	black	
	8 641 62B	white	

List continues next page.



Date: 2025-03-04

Signature:

as on page 1

Additional information :

Type	References	Colour	Description
A027787	8 643 62B	aluminium	Socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters
	8 645 62B	black	
	8 646 62B	sand	
	8 641 93B	white	Socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters x 50
	3 983 03B	aluminium	3 x Multipack, socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters
	3 983 05B	black	
	3 983 01B	white	5 x Multipack, socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters
	8 631 23B	white	Socket-outlet (IP44) with earthing contact (2P+E) and screwless terminals and shutters and flap lid
	8 635 23B	black	
	8 641 39B	white	
	8 641 63B	white	Socket-outlet (IP21) with earthing contact (2P+E) and screwless terminals and shutters and lid
	8 643 63B	aluminium	
	8 645 63B	black	
	8 646 63B	sand	
	8 640 20B	-	Socket-outlet (IP20) with earthing contact (2P+E) and screwless terminals and shutters (mechanism only)

For accessories for both designs see CB Test Report.



Date: 2025-03-04

Signature:

as on page 1

Factories :

1. Legrand Egypt, EMB Electrical Industrial S.A.E.
Plot 18, 2nd Industrial zone 32897 Sadat City, Menoufia
Egypt
2. LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepi út 14. 6600 Szentes
Hungary