

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Cable glands for electrical installations and accessories

Name and address of the applicant

bticino S.p.A.
Viale Borri, 231
21100 Varese (VA)
Italy

Name and address of the manufacturer

Legrand France
Rue Paul Nouel
76770 Malaunay
France

Name and address of the factory

ODAG S.r.l.
Via Vecchia, 170
43019 Soragna (PR)
Italy*Note: When more than one factory, please report on page 2* Additional information on page 2

Ratings and principal characteristics

Non-metallic cable glands; cable anchorage type A; single-orifice seal; thread: M12, M16, M20, M25, M32, M40, M50 or M63; temperature range: -20 to +80 °C; impact category: 2, 4 or 5; IP68 (immersion depth: 1 meter, immersion time: 2 hours) (see also pages from 4 to 8 of Test Report No. MI22-0077382-01 and/or Additional Sheet)

Trademark / Brand (if any)



Legrand

Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

PSP series
(see also pages from 5 to 8 of Test Report No. MI22-0077382-01)

Additional information (if necessary may also be reported on page 2)

 Additional information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62444:2010

National differences:
EU Group Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

MI22-0077382-01

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43
Milano, 20138
Italy

Date: 2022-11-30

Signature: Mauro Casari

Description of cable glands PSP series and their accessories (continues on page 2)

Code	Description	Impact category	Colour
098000	Cable gland thread M12 with gasket and nut (sold assembled)	2	Silver grey (RAL 7001)
098001	Cable gland thread M16 with gasket and nut (sold assembled)	2	
098003	Cable gland thread M20 with gasket and nut (sold assembled)	4	
098005	Cable gland thread M25 with gasket and nut (sold assembled)	4	
098006	Cable gland thread M32 with gasket and nut (sold assembled)	4	
098007	Cable gland thread M40 with gasket and nut (sold assembled)	5	
098008	Cable gland thread M50 with gasket and nut (sold assembled)	5	
098009	Cable gland thread M63 with gasket and nut (sold assembled)	5	
381800	Cable gland thread M12 with gasket and nut (sold not assembled)	2	
381801	Cable gland thread M16 with gasket and nut (sold not assembled)	2	
381802	Cable gland thread M20 with gasket and nut (sold not assembled)	4	
381803	Cable gland thread M25 with gasket and nut (sold not assembled)	4	
381804	Cable gland thread M32 with gasket and nut (sold not assembled)	4	
381805	Cable gland thread M40 with gasket and nut (sold not assembled)	5	
381806	Cable gland thread M50 with gasket and nut (sold not assembled)	5	
381807	Cable gland thread M63 with gasket and nut (sold not assembled)	5	
381540	Cable gland thread M12 with gasket	2	Silver grey (RAL 7001)
381541	Cable gland thread M16 with gasket	2	
381542	Cable gland thread M20 with gasket	4	
381543	Cable gland thread M25 with gasket	4	
381544	Cable gland thread M32 with gasket	4	
381545	Cable gland thread M40 with gasket	5	
381546	Cable gland thread M50 with gasket	5	
381547	Cable gland thread M63 with gasket	5	
381558	Cable gland thread M12 with gasket	2	Graphite black (RAL 9011)
381559	Cable gland thread M16 with gasket	2	
381560	Cable gland thread M20 with gasket	4	
381561	Cable gland thread M25 with gasket	4	
381562	Cable gland thread M32 with gasket	4	
381563	Cable gland thread M40 with gasket	5	
381564	Cable gland thread M50 with gasket	5	
381565	Cable gland thread M63 with gasket	5	

Description of cable glands PSP series and their accessories (continued from page 1)

Code	Description	Impact category	Colour
381576	Cable gland thread M12 with gasket	2	Light grey (RAL 7035)
381577	Cable gland thread M16 with gasket	2	
381578	Cable gland thread M20 with gasket	4	
381579	Cable gland thread M25 with gasket	4	
381580	Cable gland thread M32 with gasket	4	
381581	Cable gland thread M40 with gasket	5	
381582	Cable gland thread M50 with gasket	5	
381583	Cable gland thread M63 with gasket	5	
386571	Nut thread M12	—	Silver grey (RAL 7001)
386572	Nut thread M16	—	
386573	Nut thread M20	—	
386574	Nut thread M25	—	
386575	Nut thread M32	—	
386576	Nut thread M40	—	
386577	Nut thread M50	—	
386578	Nut thread M63	—	
386671	Nut thread M12	—	Graphite black (RAL 9011)
386672	Nut thread M16	—	
386673	Nut thread M20	—	
386674	Nut thread M25	—	
386675	Nut thread M32	—	
386676	Nut thread M40	—	
386677	Nut thread M50	—	
386678	Nut thread M63	—	
386881	Nut thread M12	—	Light grey (RAL 7035)
386882	Nut thread M16	—	
386883	Nut thread M20	—	
386884	Nut thread M25	—	
386885	Nut thread M32	—	
386886	Nut thread M40	—	
386887	Nut thread M50	—	
386888	Nut thread M63	—	