



Ref. Certif. No.

SE-118492

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Fixed socket-outlet (flush-type)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech
Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045
Limoges Cedex, France

Name and address of the factory

☒ Additional Information on page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

13A 250V~, IP20

Trademark / Brand (if any)

See page 2

Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See page 2

Additional information (if necessary may also be reported on page 2)

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60884-1:2022

As shown in the Test Report Ref. No. which forms part of this Certificate

2512B0185SHA-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Date: 22 January, 2026

intertek

Signature:

Hyden Li

Factories

1. Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China
2. Novateur Electrical & Digital Systems Private Limited
A-2, MIDC Industrial Area, Malegaon Village, Sinnar, Nashik Maharashtra, 422113, India

Model / Type Ref.

6 170 45, 6 172 45, 6 173 45, 6 174 45, 6 176 45, 6 177 45, 6 178 45, 281112MW, 281112MG, 281112MB, 281112DS, 281112CH, 281112DB, 281112BA, 281112BB, 6 180 45, 8 380 27, MEC31033WH, MEC31033SL, MEC31033CH, MEC31033BL, MEC31033RG

Trademark

or tenby for 8 380 27



for other models

Additional information

Flush type, Class I, rewirable, with screw-type terminals, with 2 gang socket outlets comply with type G (configuration of BS 1363-2), with shutters, with plastic or metal cover plate, with or without metal frame.

Total 22 models:

Mounting plate (style 1) with removable cover plate for model 6 170 45, 6 172 45, 6 173 45 and 6 174 45;

Mounting plate (style 2) with removable cover plate for model 6 176 45, 6 177 45 and 6 178 45;

6 170 45, 6 176 45: with white plastic front cover and white plastic cover plate, without metal frame;

6 173 45: with dark plastic front cover and dark plastic cover plate, without metal frame;

6 174 45: with brown plastic front cover and brown plastic cover plate, without metal frame;

6 177 45: with anthracite plastic front cover and anthracite plastic cover plate, without metal frame;

6 172 45, 6 178 45: with ivory plastic front cover and ivory plastic cover plate, without metal frame;

281112MW: with dark plastic front cover and matt white plastic cover plate, with metal frame;

281112MG: with dark plastic front cover and matt grey plastic cover plate, with metal frame;

281112MB: with dark plastic front cover and matt black plastic cover plate, with metal frame;

281112DS: with dark plastic front cover and dark silver plastic cover plate, with metal frame;

281112CH: with dark plastic front cover and champagne plastic cover plate, with metal frame;

281112DB: with dark plastic front cover and dark bronze plastic cover plate, with metal frame;

281112BA: with dark plastic front cover and plastic lining & brushed aluminium metal sheet cover plate, with metal frame;

281112BB: with dark plastic front cover and plastic lining & brushed black metal sheet cover plate, with metal frame.

6 180 45: "White" plastic front cover and cover plate, without metal frame.

8 380 27: "White" plastic front cover and cover plate, without metal frame.

Note: 6 180 45 and 8 380 27 are similar to 6 176 45 except the shape of cover plate.

MEC31033WH: with white plastic front cover and white plastic cover plate, without metal frame.

MEC31033SL: with white plastic front cover and silver plastic cover plate, without metal frame.

MEC31033CH: with white plastic front cover and champagne plastic cover plate, without metal frame.

MEC31033BL: with white plastic front cover and black plastic cover plate, without metal frame.

MEC31033RG: with white plastic front cover and rose gold plastic cover plate, without metal frame.

Date: 22 January, 2026

Signature:

