

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Functional Moudle of Rocker Double-pole Switch

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co.,Ltd.
Bldg. B1-B3, East NO. 39 Hechang 6th Rd., HZZK hi-tech
Industrial Development Zone, Huizhou, Guangdong, P. R. China

Name and address of the manufacturer

LEGRAND FRANCE
128, Avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES
Cedex-FRANCE

Name and address of the factory

Refer to page 2

Note: When more than one factory, please report on page 2

Ratings and principal characteristics

20AX 250V~

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

/

Model / Type Ref.

Refer to page 2

Additional information (if necessary may also be reported on page 2)

National Differences specified in the CB Test Report.
Model Differences refer to the test reports.
Modification Contents Summary refers to page 2

A sample of the product was tested and found to be in conformity with

IEC 60669-1:2017

As shown in the Test Report Ref. No. which forms part of this Certificate

CVC0012024-0131, CVC0012024-0131-M1,
CVC0012024-0131-M2

This CB Test Certificate is issued by the National Certification Body

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn

Date: 2026-03-10

Signature: _____

Name and address of factory:

1. Legrand Intelligent Electrical (Huizhou) Co.,Ltd.

Bldg. B1-B3, East No.39 Hechang 6th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA

2. NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD

A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. - NASHIK- 422113. MAHARASHTRA. INDIA

3. LEGRAND

Avenue du Parc Alata - 60550 Verneuil en Halatte – FRANCE

4. RAIS HASSAN SAADI Logistics Dubai

Jebel Ali Free Zone, P.O. Box 7 Dubai - UNITED ARAB EMIRATES

5. LEGRAND France

128, Avenue du Marechal de Lattre de Tassigny 87045 LIMOGES Cedex FRANCE

6. Legrand Electric Ltd

Unit 12 No.1 Industrial Estate Medomsley Road Consett, DH8 6SR, County Durham, UNITED KINGDOM

Model list:

AC21110MW, AC21110MT, AC21110MB, AC21109MW, AC21109MT, AC21109MB, AC21110CH, AC21110DB, AC21110RS, AC21109CH, AC21109DB, AC21109RS (The main device part of function module No. is A027514AA)

AA21110MW, AA21110MT, AA21110MB, AA21109MW, AA21109MT, AA21109MB, AA21110CH, AA21110DB, AA21110RS (The main device part of function module No. is A027537AA)

Modification Contents Summary: This certificate is a technical modification to CNCVC1893-M1, which was issued on 2025-4-18; and modification to CNCVC1893, which was issued on 2024-6-26. Modification contents refer to the test report.

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Bottom Colours are indicated to show the factory locations for each reference and accessories in the table.

Factories	Address
LEGRAND Intelligent ELECTRICAL (HUIZHOU) CO, LTD	Bldg. B1-B3, East No.39 Hechang 6 th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA
LEGRAND Intelligent ELECTRICAL (HUIZHOU) CO, LTD NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD LEGRAND RAIS HASSAN SAADI Logistics Dubai	Bldg. B1-B3, East No.39 Hechang 6 th Rd, HZZK Hi-tech Industrial Development Zone, Huizhou 516001, Guangdong, CHINA A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. – NASHIK- 422113. MAHARASHTRA. INDIA Avenue du Parc Alata – 60550 Verneuil en Halatte – FRANCE Jebel Ali Free Zone, P.O. Box 7 Dubai – UNITED ARAB EMIRATES
LEGRAND France	128, Avenue du Marechal de Lattre de Tassigny 87045 LIMOGES Cedex FRANCE
NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PVT. LTD	A-2, MIDC AREA, MALEGAON VILLAGE, SINNAR, DIST. – NASHIK- 422113. MAHARASHTRA. INDIA
Legrand Electric Ltd	Unit 12 No.1 Industrial Estate Medomsley Road Consett, DH8 6SR, County Durham, UNITED KINGDOM

All the commercial references listed below may be supplemented with a prefix of type LG-, BT-, ...(to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...In this case, the products are technically the same.

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

CLASSIC references

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose				
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Pattern	Actuating	Module
A0275 14AA	AC211 09MW	AC211 09MT	AC211 09MB	AC211 09CH	AC211 09DB	AC211 09RS	20AX – 250V~	2	R	1
A0275 14AA	AC211 10MW	AC211 10MT	AC211 10MB	AC211 10CH	AC211 10DB	AC211 10RS	20AX – 250V~	2	R	1

ELITE references

	Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose				
Type reference	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Commercial ref	Rated values	Pattern	Actuating	Module
A0275 37AA	AA211 09MW	AA211 09MT	AA211 09MB				20AX – 250V~	2	R	1
A0275 37AA	AA211 10MW	AA211 10MT	AA211 10MB	AA211 10CH	AA211 10DB	AA211 10RS	20AX – 250V~	2	R	1

Blank

Commercial ref						Designation
Matt White	Matt Titanium	Matt Black	Champagne	Dark Bronze	Rose	
AC150MW	AC150MT	AC150MB	AC150CH	AC150DB	AC150RS	1 BLANK MODULE
AC153MW	AC153MT	AC153MB	AC153CH	AC153DB	AC153RS	2 BLANK MODULES

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Frame

Commercial ref	Designation
A1402	1G 1 AND 2M BRITISH STD FRAME
A1403	1G 1 AND 2M BS FRAME W EARTH
A1404	1G 3M HORIZOVERTICAL BS FRAME
A1408	2G 3M BS FRAME
A1409	2G 2 X 2M BS FRAME
A1417	6M BS FRAME
A1411	8M BS FRAME
A1406	4M IT/FR/SCH FRAME
A1407	6M IT/FR/SCH FRAME
A1400	1M PANEL MOUNTING SUPPORT
A1401	2M PANEL MOUNTING SUPPORT
A1405	3M IT/US FRAME
A1412	2M FR/B/SCH CLAW FRAME
A1413	1 & 2M FR/B/SCH SCREW FRAME
A1414	2X6M FR/B/SCH HOR SCREW FRAME
A1410	4"X4" FRAME
A1415	1&2M 2"X4" FRAME
A1416	2X3M 4"X4" FRAME

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Cover plates

Comm ercial ref									Designation
Matt White	Matt Titani um	Matt Blac k	Frost ed White	Frost ed Black	Dark Alumini um	Brushe d Stainle ss Steel	Night Blue	Solid Alumi nium	
Classic									
AC110 0MW	AC11 00MT	AC1 100 MB	AC11 00FW	AC11 00FB	AC110 0DA	AC110 0BS	AC1 100N B	AC11 00SA	1G 1M BS PLATE
AC110 1MW	AC11 01MT	AC1 101 MB	AC11 01FW	AC11 01FB	AC110 1DA	AC110 1BS	AC1 101N B	AC11 01SA	1M ITALIANUS PLATE
AC110 2MW	AC11 02MT	AC1 102 MB	AC11 02FW	AC11 02FB	AC110 2DA	AC110 2BS	AC1 102N B	AC11 02SA	1G 2M BS PLATE
AC110 3MW	AC11 03MT	AC1 103 MB	AC11 03FW	AC11 03FB	AC110 3DA	AC110 3BS	AC1 103N B	AC11 03SA	2M ITALIANUS PLATE
AC110 4MW	AC11 04MT	AC1 104 MB	AC11 04FW	AC11 04FB	AC110 4DA	AC110 4BS	AC1 104N B	AC11 04SA	1G 3M BS HORIZVERT PLATE
AC110 5MW	AC11 05MT	AC1 105 MB	AC11 05FW	AC11 05FB	AC110 5DA	AC110 5BS	AC1 105N B	AC11 05SA	3M BS PLATE FOR 2G BOX
AC110 7MW	AC11 07MT	AC1 107 MB	AC11 07FW	AC11 07FB	AC110 7DA	AC110 7BS	AC1 107N B	AC11 07SA	3M IT/US PLATE

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

AC110 8MW	AC11 08MT	AC1 108 MB	AC11 08FW	AC11 08FB	AC110 8DA	AC110 8BS	AC1 108N B	AC11 08SA	2 X 2M BS PLATE
AC111 0MW	AC11 10MT	AC1 110 MB	AC11 10FW	AC11 10FB	AC111 0DA	AC111 0BS	AC1 110N B	AC11 10SA	4M IT/FR/SCH PLATE
AC111 1MW	AC11 11MT	AC1 111 MB	AC11 11FW	AC11 11FB	AC111 1DA	AC111 1BS	AC1 111N B	AC11 11SA	6M IT/FR/SCH PLATE
AC111 8MW	AC11 18MT	AC1 118 MB	AC11 18FW	AC11 18FB	AC111 8DA	AC111 8BS	AC1 118N B	AC11 18SA	4X4 US PLATE FOR 2M
Elite									
			AA11 04FW	AA11 04FB	AA110 4DA	AA110 4BS	AA11 04NB	AA11 04SA	1G PLATE FOR 1M SWITCH
			AA11 05FW	AA11 05FB	AA110 5DA	AA110 5BS	AA11 05NB	AA11 05SA	1G PLATE FOR 2X1M SWITCHES
			AA11 09FW	AA11 09FB	AA110 9DA	AA110 9BS	AA11 09NB	AA11 09SA	2G PLATE 2M SWITCH +2M SWITCH
			AA11 08FW	AA11 08FB	AA110 8DA	AA110 8BS	AA11 08NB	AA11 08SA	2G PLATE FOR 3X1M SWITCHES
			AA11 12FW	AA11 12FB	AA111 2DA	AA111 2BS	AA11 12NB	AA11 12SA	2 X 4 PLATE FOR 3M

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Hybrid

			AB11 00FW	AB11 00FB	AB110 0DA	AB110 0BS	AB11 00N B	AB11 00SA	4M HYBRID PLATE 2M + 2M SWITCH
			AB12 01FW	AB12 01FB	AB120 1DA	AB120 1BS	AB12 01N B	AB12 01SA	6M HYBRID PLATE 3M + 2M SWITCH
			AB12 04FW	AB12 04FB	AB120 4DA	AB120 4BS	AB12 04N B	AB12 04SA	6M HYBRID PLATE 4M + 1M SWITCH
			AB12 00FW	AB12 00FB	AB120 0DA	AB120 0BS	AB12 00N B	AB12 00SA	6M HYBRID PLATE 3M + 2M DIMMER
			AB12 06FW	AB12 06FB	AB120 6DA	AB120 6BS	AB12 06N B	AB12 06SA	8M HYBRID PLATE 5M + 2M DIMMER

Cover plates

Commercial ref

Cha mpag ne	Drak Bron ze	Rose	Brus hed Bron ze	Brus hed Antiq ue Bras s	Solid Dark Bron ze	Solid Sand	Solid Blac k	Solid Rose	Solid Cham pange	Designation
-------------------	--------------------	------	---------------------------	---	-----------------------------	---------------	--------------------	---------------	------------------------	-------------

Classic

AC11 00CH	AC1 100D B	AC1 100R S	AC1 100B B	AC1 100A B	AC1 100S Z	AC1 100S D	AC1 100S B	AC1 100S R	AC110 0SC	1G 1M BS PLATE
AC11 02CH	AC1 102D B	AC1 102R S	AC1 102B B	AC1 102A B	AC1 102S Z	AC1 102S D	AC1 102S B	AC1 102S R	AC110 2SC	1G 2M BS PLATE
AC11 04CH	AC1 104D B	AC1 104R S	AC1 104B B	AC1 104A B	AC1 104S Z	AC1 104S D	AC1 104S B	AC1 104S R	AC110 4SC	1G 3M BS HORIZ/VERT PLATE

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

AC1 105 CH	AC1 105D B	AC1 105R S	AC1 105B B	AC1 105A B	AC1 105S Z	AC1 105S D	AC1 105S B	AC1 105S R	AC110 5SC	3M BS PLATE FOR 2G BOX
AC1 108 CH	AC1 108D B	AC1 108R S	AC1 108B B	AC1 108A B	AC1 108S Z	AC1 108S D	AC1 108S B	AC1 108S R	AC110 8SC	2 X 2M BS PLATE
Elite										
			AA1 104B B	AA1 104A B	AA1 104S Z	AA11 04S D	AA1 104S B	AA11 04S R	AA110 4SC	1G PLATE FOR 1M SWITCH
			AA1 105B B	AA1 105A B	AA1 105S Z	AA11 05S D	AA1 105S B	AA11 05S R	AA110 5SC	1G PLATE FOR 2X1M SWITCHES
			AA1 108B B	AA1 108A B	AA1 108S Z	AA11 08S D	AA1 108S B	AA11 08S R	AA110 8SC	2G PLATE FOR 3X1M SWITCHES
			AA1 109B B	AA1 109A B	AA1 109S Z	AA11 09S D	AA1 109S B	AA11 09S R	AA110 9SC	2G PLATE 4 x 1M SWITCH
			AA1 118B B	AA1 118A B	AA1 118S Z	AA11 18S D	AA1 118S B	AA11 18S R	AA111 8SC	2 X 4 PLATE FOR 3M SLENDER

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China

Tel: +86-20-32293691

Mail: intl@cvc.org.cn

Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Hybrid

			AB1 100B B	AB1 100A B	AB1 100S Z	AB11 00S D	AB1 100S B	AB11 00S R	AB110 0SC	4M HYBRID PLATE 2M +2M SWITCH
			AB1 200B B	AB1 200A B	AB1 200S Z	AB12 00S D	AB1 200S B	AB12 00S R	AB120 0SC	6M HYBRID PLATE 3M+2M DIMMER
			AB1 201B B	AB1 201A B	AB1 201S Z	AB12 01S D	AB1 201S B	AB12 01S R	AB120 1SC	6M HYBRID PLATE 3M+2M SWITCH
			AB1 204B B	AB1 204A B	AB1 204S Z	AB12 04S D	AB1 204S B	AB12 04S R	AB120 4SC	6M HYBRID PLATE 4M+1M SWITCH
			AB1 206B B	AB1 206A B	AB1 206S Z	AB12 06S D	AB1 206S B	AB12 06S R	AB120 6SC	8M HYBRID PLATE 5M+2M DIMMER

Cover plates

Commercial ref			Designation
Brushed stainless steel	Polished stainless steel	Glossy gold	
833091	833291	833491	1 gang front plate for 1 module
833092	833292	833492	1 gang front plate for 2 module
833093	833293	833493	2 gang front plate for 3 module
833094	833294	833494	2 gang front plate for 2X2 module

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Cover plates + Frame

Commercial ref									Designation
Matt White	Matt Titanium	Matt Black	Frosted White	Frosted Black	Dark Aluminium	Brushed Stainless Steel	Night Blue	Solid Aluminium	
Classic									
AC1204MW	AC1204MT	AC1204MB	AC1204FW	AC1204FB	AC1204DA	AC1204BS	AC1204NB	AC1204SA	6M BS PLATE+FRAME
AC1209MW	AC1209MT	AC1209MB	AC1209FW	AC1209FB	AC1209DA	AC1209BS	AC1209NB	AC1209SA	2 X 6M BS PLATE+FRAME
AC1206MW	AC1206MT	AC1206MB	AC1206FW	AC1206FB	AC1206DA	AC1206BS	AC1206NB	AC1206SA	8M PLATE+FRAME
			AB1208FW	AB1208FB	AB1208DA	AB1208BS	AB1208NB	AB1208SA	4M HYBRID PLATE+FRAME 2M + 2M SWITCH

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____

Cover plates + Frame

Commercial ref										Designati on
Cha mpa gne	Dra k Bro nze	Ros e	Bru she d Bro nze	Brush ed Antiqu e Brass	Solid Dark Bronz e	Solid Sand	Solid Blac k	Solid Rose	Solid Champange	
Classic										
AC 120 4C H	AC1 204 DB	AC1 204 RS	AC1 204 BB	AC12 04AB	AC12 04SZ	AC1 204S D	AC1 204 SB	AC12 04SR	AC1204SC	6M BS PLATE+F RAME
AC 120 9C H	AC1 209 DB	AC1 209 RS	AC1 209 BB	AC12 09AB	AC12 09SZ	AC1 209S D	AC1 209 SB	AC12 09SR	AC1209SC	2 X 6M BS PLATE+F RAME
AC 120 6C H	AC1 206 DB	AC1 206 RS	AC1 206 BB	AC12 06AB	AC12 06SZ	AC1 206S D	AC1 206 SB	AC12 06SR	AC1206SC	8M PLATE+F RAME

Cover plates + Mounting Box

Commercial ref	Color	Designation
733891	Metalclad	1 gang carrier plate with box for 1 module
733892	Metalclad	1 gang carrier plate with box for 2 module
733893	Metalclad	2 gang carrier plate with box for 3 module
733894	Metalclad	2 gang carrier plate with box for 2X2 module

Mounting Box

Commercial ref	Color	Designation
736400	Metalclad	1 gang surface mounting box
736401	Metalclad	2 gang surface mounting box

CVC Certification & Testing Co., Ltd.

No. 3, Tiantaiyi Road, High-tech Industrial Development Zone,
Guangzhou, 510663, P. R. China
Tel: +86-20-32293691
Mail: intl@cvc.org.cn
Website: www.cvc.org.cn



Date: 2026-03-10

Signature: _____