



Ref. Certif. No.

SE-104454

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Rotary dimmer (Rotary dimmer RLC + LED)

Name and address of the applicant

Legrand Intelligent Electrical (Huizhou) Co., Ltd.
Bldg. B1-B3, East No.39 Hechang 6th Rd., HZZK Hi-tech Industrial Development Zone, Huizhou, Guangdong, China

Name and address of the manufacturer

Same as applicant

Name and address of the factory

Note: When more than one factory, please report on page 2

Same as applicant

Ratings and principal characteristics

See page 2

Trademark (if any)



Customer's Testing Facility (CTF) Stage used

-

Model / Type Ref.

See page 2

Additional information (if necessary may also be reported on page 2)

-

A sample of the product was tested and found to be in conformity with

IEC 60669-1:1998+A1+A2, IEC 60669-2-1:2002+A1+A2

As shown in the Test Report Ref. No. which forms part of this Certificate

210208001GZU-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Signature: *Quan Li*

Date: 06 April, 2021

Quan Li



Ref. Certif. No.

SE-104454

Ratings and principal characteristics

100-240 V; 50/60 Hz; Without contact gap; Integral type; IP20;

1) At 100-200 V rating voltage;

5-150 W for incandescent lamp;

5-150 VA for fluorescent Lamp; electronic step-down converter for extra low-voltage incandescent lamps (for example, halogen); Iron core transformer for extra low-voltage incandescent lamps (for example, halogen);

5-37 VA for self-ballasted fluorescent compact lamp (CFL) or selfballast LED lamp;

2) At 200-240 V rating voltage;

5-300 W for incandescent lamp;

5-300 VA for fluorescent Lamp; electronic step-down converter for extra low-voltage incandescent lamps (for example, halogen); Iron core transformer for extra low-voltage incandescent lamps (for example, halogen);

5-75 VA for self-ballasted fluorescent compact lamp (CFL) or selfballast LED lamp

Model / Type Ref.

CXM17; AG05476AA; AG06488AA; 617635; 617735; 617835

282419; 282419-C1; 282419-C2; 282419-C3; 282419-C; 833151, 832151, 731151; 832141; 832351; 832551; 833351; 833551; 281086MW; 281086MG; 281086MB; 281086DS; 281086CH; 281086DB; 281086BA; 281086BB; 281086BC

Date: 06 April, 2021

Signature: 