

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Dimmer switch
Name and address of the applicant	LEGRAND France 128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex France
Name and address of the manufacturer	LEGRAND France 128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex France
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	See additional page(s) for the listing of 3 factories
Ratings and principal characteristics	110 V ~ 75 W max or 230 V ~ 125 W max 0,68 A max 50/60 Hz IP 20
Trademark / Brand (if any)	BTICINO
Customer's Testing Facility (CTF) Stage used	N/A
Model / Type Ref.	CXM22 For detailed Type Reference List see Additional page(s).
Additional information (if necessary may also be reported on page 2)	See additional page(s) for further Additional information. For accessories (cover plates, covers and frames) see CB Test Report.
A sample of the product was tested and found to be in conformity with	IEC 60669-2-1:2021 IEC 60669-1:2017 See Test Report for National Differences
As shown in the Test Report Ref. No. which forms part of this Certificate	HU24F679 001

This CB Test Certificate is issued by the National Certification Body

TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2024-11-22

Signature:



Tötös Tamás László

Additional information :

Type Reference List

Range	Reference	Designation - PRO/DIY - Description
CLASSIA	RW4419M2	DIMMER 2WIRES 125W - PRO - WCP
	RA4419M2	DIMMER 2WIRES 125W - PRO - WCP
	RG4419M2	DIMMER 2WIRES 125W - PRO - WCP
LIVING NOW	K4419M2	DIMMER W/O NEUTRAL - PRO - 2M MO
LIVING LIGHT	N4419M2	UNIVERSAL DIMMER WHITE - PRO - WCP
	L4419M2	UNIVERSAL DIMMER ANTHRACITE - PRO - WCP
	NT4419M2	UNIVERSAL DIMMER TECH - PRO - WCP
MATIX GO	JW4419M2	DIMMER 2 WIRES 2M WHITE - PRO - WCP
	JG4419M2	DIMMER 2 WIRES 2M GREY - PRO - WCP
	JB4419M2	DIMMER 2 WIRES 2M BLACK - PRO - WCP

CP means Complete Product WCP means Without Cover Plate
 MO means Mechanism Only WFCP means Without Frame/Cover Plate
 FwC means FwC WCCP means Without Cover/Cover Plate

All the commercial references listed above may be supplemented with a prefix of type "BT-" and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...



Date: 2024-11-22

Signature:

as on page 1

Factories :

1. LEGRAND France
128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex
France

2. BTICINO S.p.A.
Via Luciano Manare 4 22036 Erba
Italy

3. BTICINO S.p.A.
Viale Borri 21100 Varese
Italy