

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

| | |
|---|--|
| Product | Dimmer switch |
| Name and address of the applicant | LEGRAND France 128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex France |
| Name and address of the manufacturer | LEGRAND France 128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex France |
| Name and address of the factory <i>Note: When more than one factory, please report on page 2</i> | See additional page(s) for the listing of 6 factories |
| Ratings and principal characteristics | 110 V ~ 75 W max or 240 V ~ 150 W max 0,68 A max 50/60 Hz IP 20 |
| Trademark / Brand (if any) | LEGRAND |
| Customer's Testing Facility (CTF) Stage used | N/A |
| Model / Type Ref. | CXM23 For detailed Type Reference List see Additional page(s). |
| Additional information (if necessary may also be reported on page 2) | See additional page(s) for further Additional information. For accessories (cover plates, covers, boxes and frames) see CB Test Report. |
| A sample of the product was tested and found to be in conformity with | IEC 60669-2-1:2021 IEC 60669-1:2017 See Test Report for National Differences |
| As shown in the Test Report Ref. No. which forms part of this Certificate | HU247UM3 001 |

This CB Test Certificate is issued by the National Certification Body

TÜV Rheinland InterCert Kft., MEEI Division
H-1143 Budapest, Gizella út 51-57., Hungary
Web: www.tuv.com

Date: 2024-11-22

Signature:



Tötös Tamás László

Additional information :

Type Reference List

| Range | Reference | Designation |
|-------------------|------------|---------------------------------|
| ARTEOR | 5 741 88A | DIMMER 3 WIRES 150W ALU |
| | 5 741 89A | DIMMER 3 WIRES 150W WHITE |
| | 5 741 90A | DIMMER 3 WIRES 150W MAGNESIUM |
| | 5 741 91A | DIMMER 3 WIRES 150W CHAMPAGNE |
| CELIANE | 0 670 86A | DIMMER 3 WIRES 150W |
| CELIANE | CM0064 | DIMMER 3 WIRES 150W |
| MOSAIC | 0 784 08A | DIMMER 3WIRES 150W MOSAIC WHITE |
| | 0 792 08A | DIMMER 3WIRES 150W MOSAIC ALU |
| | 0 791 08LA | DIMMER 3WIRES 150W MOSAIC BLACK |
| DOOXIE | 6 000 66A | DIMMER 3 WIRES 150W WHITE |
| | 6 001 66A | DIMMER 3 WIRES 150W ALU |
| | 6 002 66A | DIMMER 3 WIRES 150W BLACK |
| NILOE STEP | 8 639 80A | DIMMER 3 WIRES 150W WHITE |
| | 8 639 81A | DIMMER 3 WIRES 150W ALU |
| | 8 639 82A | DIMMER 3 WIRES 150W GREY |
| | 8 639 83A | DIMMER 3 WIRES 150W BLACK |
| | 8 640 40A | DIMMER 3 WIRES 150W |
| VALENA LIFE | 7 519 91A | DIMMER 3 WIRES 150W WHITE |
| | 7 519 92A | DIMMER 3 WIRES 150W IVORY |
| | 7 519 93A | DIMMER 3 WIRES 150W ALU |
| VALENA NEXT | 7 412 90A | DIMMER 3 WIRES 150W WHITE |
| | 7 413 90A | DIMMER 3 WIRES 150W ALU |
| | 7 414 90A | DIMMER 3 WIRES 150W BLACK |
| | 7 415 90A | DIMMER 3 WIRES 150W WHITE |
| | 7 416 90A | DIMMER 3 WIRES 150W ALU |
| | 7 417 90A | DIMMER 3 WIRES 150W BLACK |
| VALENA INMATIC | 7 519 90A | DIMMER 3 WIRES 150W |

< For further details see CB Test Report. >



Date: 2024-11-22

Signature:

as on page 1

Factories :

1. LEGRAND France
128 Avenue du Maréchal de Lattre de Tassigny 87045 Limoges Cedex
France
2. LEGRAND Magyarország Villamossági Rendszerek ZRt.
Ipartelepí út 14. 6600 Szentés
Hungary
3. LEGRAND Elektrik Sanayi A.S.
Gebze Organize Sanayi Bolgesi, Ihsan Dede Caddesi 112 41480 Kocaeli
Türkiye
4. CARDONAPLAST SAU
Pol. Ind. la Cort C/Forn 4-5 08261 Cardona
Spain
5. NOVATEUR ELECTRICAL & DIGITAL SYSTEMS PRIVATE LTD
A-2, SINNAR - MALEGAON VILLAGE MIDC, NASHIK PUNE ROAD, NASHIK district,
MAHARASHTRA. 422113
India
6. NP Hungária Kft.
Ipari park 07/54 hrsz. 5440 Kunszentmárton
Hungary