

LICENCE

No. 19708 replaces No.12513, 12514

Issued to:
Applicant:
Legrand Group Belgium N.V.
Kouterveldstraat 9, Ind. Zone
1831 DIEGEM
Belgium

Licensee:

Legrand Group Belgium N.V. Kouterveldstraat 9, Ind. Zone 1831 DIEGEM Belgium



Trade name(s) : LEGRAND

Type(s)/model(s) : Appareillage Saillie, Série Oteo (see appendix)

The product and any acceptable variation thereto is specified in the annex to this licence and the documents therein referred to.

SGS CEBEC hereby declares that the above-mentioned product has been certified on the basis of:

- a type test according to the standard specified in annex

an inspection of the production location

- a certification agreement with the number 178

SGS CEBEC hereby grants the right to use the CEBEC certification mark. The CEBEC certification mark may be applied to the product as specified in this licence for the duration of the CEBEC certification agreement and under the conditions of the CEBEC certification agreement.

This licence is issued on: 15/10/2015

ir. C. Lana, Certification Manager

© Only integral publication of this certificate, including the annex, is allowed
This certificate is only valid combined with the publication on the following web address: www.sgs.com/ee







SGS Belgium NV-Division SGS CEBEC Business Riverside Park Bld Internationaleiaan 55 Build. D B-1070 Brussels Tel.+32(0)2 556 00 20 Fax.+32(0)2 556 00 36 This certificate is issued by the company under its General Conditions for Certification Services accessible at http://www.sgs.com/terms_and_conditions.htm. Attention is drawn to the limitations of liability defined therein and in the Test Report herein mentioned which findings are reflected in this Certificate. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.



SPECIFICATION OF THE CERTIFIED PRODUCT

Product data

Product : socket-outlets (2-pole)

Trade name(s) : LEGRAND

Type(s)/Model(s) : Appareillage Saillie, Série Oteo (see appendix)

rated current (In) : 16 A

rated voltage (Un) : 250 Vac

standard sheet : I & V

earthing : with & without earthing system

method of connection : rewirable

type of terminals : screw type

protection against electric shock : increased

method of installation : type A

method of mounting : surface type

existence of shutters : with shutters

certification mark : complies with the requirements

markings : are shown on the body

Additional information

See Appendix

TESTS

Test requirements

NBN C 61-112-1 based on IEC 60884-1:2002 + A1:2006

Test results

The test results are laid down in certification file ref.621341/01



Remarks

This certificate is based on certificates ref. CBs FR 592714E, FR 2625/1/17441 & FR 640022 and test reports ref. 60025795-520766A, 60025795-520766B, 17441040/6 and 120102-640025

Conclusion

The examination proved that all test requirements were met.

Checked by, project leader

Zanutto Luigi - 15/10/2015

Department Manager, Product Certification

Certification Manager

ANNEX TO CEBEC LICENCE No. 19708 Page 3 of 3



FACTORY LOCATION(S)

Legrand SNC 128, avenue du Maréchal de Lattre de Tassigny 87045 LIMOGES CEDEX France

<u>Products references Series Oteo.</u>

Socket-outlets

Reference		Ratings	Function
Complete	Modular		
86024	86124	16A/250V~	2P
86028	86128	16A/250V~	2P + E
-	86178	16A/250V~	2 x 2P + E

Surface mounting frames

Reference	Description	
86091	1 gang	
86092	2 gang	
86093	3 gang	