



Ref. Certif. No.

SE-108639

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Three and Four poles Moulded Case Circuit Breaker

Name and address of the applicant

LEGRAND FRANCE
128 AVENUE DU MARÉCHAL DE LATTRE DE TASSIGNY
FR-87045 LIMOGES CEDEX, FRANCE

Name and address of the manufacturer

BTICINO SpA - LEGRAND GROUP
VIALE BORRI 231, VARESE 21100 ITALY

Name and address of the factory
Note: When more than one factory, please report on page 2

See page 2

Ratings and principal characteristics

$U_e = 240-690\text{Vac}$ (50.0-60.0Hz), $I_n = 160\text{A}$
 $U_i = 800\text{V}$, $U_{imp} = 8,00\text{ kV}$, Pattern No. 3 and 4

Trademark (if any)

Legrand

Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

DPX³ 160 HP

Additional information (if necessary may also be reported on page 2)

See page 2

A sample of the product was tested and found to be in conformity with

IEC 60947-2:2016+A1

As shown in the Test Report Ref. No. which forms part of this Certificate

2026732STO-001

This CB Test Certificate is issued by the National Certification Body

Intertek Semko AB
Torshamnsgatan 43
Box 1103
SE-164 22 Kista, Sweden

Signature: *Quan Li*

Date: 20 July, 2022

Quan Li

Factories

Bticino S.p.a. – Via dei Folzoni, 5 – 24052, Azzano, San Paolo, Bergamo (Italy)

Legrand Low Voltage Electrical (Wuxi) CO., LTD, No.88, Ximei Road, New Zone, Wuxi, Jiangsu Province (P.R. China)

Novateur Electrical & Digital Systems Private Limited, D-4, MIDC Area, Jalgaon-425003 Maharashtra

OA0 KOHTAKTOP - 12 Karl Marx str. Ulyanovsk 432001- Russian Federation

Additional information

DPX³ 160 HP (Thermal-magnetic release)

Common characteristics:

Voltage ratings U_e=240-690V (50-60Hz)

Rated current I_n=160A

Current setting Adjustable (0.8-1)xI_n–Overload

Fixed 10xI_n –Short Circuit

DPX³ 160 HP (Traffic Red label)

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
240	154	70,0	70,0	N/A
415	75,6	36,0	36,0	N/A
500	24,4	12,0	12,0	N/A
690	7,7	5,00	5,00	N/A

DPX³ 160 HP (Blue Lilac label)

U _e (V)	I _{cm} (kA)	I _{cu} (kA)	I _{cs} (kA)	I _{cw} (kA)
240	198	90,0	90,0	N/A
415	105	50,0	50,0	N/A
500	32,0	16,0	16,0	N/A
690	9,20	6,00	6,00	N/A

Date: 20 July, 2022

Signature: *Anam Li*