

LCIE N° : NF012_4571/M1

Titulaire :
License Holder:

LEGRAND FRANCE
128 AVENUE DU MARECHAL DE LATTRE DE TASSIGNY
87045 LIMOGES CEDEX
FRANCE

Site de fabrication :
Factory:

0002AP
1456AP

Produit :
Product:

**Interrupteur pour installations électriques fixes
domestiques et analogues**
Switch for household and similar fixed electrical installations

Marque commerciale (s'il y a lieu) :
Trade mark (if any):



Modèle, type, référence :
Model, type, reference:

Series / Gamme : **CELIANE**
Voir Annexe / See Annex

Caractéristiques principales :
Main characteristics:

Voir Annexe / See Annex

Informations complémentaires :
Additional information:

/

Le produit est conforme à :
The product is in conformity with:

EN 60669-1:2018

Documents pris en compte :
Relevant documents:

TR n° 23848234-805357 Version 01
CBTC N° HU-005022-M1 / TR N° HU24CENE 002

Annule et remplace (s'il y a lieu) :
Cancels and replaces (if necessary):

La licence / *License* NF012_4571 du/of 16/12/2024. Ajout de site(s) de fabrication/addition of factory(ies), Ajout de référence(s) produit/addition of product references


En vertu de la présente décision notifiée par le LCIE organisme mandaté, AFNOR Certification accorde le droit d'usage de la Marque NF à la société qui en est titulaire pour les produits visés ci-dessus, dans les conditions définies par les règles générales de la Marque NF et par les règles de certification NF, pour autant que les contrôles réguliers de la fabrication et les vérifications par tierce partie soient satisfaisants.

On the strength of the present decision notified by LCIE mandated certification body, AFNOR Certification grants the right to use the NF Mark to the licence holder for the above mentioned products, within the frame of the general rules of the NF Mark and of the NF certification rules, as far as the regular checking and third party verifications of the production are satisfactory.

Fontenay-aux-Roses, 07/02/2025

Date de fin de validité / *Expiry date* :

La validité de la présente licence cesse dès l'annulation de l'une des normes sur lesquelles elle est fondée.
The present license is valid until the cancellation of one of the standards on which it is based.


Julien GAUTHIER
Responsable Certification/Certification Officer

LABORATOIRE CENTRAL DES
INDUSTRIES ELECTRIQUES
S.A.S au capital de 15.745.984 €
RCS Nanterre B 408 363 174
33 avenue du Général Leclerc
F - 92266 FONTENAY AUX ROSES

RÉFÉRENCES - CARACTÉRISTIQUES PRINCIPALES
REFERENCES - MAIN CHARACTERISTICS

Type Ref.	Ref. Mechanism only	Ref. Blanc White	Ref. Titane Titanium	Réf. Noir Black	PRO / DIY	Pattern	Rated current Rated voltage	Method of actuating	Pilot light	Specificity
Without	CM0001	CC0001	CD0001	CE0001	PRO	6	10AX 250V~	Rocker	No	Sans plaque Without cover plate
		CF0001			PRO	6	10AX 250V~	Rocker	No	Sans support/plaque Without cover plate
		CC1001	CD1001	CE1001	PRO	6	10AX 250V~	Rocker	Locator	Sans plaque Without cover plate
		CG0001	CH0001		DIY	6	10AX 250V~	Rocker	No	Produit complet Complete product
		CG1001	CH1001		DIY	6	10AX 250V~	Rocker	Locator	Produit complet Complete product
		CX0001	CY0001	CZ0001	DIY	6	10AX 250V~	Rocker	No	Sans plaque Without cover plate
		CL4001	CL7001		DIY	6	10AX 250V~	Rocker	No	Sans plaque Without cover plate
		CX1001	CY1001	CZ1001	DIY	6	10AX 250V~	Rocker	Locator	Sans plaque Without cover plate
		CX7001	CY7001	CZ7001	DIY	6	10AX 250V~	Rocker	Indicator	Sans plaque Without cover plate
		CC2001	CD2001	CE2001	PRO	2x6	10AX 250V~	Rocker	No	Sans plaque Without cover plate
		CF2001			PRO	2x6	10AX 250V~	Rocker	No	Sans support/plaque Without frame/cover plate
		CG2001	CH2001		DIY	2x6	10AX 250V~	Rocker	No	Produit complet Complete product
		CX2001	CY2001	CZ2001	DIY	2x6	10AX 250V~	Rocker	No	Sans plaque Without cover plate
		CX3001	CY3001	CZ3001	DIY	2x6	10AX 250V~	Rocker	Locator	Sans plaque Without cover plate
		CG3001	CH3001		DIY	2x6	10AX 250V~	Rocker	Locator	Produit complet Complete product

Type Ref.	Ref. Mecanism only	Ref. Blanc White	Ref. Titane Titanium	Ref. Noir Black	PRO / DIY	Pattern	Rated current Rated voltage	Method of actuating	Pilot light	Specificity
		CC4001	CD4001	CE4001	PRO	2x6	10AX 250V~	Rocker	Indicator	Sans plaque Without cover plate
		CX4001	CY4001	CZ4001	DIY	2x6	10AX 250V~	Rocker	Indicator	Sans plaque Without cover plate
		CG8001			DIY	6	10AX/250 V~	Rocker	No	Produit complet Etanche Waterproof Complete product
Without	CM0031	CC0031	CD0031	CE0031	PRO	6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
		CC1031	CD1031	CE1031	PRO	6	6A 250V~	Momentary Rocker	Locator	Sans plaque Without cover plate
		CC5031	CD5031	CE5031	PRO	6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
		CF0031			PRO	6	6A 250V~	Momentary Rocker	No	Sans support/plaque Without frame/cover plate
		CG0031	CH0031	CJ0031	DIY	6	6A 250V~	Momentary Rocker	No	Produit complet Complete product
		CX0031	CY0031	CZ0031	DIY	6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
		CX1031	CY1031	CZ1031	DIY	6	6A 250V~	Momentary Rocker	Locator	Sans plaque Without cover plate
		CC6031	CD6031	CE6031	PRO	6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
		CX6031	CY6031	CZ6031	DIY	6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
		CX2031	CY2031	CZ2031	DIY	2x6	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
Without	Without	CC2031	CD2031	CE2031	PRO	6+6	10AX 250V~ 6A 250V~	Rocker + Momentary rocker	No	Sans plaque Without cover plate
		CX0037	CY0037	CZ0037	DIY	6+6	10AX 250V~ 6A 250V~	Rocker + Momentary rocker	No	Sans plaque Without cover plate
Without	CM0033				PRO	1	6A 250V~	Momentary Rocker	No	Mécanisme seul Mecanism only

Type Ref.	Ref. Mecanism only	Ref. Blanc White	Ref. Titane Titanium	Réf. Noir Black	PRO / DIY	Pattern	Rated current Rated voltage	Method of actuating	Pilot light	Specificity
Without	CM0002				PRO	1	10AX 250V~	Rocker	No	Sans doigt/plaque Without rocker/cover plate
Without	CM0032				PRO	1	6A 250V~	Momentary Rocker	No	Mécanisme seul Mecanism only Without cover plate
CO26P	CM0034				PRO	6	6A 250V~	Momentary Cord- Operated	No	Mécanisme seul Mecanism only Without cover plate
RB6	CM0043	CC0043	CD0043	CE0043	PRO	4	6AX 250V~	Rocker	No	Sans plaque Without cover plate
		CX0043	CY0043	CZ0043	PRO	4	6AX 250V~	Rocker	No	Sans plaque Without cover plate
RB6P	CM0044	CC0044	CD0044	CE0044	PRO	5	6A 250V~	Momentary Rocker	No	Sans plaque Without cover plate
RB4P	CM0045				PRO	4	6A 250V~	Momentary Rocker	No	Mécanisme seul Mecanism only
A028961AA	CM0005				PRO	7	10AX 250V~	Rocker	No	Mécanisme seul Mecanism only Without cover plate
A028963AA	CM0020				PRO	2	16AX 250V~	Rocker	No	Mécanisme seul Mecanism only Without cover plate

"All the commercial references listed above may be supplemented with a prefix of type LG-, BT-, ... (to indicate the brand) and/or suffix of type 0, 1, 2, 3, 4, FI, EX, ...

In this case, the products are technically the same."

"Toutes les références commerciales énumérées ci-dessus peuvent être complétées par un préfixe du type LG-, BT-, ... (pour indiquer la marque) et/ou un suffixe du type 0, 1, 2, 3, 4, FI, EX, ...

Dans ce cas, les produits sont techniquement les mêmes".

Classification

Function / Patern number	See Table
Contact opening (gap)	Normal-gap
Degree of protection (IP)	IP20, IP44 with specific accessoires
Level of shock resistance (IK)	IK02
Method of actuating	See Table
Method of mounting	Flush type / Surface type with box for surface mounting
Method of installation	Design A
Type of terminals	Screw type (rigid and flexible)
Rated current (A)	6A, 10AX - See Table
Rated voltage (V)	250V~

Accessoires / Accessories

Voyants / Pilot light

References	Designation	Characteristics	Specific for
CM0220	Voyant lumineux Locator LED	230V~ 0,15mA	
CM0221	Voyant témoin Indicator LED	230V~ 3mA	
CM0222	Voyant témoin phase distribuée Distributed phase indicator	230V~ 3mA	
CM0223	Voyant lumineux Locator LED	12-24-48V	
CM0224	Voyant lumineux Blanc White Locator LED	230V~ 0,15mA	CM0005 CM0020
CM0225	Voyant témoin Bleu Blue Indicator LED	230V~ 0,6mA	CM0005 CM0020

References	Designation	Specificity
0 802 50	étroit 1/2 poste 1 module	A vis With Screws
0 802 51	1 poste 2 modules	A vis With Screws
0 802 52	2 postes 4 modules	A vis With Screws
0 802 53	3 postes 6 modules	A vis With Screws
0 802 54	4 postes 8 modules	A vis With Screws
0 802 59	3 modules	A vis With Screws
0 802 61	1 poste 2 modules	A griffes With claws
0 802 64	2x2 postes 2x4/5 modules	A vis With Screws
0 802 66	2x3 postes 2X6/8 modules	A vis With Screws
0 802 68	métallique métallic 2X10 modules	A vis With Screws

Doigt de commande / Rocker

Designation	References Blanc/White	References Ivoire/Ivory	References Noir/Black	References Titane/Titanium
Doigt simple Single rocker	CB0001	CI0001	CN0001	CT0001
Doigt simple à voyant Single indicator rocker	CB0007	CI0007	CN0007	CT0007
Doigt variateur ventilation Ventilation dimmer rocker	CB0015		CN0015	CT0015
Doigt bipolaire Double pole rocker	CB0020	CI0020	CN0020	CT0020
Doigt commande général General command rocker	CB0021	CI0021	CN0021	CT0021
Doigt commande entrée/bureau Desk/Entrance rocker	CB0022		CN0022	CT0022
Doigt commande chevets Bed light rocker	CB0023		CN0023	CT0023
Doigt "Ne pas déranger" "Do not disturb" rocker	CB0024	CI0024	CN0024	CT0024
Doigt volets chambre hôtel Hotel room shutters rocker	CB0025	CI0025	CN0025	CT0025
Doigt stores chambre hôtel Hotel room roller blind rocker	CB0026	CI0026	CN0026	CT0026
Doigt compact 5 commandes 5 compact command rocker	CB0029		CN0029	CT0029
Doigt volets roulants/stores Roller shutter/blind rocker	CB0043	CI0043	CN0043	CT0043
Doigt simple à voyant Single light rocker	CB1001	CI1001	CN1001	CT1001
Doigt bipolaire à voyant Double pole light rocker	CB1020	CI1020	CN1020	CT1020
Doigt double Double commande rocker	CB2001	CI2001	CN2001	CT2001
Doigt double témoin Indicator double commande rocker	CB2007	CI2007	CN2007	CT2007
Doigt double à voyant Double commande indicator rocker	CB3001	CI3001	CN3001	CT3001
Doigt double "Ne pas déranger" "Do not disturb" double rocker	CB3033		CN3033	CT3033
Doigt simple porte-étiquette Label holder single rocker	CB5001	CI5001	CN5001	CT5001
Doigt commande VMC Mechanical ventilation command rocker	CB6001	CI6001	CN6001	CT6001
Doigt simple IP44 IP44 single rocker	CB8001	CI8001		
Doigt double IP44 IP44 double rocker	CB4001	CI4001		
Doigt simple pour permutateur Rocker for Intermediate switch	CB0005		CN0005	CT0005
Doigt simple à voyant pour permutateur Luminous rocker for Intermediate switch	CB1005		CN1005	CT1005



Plaques / Cover Plate - Entraxe 71mm - DECO

Nbr de postes / modules Number of gang / module	BLANC EMAILLE ENAMELLED WHITE		IVOIRE IVORY		BLEU DE FOUR BLEU DE FOUR		JAUNE SAFFRAN SAFFRON YELLOW		VERT CELADON CELADON GREEN	
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 module	CP0013		CP0213							
1 poste / 1 gang	CP0001	CP0021	CP0201	-	CP0301	CP0321	CP0401	CP0421	CP0501	CP0521
2 postes / 2 gang	CP0002	CP0022	CP0202	-	CP0302	CP0322	CP0402	CP0422	CP0502	CP0522
3 postes / 3 gang	CP0003	CP0023	CP0203	-	CP0303	CP0323	CP0403	CP0423	CP0503	CP0523
4 postes / 4 gang	CP0004	CP0024	CP0204	-	CP0304	CP0324	CP0404	CP0424	CP0504	CP0524
2 postes - 4/5 modules	CP0008				CP0308		CP0408		CP0508	
2x2 postes / 2x2 gang	CP0009		CP0209							
2x3 postes / 2x3 gang	CP0010		CP0210							

Plaques / Cover Plate - Entraxe 57mm - DECO

BLANC EMAILLE ENAMELLED WHITE	BLEU DE FOUR BLEU DE FOUR	JAUNE SAFFRAN SAFFRON YELLOW	VERT CELADON CELADON GREEN
PRO	PRO	PRO	PRO
CP0006	CP0306	CP0406	CP0506
CP0007	CP0307	CP0407	CP0507

Plaques / Cover Plate - Entraxe 71mm - DECO MAT

Nbr de postes / modules Number of gang / module	NOIR MAT MAT BLACK		BLEU ORAGE STORM BLUE		GRIS CENDRE ASH GREY		BLANC AMANDE ALMOND WHITE	
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 module	CP0113							
1 poste / 1 gang	CP0101	CP0121	CP0901	CP0921	CP1001	CP1021	CP1101	
2 postes / 2 gang	CP0102	CP0122	CP0902	CP0922	CP1002	CP1022	CP1102	
3 postes / 3 gang	CP0103	CP0123	CP0903	CP0923	CP1003	CP1023	CP1103	
4 postes / 4 gang	CP0104	CP0124	CP0904	CP0924	CP1004	CP1024	CP1104	
2 postes - 4/5 modules	CP0108		CP0908		CP1008		CP1108	
2x2 postes / 2x2 gang	CP0109							
2x3 postes / 2x3 gang	CP0110							

Plaques / Cover Plate - Entraxe 57mm - DECO MAT

Nbr de postes / modules Number of gang / module	NOIR MAT MAT BLACK	BLEU ORAGE STORM BLUE	GRIS CENDRE ASH GREY	BLANC AMANDE ALMOND WHITE
	PRO	PRO	PRO	PRO
2 postes / 2 gang	CP0106	CP0906	CP1006	CP1106
3 postes / 3 gang	CP0107	CP0907	CP1007	CP1107

Annexe de la licence / Annex of license NF012_4571/M1



Plaques / Cover Plate - Entraxe 71mm - GRAPHIQUE

Nbr de postes / modules Number of gang / module	BLANC RELIEF RELIEFED WHITE		NOIR METEORE METEOR BLACK	
	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP0601	CP0621	CP0701	CP0721
2 postes / 2 gang	CP0602	CP0622	CP0702	CP0722
3 postes / 3 gang	CP0603	CP0623	CP0703	CP0723
4 postes / 4 gang	CP0604	CP0624	CP0704	CP0724
2 postes - 4/5 modules	CP0608		CP0708	

Plaques / Cover Plate - Entraxe 57mm - GRAPHIQUE

Nbr de postes / modules Number of gang / module	BLANC RELIEF RELIEFED WHITE		NOIR METEORE METEOR BLACK	
	PRO		PRO	
2 postes / 2 gang	CP0606		CP0706	
3 postes / 3 gang	CP0607		CP0707	

Plaques / Cover Plate - Entraxe 71mm - ANODISEE

Nbr de postes / modules Number of gang / module	LAITON SATINE SATIN BRASS		BRONZE SATINE SATIN BRONZE		ALUMINIUM SATINE SATIN ALUMINIUM		ACIER SATINE SATIN STEEL	
	PRO	DIY	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP1201	CP1221	CP1601	CP1621	CP1701	CP1721	CP1801	CP1821
2 postes / 2 gang	CP1202	CP1222	CP1602	CP1622	CP1702	CP1722	CP1802	CP1822
3 postes / 3 gang	CP1203	CP1223	CP1603	CP1623	CP1703	CP1723	CP1803	CP1823
4 postes / 4 gang	CP1204	CP1224	CP1604	CP1624	CP1704	CP1724	CP1804	CP1824
2 postes - 4/5 modules	CP1208		CP1608		CP1708		CP1808	
2x2 postes / 2x2 gang							CP1809	
2x3 postes / 2x3 gang							CP1810	

Plaques / Cover Plate - Entraxe 57mm - ANODISEE

Nbr de postes / modules Number of gang / module	LAITON SATINE SATIN BRASS		BRONZE SATINE SATIN BRONZE		ALUMINIUM SATINE SATIN ALUMINIUM		ACIER SATINE SATIN STEEL	
	PRO		PRO		PRO		PRO	
2 postes / 2 gang	CP1206		CP1606		CP1706		CP1806	
3 postes / 3 gang	CP1207		CP1607		CP1707		CP1807	



Plaques / Cover Plate - Entraxe 71mm - RETROS

Nbr de postes / modules Number of gang /module	LIEGE CORK		HETRE BEECH		FEUTRE FELT	
	PRO	DIY	PRO	DIY	PRO	DIY
1 poste / 1 gang	CP1301	CP1321	CP1401	CP1421	CP1501	CP1521
2 postes / 2 gang	CP1302	CP1322	CP1402	CP1422	CP1502	CP1522
3 postes / 3 gang	CP1303	CP1323	CP1403	CP1423	CP1503	CP1523
4 postes / 4 gang	CP1304	CP1324	CP1404	CP1424	CP1504	CP1524
2 postes - 4/5 modules	CP1308		CP1408		CP1508	

Plaques / Cover Plate - Entraxe 71mm - VERRE - METAL

Nbr de postes / modules Number of gang /module	VERRE ONYX NOIR ONYX BLACK GLASS	VERRE OPALE BLANC OPAL WHITE GLASS	NICKEL SATINE SATIN NICKEL	NICKEL SOMBRE SATINE SATIN DARK NICKEL
	PRO	PRO	PRO	PRO
1 poste / 1 gang	CP1901	CP2001	CP2101	CP2201
2 postes / 2 gang	CP1902	CP2002	CP2102	CP2202
3 postes / 3 gang	CP1903	CP2003	CP2103	CP2203
4 postes / 4 gang	CP1904	CP2004	CP2104	CP2204
2 postes - 4/5 modules	CP1908	CP2008	CP2108	CP2208

Plaques / Cover Plate - Entraxe 71mm - BOIS - PORCELAINE

Nbr de postes / modules Number of gang /module	CHENE OAK	FRENE WENGE ASH WENGE	PORCELAINE PORCELAIN
	PRO	PRO	PRO
1 poste / 1 gang	CP2401	CP2501	CP2301
2 postes / 2 gang	CP2402	CP2502	CP2302
3 postes / 3 gang	CP2403	CP2503	CP2303
4 postes / 4 gang	CP2404	CP2504	
2 postes - 4/5 modules	CP2408	CP2508	

Cadre Saillie / Box for surface mounting

1 poste 2 modules	2 postes 4 modules	3 postes 6 modules	Couleur / Color	PRO / DIY
CB0231	CB0232	CB0233	Blanc / White	PRO
CN0231	CN0232	CN0233	Noir /Black	PRO
CX0231	CX0232		Blanc / White	DIY
CZ0231			Noir /Black	DIY

Plaques / Cover Plate - Entraxe 71mm- ANTIMICROBIEN

Nbr de postes / modules Number of gang / module	ANTIMICROBIAN WHITE ENAMELLED WHITE
	PRO
1 poste / 1 gang	CP2601
2 postes / 2 gang	CP2602
3 postes / 3 gang	CP2603

Plaques / Cover Plate - Entraxe 71mm - IP44

Nbr de postes / modules Number of gang / module	BLANC WHITE	IVOIRE IVORY
	PRO	PRO
1 poste / 1 gang	CP2701	CP2801
2 postes / 2 gang	CP2702	CP2802