
























# Goulottes en acier GW0 6

tableau de choix

| Tableau capacité<br>www.ecataleg.be    |                  | Section en mm   | 110 x 63  |          | 130 x 63  |          | 170 x 63  |          | 170A x 63   |  |
|--|------------------|---|---|----------|---|----------|---|----------|---|--|
|  |                  |   |  |          |  |          |  |          |  |  |
|  |                  | Couleur   | RAL 1013  | RAL 9010 | RAL 1013  | RAL 9010 | RAL 1013  | RAL 9010 | RAL 1013  | RAL 9010                                       |
| Goulotte                               | Longueur 2000 mm |    | VG351113  | VG351213 | VG351115  | VG351215 | VG351116  | VG351216 | VG351117  | VG351217                                       |
|  | Longueur 3000 mm |   | VG351133  | VG351233 | VG351135  | VG351235 | VG351136  | VG351236 | VG351137  | VG351237                                       |
| Couvercle                              | Longueur 1000 mm |    | VG351110  | VG351210 | VG351110  | VG351210 | VG351110  | VG351210 | VG351110  | VG351210                                       |
|  | Longueur 1500 mm |   | VG351130  | VG351230 | VG351130  | VG351230 | VG351130  | VG351230 | VG351130  | VG351230                                       |
| Couvercle intermédiaire                | Longueur 100 mm  |    | VG351120  | VG351220 | VG351120  | VG351220 | VG351120  | VG351220 | VG351120  | VG351220                                       |
| Jeu de raccords <sup>(1)</sup>         |                  |    | VG351523  | VG351523 | VG351525  | VG351525 | VG351526  | VG351526 | VG351527  | VG351527                                       |
| Angle intérieur / extérieur 90° +/- 5° | Emboîtable       |    | VG351163  | VG351173 | VG351165  | VG351175 | VG351166  | VG351176 | VG351167  | VG351177                                       |
| Angle intérieur 135-180°               |                  |   | VG351193  | VG351203 | VG351195  | VG351205 | VG351196  | VG351206 | VG351197  | VG351207                                       |
| Angle intérieur                        | Raccord          |  | VG351263  | VG351273 | VG351265  | VG351275 | VG351266  | VG351276 | VG351267  | VG351277                                       |
| Angle extérieur                        |                  |  | VG351293  | VG351303 | VG351295  | VG351305 | VG351296  | VG351306 | VG351297  | VG351307                                       |
| Couvercle pour angle extérieur         |                  |  | VG351140  | VG351240 | VG351140  | VG351240 | VG351140  | VG351240 | VG351140  | VG351240                                       |
| Angle plat                             | Raccord          |  | VG351323  | VG351333 | VG351325  | VG351335 | VG351326  | VG351336 | -   | -  |
| Couvercle pour angle plat              |                  |  | VG351160  | VG351260 | VG351160  | VG351260 | VG351160  | VG351260 | -   | -  |
| Angle plat montant                     | Raccord          |  | -   | -        | -   | -        | -   | -        | VG351327  | VG351337                                       |
| Couvercle pour angle plat montant      |                  |  | -   | -        | -   | -        | -   | -        | VG351160  | VG351260                                       |
| Angle descendant                       | Raccord          |  | -   | -        | -   | -        | -   | -        | VG351357  | VG351367                                       |
| Couvercle pour angle plat descendant   |                  |  | -   | -        | -   | -        | -   | -        | VG351160  | VG351260                                       |
| Dérivation en T                        | Raccord          |  | VG351383  | VG351393 | VG351385  | VG351395 | VG351386  | VG351396 | -   | -  |
| T-montant                              |                  |  | -   | -        | -   | -        | -   | -        | VG351387  | VG351397                                       |
| T-descendant                           |                  |  | -   | -        | -   | -        | -   | -        | VG351417  | VG351427                                       |
| Pièce de finition en T                 |                  |  | VG351553  | VG351563 | VG351555  | VG351565 | VG351556  | VG351566 | VG351557 <sup>2</sup><br>VG351587 <sup>3</sup>                                      | VG351567 <sup>2</sup><br>VG351597 <sup>3</sup> |

<sup>1</sup> Sans peinture : ces pièces ne sont pas visibles - <sup>2</sup> Comme goulotte verticale, utiliser goulotte dev170 mm - <sup>3</sup> Comme goulotte verticale, utiliser goulotte de 130 mm.