

| Section en mm | | | 110 x 63 | | 130 x 63 | | 170 x 63 | | 170A x 63 | | |
|---|--|--------------------|----------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|------------------------|
| | | | | | | | | | | | |
| Couleur | | | RAL 1013 | RAL 9010 | RAL 1013 | RAL 9010 | RAL 1013 | RAL 9010 | RAL 1013 | RAL 9010 | |
| Embout | | | VG351023 | VG351043 | VG351025 | VG351045 | VG351026 | VG351046 | VG351026 | VG351046 | |
| Couvre-joint | 25 mm | | VG351093 | VG351103 | VG351095 | VG351105 | VG351096 | VG351106 | VG351097 | VG351107 | |
| Couvre-joint | 40 mm | | VG351063 | VG351073 | VG351065 | VG351075 | VG351066 | VG351076 | VG351067 | VG351077 | |
| Pièce de finition latérale | | | VG351473 | VG351483 | VG351475 | VG351485 | VG351476 | VG351486 | VG351476 | VG351486 | |
| Pièce obturatrice | | | VG351503 | VG351513 | VG351505 | VG351515 | VG351506 | VG351516 | VG351506 | VG351516 | |
| Pièce de finition terminale | | | VG351443 | VG351453 | VG351445 | VG351455 | VG351446 | VG351456 | VG351446 | VG351456 | |
| ⁽¹⁾Corps gaine verticale | | | VG351409 | VG351409 | VG351409 | VG351409 | VG351409 | VG351409 | VG351409 | VG351409 | |
| Couvercle gaine verticale | | | VG351429 | VG351429 | VG351429 | VG351429 | VG351429 | VG351429 | VG351429 | VG351429 | |
| Snapper GWO 6 | | | VG351319 | VG351319 | VG351319 | VG351319 | VG351319 | VG351319 | VG351319 | VG351319 | |
| Cloison de séparation <small>(utiliser avec 2 x VG351319)</small> | Longueur 1000 mm | | VG351189 | VG351189 | VG351189 | VG351189 | VG351189 | VG351189 | VG351189 | VG351189 | |
| Isolant acoustique <small>(synthétique)</small> | | | VG351389 | VG351389 | VG351389 | VG351389 | VG351399 | VG351399 | VG351399 | VG351399 | |
| Gabarit pour découpe | | | VG351533 | VG351533 | VG351535 | VG351535 | VG351536 | VG351536 | VG351536 | VG351536 | |
| Pinceau retouche | | | VG351019 | VG351029 | VG351019 | VG351029 | VG351019 | VG351029 | VG351019 | VG351029 | |
| Accessoires autre appareillage | Boîte d'installation | simple | | VG351329 | VG351329 | VG351329 | VG351329 | VG351329 | VG351329 | VG351329 | |
| | | double | | VG351339 | VG351339 | VG351339 | VG351339 | VG351339 | VG351339 | VG351339 | |
| | Support enclipsable | 2/3 modules | | VG351069 | VG351069 | VG351069 | VG351069 | VG351069 | VG351069 | VG351069 | |
| | | 4/6 modules | | VG351109 | VG351109 | VG351109 | VG351109 | VG351109 | VG351109 | VG351109 | |
| Accessoires appareillage Mosaïc | Plaque de finition pour support | 2 modules | | - | VG351049 | - | VG351049 | - | VG351049 | - | VG351049 |
| | | 3 modules | | - | VG351059 | - | VG351059 | - | VG351059 | - | VG351059 |
| | | 4 modules | | - | VG351089 | - | VG351089 | - | VG351089 | - | VG351089 |
| | | 6 modules | | - | VG351099 | - | VG351099 | - | VG351099 | - | VG351099 |
| | Prises de courant 230 V⁽¹⁾ | 2x2P+A (4 modules) | | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ | 077142L ⁽¹⁾ |
| | | 3x2P+A (6 modules) | | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ | 077143L ⁽¹⁾ |

(1) Les prises de courant ont une teinte comparable au blanc RAL9003