







	1F+N	3F+N	3F+N	1F+N/3F+N	2x 3F+N	2x 3F+N	3F+N
	252	254	404	256	258	408	634

MATÉRIEL DE FIXATION

Collier 60 kg (LB plus – TYPE A)	75003000	75003000	75003000	75003000	75003000	75003000	75003000
Bride 60 kg (LB plus – TYPE B)	75003004	75003004	75003004	75003004	75003004	75003004	75003004
Crochet (pour armatures d'éclairage)	75003001	75003001	75003001	75003001	75003001	75003001	75003001
Œillet	75003002	75003002	75003002	75003002	75003002	75003002	75003002
Fixation pigtail (pour chaîne)	75003005	75003005	75003005	75003005	75003005	75003005	75003005
Bride de fixation pour goulotte de câble	75003006	75003006	75003006	75003006	75003006	75003006	75003006
Câble de fixation en acier avec verrouillage	75003008	75003008	75003008	75003008	75003008	75003008	75003008
Bride avec câble de fixation en acier	75003009	75003009	75003009	75003009	75003009	75003009	75003009
Collier sol	75003007	75003007	75003007	75003007	75003007	75003007	75003007

ACCESSOIRES

Contact mobile 16 A	–	75105000	75105000	75105000	75105000	75105000	75105000
Ensemble codage pour capteur de courant LB plus	–	–	–	75105001	75105001	75105001	75105001
Goulotte en plastique	71000104	71000104	71000104	71000104	71000104	71000104	71000104

		252	254 - 404	256	258 - 408	634
	LB PLUS	2 conducteurs 25 A	4 conducteurs 25-40 A	6 conducteurs 25 A	8 conducteurs 25-40 A	4 conducteurs 63 A
TYPE A						
TYPE B	