

Jeux de barres et accessoires

≤ 3200				≤ 4000			
 339920/21/22/23 (entraxes : 75 mm)		 339929/30 (entraxes : 125 mm)		 339920/21/22/23 (entraxes : 75 mm)		 339929/30 (entraxes : 125 mm)	
Jeu de barres vertical		Jeu de barres horizontal		Jeu de barres vertical		Jeu de barres horizontal	
I (A)		I (A)		I (A)		I (A)	
IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
700	630	430	350	700	630	500	420
1150	1000	650	510	1180	1020	750	630
1600	1380	1000	900	1600	1380	1000	900
-	-	-	-	2020	1720	1120	1000
800	700	500	400	800	700	600	500
1350	1150	770	590	1380	1180	750	630
1900	1600	1100	1000	1900	1600	1100	1000
-	-	-	-	2350	1950	1350	1200
950	850	600	475	950	850	700	600
1500	1300	890	700	1600	1400	1000	850
2200	1900	1250	1100	2200	1900	1250	1100
-	-	-	-	2700	2300	1600	1400
1000	900	630	500	1000	900	750	630
1650	1450	940	740	1700	1480	1050	900
2350	2000	1300	1150	2350	2000	1300	1150
-	-	-	-	2850	2400	1650	1450
1250	1050	750	580	1250	1050	850	700
1900	1600	1120	900	2050	1800	1200	1050
2900	2450	1600	1400	2900	2450	1600	1400
-	-	-	-	3500	2900	1900	1650
1450	1270	1000	800	1450	1270	1000	800
2500	2150	1450	1250	2500	2150	1450	1250
3450	2900	1800	1600	3450	2900	1800	1600
-	-	-	-	4150	3450	2150	1950
950	850	880	650	950	850	880	650
1680	1470	1250	1050	1680	1470	1250	1050
-	-	-	-	2300	2030	2000	1600
1150	1020	1000	800	1150	1020	1000	800
2030	1750	1600	1250	2030	1750	1600	1250
-	-	-	-	2800	2400	2250	1850
1460	1270	1150	950	1460	1270	1150	950
2500	2150	1700	1500	2500	2150	1700	1500
-	-	-	-	3450	2900	2500	2000
1750	1500	1350	1150	1750	1500	1350	1150
3050	2550	2000	1650	3050	2550	2000	1650
-	-	-	-	4150	3500	2900	2400
2000	1750	1650	1450	2000	1750	1650	1450
3600	3000	2500	2000	3600	3000	2500	2000
-	-	-	-	4800	4000	3500	3000

≤ 1600 / 3200							
 339920/21/22/23 (entraxes : 75 mm)				 339925/26/27 (entraxes : 125 mm)			
Jeu de barres vertical		Jeu de barres horizontal		Jeu de barres vertical		Jeu de barres horizontal	
I (A)		I (A)		I (A)		I (A)	
IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30	IP ≤ 30	IP > 30
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
-	-	-	-	-	-	-	-
800	630	630	500	800	630	630	500
1000	800	800	630	1000	800	800	630
1250	1000	1000	800	1250	1000	1000	800
1450	1250	1250	1000	1450	1250	1250	1000
1750	1600	1400	1250	1750	1600	1400	1250
3500 ⁽¹⁾	3200 ⁽¹⁾	2400	2000	3500 ⁽²⁾	3200 ⁽²⁾	2400	2000



404432 + 339902 + 337980 (p. 283)

Réf.	Barres aluminium en C		
	Barres aluminium cuivré étamé en C Compatibilité électrolytique avec le cuivre garantie		
	30 x 14 mm - longueur 1600 mm		
	Section (mm)	I admissible (A)	
		IP ≤ 30	IP > 30
404430	187	320	250
404431	238	500	400
404432	323	700	630
	40 x 30 mm - longueur 1780 mm		
037354	524	800	630
037355	549	1000	800
037356	586	1250	1000
037357	686	1450	1250
037358	824	1750	1600

Réf.	Ecrus marteau pour barres ALU en C		
	Pour barre	Dim.	Longueur (mm)
404493	404430 404431 404432	M8	22
404494	404433	M8	27
404495	404433 404434 404435 404436 404437 404438	M8	40

Réf.	Capuchons isolants pour écrous		
339941	Pack de 50 capuchons M8		
339942	Pack de 50 capuchons M10		
339943	Pack de 50 capuchons M12		

Réf.	Barres cuivre			Rigides, plates, trous taraudés	
	Section (mm)	I admissible (A)		Trous ø mm	Longueur (mm)
		IP ≤ 30	IP > 30		
037388	12 x 2	110	80	M5	990
037389	12 x 4	160	125	M5	990
037433	15 x 4	200	160	M6	990
037434	18 x 4	245	200	M6	990
037438	25 x 4	280	250	M6	990
037418	25 x 5	330	270	M6	1750
037419	32 x 5	450	400	M6	1750
	Rigides, plates, trous lisses				
037440	50 x 5	700	630	10,5 - 6,5	1750
037441	63 x 5	800	700	10,5 - 8,5	1750
037459	75 x 5	950	850	10,5 - 6,5	1750
037443	80 x 5	1000	900	10,5 - 6,5	1750
037446	100 x 5	1250	1050	10,5 - 6,5	1750

Réf.	Accessoires		
037311	Profilé isolant Profilé isolant pour barres cuivre plates 18 x 4, 25 x 4, 25 x 5 et 32 x 5 mm, longueur 1 m Livré avec clips de fixation		
036774	Visserie isolante M6 x 10		
036775	Vis HF avec rondelle contact M6 x 10		
037359	Ecrus marteau M10		