







		RACCORDS		ÉCROUS	Raccords associés
		Métal 2000	Métal 2000		Conduit GE-PVC + raccord Universale
					
		Mâles droits	Mâles coudés 90°	Métal	
		Agrées UL et CSA ⁽¹⁾ Agrées IMQ ⁽²⁾ - Agrées RINA ⁽⁴⁾			
Filetage	Réf.	Réf.	Réf.		
ISO 16	382041	382341	386631		
ISO 16	382042	382342	386631		
ISO 20	382043	382343	386632		
ISO 20	382044	382344	386632		
ISO 25	382045	382345	386633		
ISO 25	382037	-	386633		
ISO 32	382046	382346	386634		
ISO 40	382047	382347	386635		
ISO 50	382048	382348	386636		
ISO 63	382049	382349	386637		
Conduit FP 2000 + raccord Universale + raccord Métal 2000					
					 
Conduits FA ou PN ou P3 + raccord Métal 2000					
PG 9	382022	382322	386622		
PG 11	382023	382323	386623		
PG 11	382025	382324	386623		
PG 13,5	382028	382326	386624		
PG 16	382029	382327	386625		
PG 21	382030	382328	386626		
PG 29	382031	382329	386627		
PG 36	382032	382330	386628		
PG 42	382033	382331	386629		
PG 48	382034	382332	386630		