

Tableau de choix de chemins de câbles P31+ hauteur 25 mm



RACCORDS							
Coudes 90°	Couvercles pour coudes 90°	Pièces en T	Couvercles pour pièces en T	Dérivations	Couvercles pour dérivations	Largeur en mm	
						75	
VG480907	VG480862	VG481096	VG480880	VG480108	VG480502	75	
VG480908	VG480863	VG481097	VG480881	VG480109	VG480503	100	
VG480909	VG480864	VG481098	VG480882	VG480118	VG480504	150	
VG480910	VG480865	VG481099	VG480883	VG480119	VG480505	200	
VG480911	VG480866	VG481110	VG480884	VG480126	VG480728	300	
VG481188	VG480867	VG483252	VG480885	VG480127	VG480745	400	
VG481189	VG480868	VG483253	VG480886	VG480128	VG480746	500	
VG482907	VG482862	VG482096	VG482880	VG482108	VG482502	75	
VG482908	VG482863	VG483097	VG482881	VG482109	VG482503	100	
VG482909	VG482864	VG483098	VG482882	VG482118	VG482504	150	
VG482910	VG482865	VG483099	VG482883	VG482119	VG482505	200	
VG482911	VG482866	VG483100	VG482884	VG482126	VG482728	300	
VG483188	VG482867	VG483452	VG482885	VG482127	VG482745	400	
VG483189	VG482868	VG483453	VG482886	VG482128	VG482746	500	
≤ 300 mm 4 x M6 x 10 mm ≥ 400 mm 6 x M6 x 10 mm		≤ 300 mm 6 x M6 x 10 mm ≥ 400 mm 9 x M6 x 10 mm		≤ 300 mm 5 x M6 x 10 mm ≥ 400 mm 8 x M6 x 10 mm		Matériel de fixation	

RACCORDS						
Raccords de montée	Couvercles pour raccords de montée	Raccords de descente	Couvercles pour raccords de descente	Embouts	Largeur en mm	
					75	
VG480972	VG480889	VG481031	VG480799	VG481518	75	
VG480973	VG480890	VG481032	VG480808	VG481519	100	
VG480974	VG480891	VG481033	VG480809	VG481520	150	
VG480975	VG480892	VG481034	VG480818	VG481521	200	
VG480976	VG480893	VG481035	VG480819	VG481522	300	
VG483977	VG480896	VG483036	VG480827	VG481523	400	
VG483978	VG480897	VG483037	VG480828	VG481524	500	
VG482972	VG482889	VG482031	VG482799	VG483518	75	
VG482973	VG482890	VG482032	VG482808	VG483519	100	
VG482974	VG482891	VG482033	VG482809	VG483520	150	
VG482975	VG482892	VG482034	VG482818	VG483521	200	
VG482976	VG482893	VG482035	VG482819	VG483522	300	
VG483984	VG482896	VG483336	VG482827	VG483523	400	
VG483985	VG482897	VG483337	VG482828	VG483524	500	
≤ 300 mm 4 x M6 x 10 mm ≥ 400 mm 6 x M6 x 10 mm		≤ 300 mm 4 x M6 x 10 mm ≥ 400 mm 6 x M6 x 10 mm		2 x M6 x 10 mm	Matériel de fixation	