

# Tableau de choix de chemins de câbles P31+ hauteur 100 mm



CHEMINS DE CÂBLES EN TÔLE PERFORÉE						
Largeur en mm	Chemins de câbles emboîtables		Chemins de câbles lourds		Chemins de câbles extra lourds	
	P31+ MF		P31+ ZW		P31+ EZW	
	L = 3 m		L = 3 m		L = 3 m	L = 6 m
100		VG480068	-	-	-	-
150		VG480069	-	-	-	-
200		VG481070	VG487411	VG487443	VG487890	
300		VG481071	VG487412	VG487445	VG487891	
400		VG480072	VG487413	VG487446	VG487892	
500		VG480073	VG487414	VG487447	-	
600		VG480107	VG487415	VG487448	-	
100		VG482068	-	-	-	-
150		VG482069	-	-	-	-
200		VG482170	VG487427	-	-	
300		VG482171	VG487428	-	-	
400		VG482072	VG487429	-	-	
500		VG482073	VG487430	-	-	
600		VG482106	VG487431	-	-	
Matériel de fixation avec chemins de câbles	≤ 300 mm 4 x  M6 x 10 mm		2 x éclisse EXTC (externe)  ou 2 x éclisse EP (interne)			
	≥ 400 mm 5 x  M6 x 10 mm					

RACCORDS						
Largeur en mm	Coudes 90°	Couvercles pour coudes 90°	Pièces en T	Couvercles pour pièces en T	Dérivations	
	100		VG480930	VG480863	VG481800	VG480881
150		VG480931	VG480864	VG481801	VG480882	VG480531
200		VG480932	VG480865	VG481802	VG480883	VG480532
300		VG480933	VG480866	VG481803	VG480884	VG480533
400		VG483319	VG480867	VG481470	VG480885	VG480534
500		VG483320	VG480868	VG481471	VG480886	VG480535
600		VG483321	VG480869	VG481472	VG480887	VG480536
100		VG482930	VG482863	VG482280	VG482881	VG482439
150		VG482931	VG482864	VG482281	VG482882	VG482441
200		VG482932	VG482865	VG482282	VG482883	VG482445
300		VG482933	VG482866	VG482283	VG482884	VG482446
400		VG483206	VG482867	VG483470	VG482885	VG482498
500		VG483207	VG482868	VG483471	VG482886	VG482499
600		VG483208	VG483314	VG483472	VG483377	VG482500
Matériel de fixation avec chemins de câbles	≤ 300 mm 8 x  M6 x 10 mm			≤ 300 mm 12 x  M6 x 10 mm		
	≥ 400 mm 10 x  M6 x 10 mm			≥ 400 mm 15 x  M6 x 10 mm		

(1) **Matériel de fixation**  
8200102 CM350401 Vis M6 + écrou à collet M6



(1) Zinc/Nickel : matière équivalente à la galvanisation à chaud