

Tableau de choix de chemins de câbles P31+ hauteur 100 mm (suite)



CHEMINS DE CÂBLES EN TÔLE AVEUGLE		COUVERCLES	Largeur en mm
Chemins de câbles emboîtables			
P31+ MF			
L = 3 m		L = 2 m	
VG480030		VG341291	100
VG480031		VG341292	150
VG480032		VG341293	200
VG480033		VG341294	300
VG480092		VG341295	400
VG480093		VG341296	500
VG480106		VG341297	600
VG482088		VG343291	100
VG482089		VG343292	150
VG482090		VG343293	200
VG482091		VG343294	300
VG482092		VG343295	400
VG482093		VG343296	500
VG482107		VG343297	600
≤ 300 mm 4 x M6 x 10 mm			Matériel de fixation avec chemins de câbles
≥ 400 mm 5 x M6 x 10 mm		Clip pour couvercle VG481709	

RACCORDS							Largeur en mm
Couvercles pour dérivations	Raccords de montée	Couvercles pour raccords de montée	Raccords de descente	Couvercles pour raccords de descente	Embouts		
VG480503	VG481995	VG480890	VG481054	VG480808	VG481659	100	
VG480504	VG481996	VG480891	VG481055	VG480809	VG481660	150	
VG480505	VG481997	VG480892	VG481056	VG480818	VG481661	200	
VG480728	VG481998	VG480893	VG481057	VG480819	VG481662	300	
VG480745	VG483181	VG480896	VG483504	VG480827	VG481663	400	
VG480746	VG483182	VG480897	VG483505	VG480828	VG481664	500	
VG480747	VG483183	VG480898	VG483506	VG480829	VG480737	600	
VG482503	VG482995	VG482890	VG482010	VG482808	VG483659	100	
VG482504	VG482996	VG482891	VG482011	VG482809	VG483660	150	
VG482505	VG482997	VG482892	VG482012	VG482818	VG483661	200	
VG482728	VG482998	VG482893	VG482013	VG482819	VG483662	300	
VG482745	VG483411	VG482896	VG483326	VG482827	VG483663	400	
VG482746	VG483412	VG482897	VG483327	VG482828	VG483664	500	
VG482747	VG483413	VG482898	VG483328	VG483829	VG482737	600	
	≤ 300 mm 8 x M6 x 10 mm		≤ 300 mm 8 x M6 x 10 mm		4 x M6 x 10 mm	Matériel de fixation avec chemins de câbles	
	≥ 400 mm 10 x M6 x 10 mm		≥ 400 mm 10 x M6 x 10 mm				

Éclisses traditionnel (p. 824)

Cloisons de séparation (p. 825)