

Tableau de choix Cablofil Inox 304L/Inox 316L

POSE MURALE											
Type	Largeur	Chemin de câbles		Etrier de montage UC 50	Console CAT 40	Console CM 50	Console CM 50XL	Console CSN auto	Console CB	Console 41	Etrier de plafond CSNC
CF 54	50 mm	CM000068	304L	CM586048	CM586194	CM586068	CM586138				
		CM000064	316L	CM586044	CM586194	CM586064	CM586134				
	100 mm	CM000078	304L					CM556108	VG350814		CM556304
		CM000074	316L					CM556104	VG350814		CM556304
	150 mm	CM000088	304L					CM556118	VG350824	CM595014	CM556314
		CM000084	316L					CM556114	VG350824	CM595014	CM556314
	200 mm	CM000098	304L					CM556128	VG350834	CM595024	CM556324
		CM000094	316L					CM556124	VG350834	CM595024	CM556324
	300 mm	CM000108	304L					CM556138	VG350844	CM595034	CM556334
		CM000104	316L					CM556134	VG350844	CM595034	CM556334
	400 mm	CM000208	304L						VG350854	CM595044	
		CM000204	316L						VG350854	CM595044	
	500 mm	CM000308	304L						VG350864	CM595054	
		CM000304	316L						VG350864	CM595054	
	600 mm	CM000408	304L						VG350874	CM595064	
		CM000404	316L						VG350874	CM595064	
CF 30	50 mm	CM000018	304L	CM586048	CM586194						
		CM000014	316L	CM586044	CM586194						
	100 mm	CM000028	304L					CM556108	VG350814		CM556304
		CM000024	316L					CM556104	VG350814		CM556304
	150 mm	CM000038	304L					CM556118	VG350824	CM595014	CM556314
		CM000034	316L					CM556114	VG350824	CM595014	CM556314
	200 mm	CM000048	304L					CM556128	VG350834	CM595024	CM556324
		CM000044	316L					CM556124	VG350834	CM595024	CM556324
	300 mm	CM000058	304L					CM556138	VG350844	CM595034	CM556334
		CM000054	316L					CM556134	VG350844	CM595034	CM556334
CF 105	100 mm	CM000898	304L						VG350814		CM556304
		CM000894	316L						VG350814		CM556304
	150 mm	CM000908	304L						VG350824	CM595014	CM556314
		CM000904	316L						VG350824	CM595014	CM556314
	200 mm	CM000918	304L						VG350834	CM595024	CM556324
		CM000914	316L						VG350834	CM595024	CM556324
	300 mm	CM000928	304L						VG350844	CM595034	CM556334
		CM000924	316L						VG350844	CM595034	CM556334
	400 mm	CM000938	304L						VG350854	CM595044	
		CM000934	316L						VG350854	CM595044	
	500 mm	CM000948	304L						VG350864	CM595054	
		CM000944	316L						VG350864	CM595054	
	600 mm	CM001038	304L						VG350874	CM595064	
		CM001034	316L						VG350874	CM595064	