

POSE AU SOL										
Type	Largeur	Chemin de câbles		Etrier de montage UC 50	Console CM 50XL	Clame de fixation FTX	Rehausse R15	Rehausse R50	Rail RCSN	
CF 54	50 mm	CM000068	304L	CM586048		CM586184				
		CM000064	316L	CM586044		CM586184				
	100 mm	CM000078	304L		CM586138	CM586184	CM586174	CM348531	CM013154	
		CM000074	316L		CM586134	CM586184	CM586174	CM348531	CM013154	
	150 mm	CM000088	304L		CM586138	CM586184	CM586174	CM348531	CM013154	
		CM000084	316L		CM586134	CM586184	CM586174	CM348531	CM013154	
	200 mm	CM000098	304L		CM586138	CM586184	CM586174	CM348531	CM013204	
		CM000094	316L		CM586134	CM586184	CM586174	CM348531	CM013204	
	300 mm	CM000108	304L		CM586138			CM348531	CM013304	
		CM000104	316L		CM586134			CM348531	CM013304	
	400 mm	CM000208	304L					CM348531	CM013404	
		CM000204	316L					CM348531	CM013404	
	500 mm	CM000308	304L					CM348531	CM013504	
		CM000304	316L					CM348531	CM013504	
	600 mm	CM000408	304L					CM348531	CM013604	
		CM000404	316L					CM348531	CM013604	
	CF 30	50 mm	CM000018	304L	CM586048		CM586184			
			CM000014	316L	CM586044		CM586184			
100 mm		CM000028	304L		CM586138	CM586184	CM586174	CM348531	CM013154	
		CM000024	316L		CM586134	CM586184	CM586174	CM348531	CM013154	
150 mm		CM000038	304L		CM586138	CM586184	CM586174	CM348531	CM013154	
		CM000034	316L		CM586134	CM586184	CM586174	CM348531	CM013154	
200 mm		CM000048	304L		CM586138	CM586184	CM586174	CM348531	CM013204	
		CM000044	316L		CM586134	CM586184	CM586174	CM348531	CM013204	
300 mm		CM000058	304L		CM586138			CM348531	CM013304	
		CM000054	316L		CM586134			CM348531	CM013304	
CF 105		100 mm	CM000898	304L		CM586138		CM586174	CM348531	CM013154
			CM000894	316L		CM586134		CM586174	CM348531	CM013154
	150 mm	CM000908	304L		CM586138		CM586174	CM348531	CM013154	
		CM000904	316L		CM586134		CM586174	CM348531	CM013154	
	200 mm	CM000918	304L		CM586138		CM586174	CM348531	CM013204	
		CM000914	316L		CM586134		CM586174	CM348531	CM013204	
	300 mm	CM000928	304L		CM586138			CM348531	CM013304	
		CM000924	316L		CM586134			CM348531	CM013304	
	400 mm	CM000938	304L					CM348531	CM013404	
		CM000934	316L					CM348531	CM013404	
	500 mm	CM000948	304L					CM348531	CM013504	
		CM000944	316L					CM348531	CM013504	
	600 mm	CM001038	304L					CM348531	CM013604	
		CM001034	316L					CM348531	CM013604	