

**Constructions E30 - E90 (suite)**

Profilé R21S <sup>(2)</sup> (41 x 21 x 1,5)	Console CB	Console CRP lourds	Support U55	Support de montage pour tige filetée	Tige filetée M10 Longueur 1000 mm EZ	Etrier plafond	Largeur en mm
-	-	-	-	-	-	-	100 mm
-	-	-	-	-	-	-	200 mm
-	-	-	-	-	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	-	100 mm
-	-	-	-	-	-	-	200 mm
VG348042	-	-	-	-	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	8238700 (optionnel)	100 mm
VG348043	-	-	-	-			150 mm
VG348043	-	-	-	-			200 mm
VG348044	-	-	-	-			300 mm
VG348045	-	-	-	-			400 mm
-	VG350810	-	-	VG350122	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	8238700 (optionnel)	100 mm
-	VG350820	-	-				150 mm
-	VG350830	-	-				200 mm
-	VG350840	-	-				300 mm
-	VG350850	-	-				400 mm
-	VG350810	-	VG348362 - L = 200 mm VG348363 - L = 300 mm VG348364 - L = 400 mm VG348365 - L = 500 mm VG348366 - L = 600 mm VG348367 - L = 700 mm VG348368 - L = 800 mm VG348369 - L = 900 mm VG348360 - L = 1000 mm VG348371 - L = 1100 mm VG348372 - L = 1200 mm	VG350122	8234000 - L = 1 m 8234100 - L = 2 m 8234200 - L = 3 m	-	100 mm
-	VG350820	-	-				150 mm
-	VG350830	-	-				200 mm
-	VG350840	-	-				300 mm
-	VG350850	-	-				400 mm
-	-	CM557213	-	-	-	-	100 mm
-	-	CM557233	-	-	-	-	150 mm
-	-		-	-	-	-	200 mm
4x  M10 <sup>(1)</sup>	2x  M6 x 10 mm <sup>(1)</sup>	-	2x  M6 x 10 mm <sup>(1)</sup>	1x  M6 x 10 mm <sup>(1)</sup> pour tige filetée	-	-	<b>Matériels de fixation</b>
-	Mur :  M8 <sup>(5)</sup>	-	M8 <sup>(5)</sup> Plafond : 2 x M10 <sup>(4)</sup> Console : 1 x M8 <sup>(5)</sup>	-	M10 <sup>(6)</sup>	-	<b>Matériels de montage</b>

Support de montage : à fixer sur le côté du chemin de câbles avec 1 vis à bouchon et 2x écrou M6 x 10 mm

