
























# Wandgoten in staal GW0 6

## keuzetabel

Capaciteitstabel www.ecataleg.be		Doorsnede in mm	110 x 63		130 x 63		170 x 63		170A x 63	
										
		Kleur	RAL 1013	RAL 9010	RAL 1013	RAL 9010	RAL 1013	RAL 9010	RAL 1013	RAL 9010
Wandgoot	Lengte 2000 mm		VG351113	VG351213	VG351115	VG351215	VG351116	VG351216	VG351117	VG351217
	Lengte 3000 mm		VG351133	VG351233	VG351135	VG351235	VG351136	VG351236	VG351137	VG351237
Deksel	Lengte 1000 mm		VG351110	VG351210	VG351110	VG351210	VG351110	VG351210	VG351110	VG351210
	Lengte 1500 mm		VG351130	VG351230	VG351130	VG351230	VG351130	VG351230	VG351130	VG351230
Tussendeksel	Lengte 100 mm		VG351120	VG351220	VG351120	VG351220	VG351120	VG351220	VG351120	VG351220
Koppelset <sup>(1)</sup>			VG351523	VG351523	VG351525	VG351525	VG351526	VG351526	VG351527	VG351527
Binnen-/ buitenhoek 90° +/- 5°	Inschuif		VG351163	VG351173	VG351165	VG351175	VG351166	VG351176	VG351167	VG351177
Binnenhoek 135-180°			VG351193	VG351203	VG351195	VG351205	VG351196	VG351206	VG351197	VG351207
Binnenhoek	Koppelen		VG351263	VG351273	VG351265	VG351275	VG351266	VG351276	VG351267	VG351277
Buitenhoek			VG351293	VG351303	VG351295	VG351305	VG351296	VG351306	VG351297	VG351307
Deksel voor buitenhoek			VG351140	VG351240	VG351140	VG351240	VG351140	VG351240	VG351140	VG351240
Platte hoek	Koppelen		VG351323	VG351333	VG351325	VG351335	VG351326	VG351336	-	-
Deksel voor platte hoek			VG351160	VG351260	VG351160	VG351260	VG351160	VG351260	-	-
Hoekstijgstuk	Koppelen		-	-	-	-	-	-	VG351327	VG351337
Deksel voor hoekstijgstuk			-	-	-	-	-	-	VG351160	VG351260
Hoekzakstuk	Koppelen		-	-	-	-	-	-	VG351357	VG351367
Deksel voor hoekzakstuk			-	-	-	-	-	-	VG351160	VG351260
T-stuk	Koppelen		VG351383	VG351393	VG351385	VG351395	VG351386	VG351396	-	-
T-stijgstuk			-	-	-	-	-	-	VG351387	VG351397
T-zakstuk			-	-	-	-	-	-	VG351417	VG351427
T-afwerkingsstuk			VG351553	VG351563	VG351555	VG351565	VG351556	VG351566	VG351557 <sup>2</sup> VG351587 <sup>3</sup>	VG351567 <sup>2</sup> VG351597 <sup>3</sup>

<sup>1</sup> Ongelakt: deze delen zijn niet zichtbaar - <sup>2</sup> Als stijggoot wandgoot 170 mm gebruiken - <sup>3</sup> Als stijggoot wandgoot 130 mm gebruiken