

Doorsnede in mm			110 x 63		130 x 63		170 x 63		170A x 63		
Kleur			RAL 1013	RAL 9010	RAL 1013	RAL 9010	RAL 1013	RAL 9010	RAL 1013	RAL 9010	
Eindeksel			VG351023	VG351043	VG351025	VG351045	VG351026	VG351046	VG351026	VG351046	
Profielafdichting	25 mm		VG351093	VG351103	VG351095	VG351105	VG351096	VG351106	VG351097	VG351107	
Profielafdichting	40 mm		VG351063	VG351073	VG351065	VG351075	VG351066	VG351076	VG351067	VG351077	
Zijdelings afwerkingsstuk			VG351473	VG351483	VG351475	VG351485	VG351476	VG351486	VG351476	VG351486	
Opvulplaat			VG351503	VG351513	VG351505	VG351515	VG351506	VG351516	VG351506	VG351516	
Eindafwerkingsstuk			VG351443	VG351453	VG351445	VG351455	VG351446	VG351456	VG351446	VG351456	
<sup>(1)</sup> Stijggoot romp			VG351409	VG351409	VG351409	VG351409	VG351409	VG351409	VG351409	VG351409	
Klemdeksel stijggoot			VG351429	VG351429	VG351429	VG351429	VG351429	VG351429	VG351429	VG351429	
Snapper GWO 6			VG351319	VG351319	VG351319	VG351319	VG351319	VG351319	VG351319	VG351319	
Tussenschot <small>(gebruiken met 2 x VG351319)</small>	Lengte 1000 mm		VG351189	VG351189	VG351189	VG351189	VG351189	VG351189	VG351189	VG351189	
Akoestisch isolatiestuk <small>(kunststof)</small>			VG351389	VG351389	VG351389	VG351389	VG351399	VG351399	VG351399	VG351399	
Zaagmal			VG351533	VG351533	VG351535	VG351535	VG351536	VG351536	VG351536	VG351536	
Reparatielak			VG351019	VG351029	VG351019	VG351029	VG351019	VG351029	VG351019	VG351029	
Benodigheden universeel scakelmateriaal	Installatiedoos	1-voudig		VG351329	VG351329	VG351329	VG351329	VG351329	VG351329	VG351329	
		2-voudig		VG351339	VG351339	VG351339	VG351339	VG351339	VG351339	VG351339	
	Opklbare houder	2/3 modules		VG351069	VG351069	VG351069	VG351069	VG351069	VG351069	VG351069	
		4/6 modules		VG351109	VG351109	VG351109	VG351109	VG351109	VG351109	VG351109	
Benodigheden Mosaic scakelmateriaal	Afdekkader voor houder	2 modules		-	VG351049	-	VG351049	-	VG351049	-	VG351049
		3 modules		-	VG351059	-	VG351059	-	VG351059	-	VG351059
		4 modules		-	VG351089	-	VG351089	-	VG351089	-	VG351089
		6 modules		-	VG351099	-	VG351099	-	VG351099	-	VG351099
Contactdozen 230 V <sup>(1)</sup>	2x2P+A (4 modules)		077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	077142L <sup>(1)</sup>	
	3x2P+A (6 modules)		077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	077143L <sup>(1)</sup>	

(1) Contactdozen zijn vergelijkbaar met RAL9003 wit