



MPX³ 32MA

MPX³ 63H

MPX³ 100H

2
Enkel magnetisch
Hoog
Draaibediening
3

3
Magneto-thermisch
Hoog
Draaibediening
3

4
Magneto-thermisch
Hoog
Draaibediening
3

Tot 690 V

Tot 690 V

Tot 690 V

50/60 Hz

50/60 Hz

50/60 Hz

690 V

1 000 V

1 000 V

6 kV

8 kV

8 kV

Cat. A

Cat. A

Cat. A

AC3

AC3

AC3

100 000

50 000

50 000

100 000

25 000

25 000

25

25

25

-20 tot +60 °C

-20 tot +60 °C

-20 tot +60 °C

13 x Ie max.

13 x Ie max.

13 x Ie max.

-

10

10

-

•

•

-

•

•

met foutmeldingscontact 417406/07

met foutmeldingscontact 417408/07

met foutmeldingscontact 417408/07

•

•

•

0,360

1

2,2

45 x 94 x 99,6 mm

55 x 140 x 144,6 mm

70 x 165 x 171 mm

		240 V 230 V 220 V	415 V 400 V	460 V 440 V	525 V 500 V	690 V 600 V	240 V 230 V 220 V	415 V 400 V	460 V 440 V	525 V 500 V	690 V 600 V	240 V 230 V 220 V	415 V 400 V	460 V 440 V	525 V 500 V	690 V 600 V	240 V 230 V 220 V	415 V 400 V	460 V 440 V	525 V 500 V	690 V 600 V	240 V 230 V 220 V	415 V 400 V	460 V 440 V	525 V 500 V	690 V 600 V			
		Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics	Icu	Ics		
100	100	100	100	100	100	100	100	100	100	100	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	100	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	100	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	100	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	100	100	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	100	8	8	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	100	8	8	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	100	100	100	100	100	6	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	50	38	50	38	6	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-		
100	100	100	100	50	38	50	38	6	6	100	100	100	100	50	38	50	38	6	5	-	-	-	-	-	-	-	-		
100	100	100	100	50	38	42	32	6	6	100	100	100	100	50	38	42	32	6	5	-	-	-	-	-	-	-	-		
100	100	50	38	20	15	10	8	4	4	100	100	50	50	50	38	12	9	5	5	100	100	100	100	50	38	35	27	12	9
100	100	50	38	20	15	10	8	4	4	100	100	50	50	50	38	12	9	5	5	100	100	100	50	50	38	35	27	12	9
100	100	50	38	20	15	10	8	4	4	100	100	50	50	35	27	12	9	5	5	100	100	100	50	50	38	35	27	12	9
100	100	50	38	20	15	10	8	4	4	100	100	50	50	35	27	10	8	5	5	100	100	100	50	50	38	25	19	12	9
-	-	-	-	-	-	-	-	-	-	100	100	50	50	35	27	10	8	5	5	100	100	100	50	50	38	20	15	12	9
-	-	-	-	-	-	-	-	-	-	100	100	50	50	35	27	10	8	5	5	100	100	100	50	50	38	15	11	10	8
-	-	-	-	-	-	-	-	-	-	100	100	50	50	35	27	10	8	5	5	100	100	100	50	50	38	15	11	8	6
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	100	100	75	50	50	38	12	9	6	6
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	100	100	75	50	50	38	12	9	6	6
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	100	100	75	50	50	38	12	9	6	6