

Keuzetabel

configureer uw LCS³ (vervolg)

| LCS ³ ULTRA LOW LOSS PRETERMINATED HD GLASVEZEL KABELS (blz. 1169) | | | | OM3 | | OS2 | |
|---|--|--------------|--------------|-----------|-----------|--------------------------|-------|
| | | | | 6-6 | 12-12 | 6-6 | 12-12 |
| | Microkabels LC Duplex (Fan-out)-LC Duplex (Fan-out) | 10 m | 032401 | 032411 | 032421 | 032431 | |
| | | 20 m | 032402 | 032412 | 032422 | 032432 | |
| | | 30 m | 032403 | 032413 | 032423 | 032433 | |
| | | 40 m | 032404 | 032414 | 032424 | 032434 | |
| | | 50 m | 032405 | 032415 | 032425 | 032435 | |
| LCS ³ ULTRA LOW LOSS PRETERMINATED HD MTP GLASVEZEL KABELS (blz. 1169) | | | | OM3 | OS2 | OM4 | OM5 |
| | Microkabels MTP(2)-MTP(2) | 12-12 | 12-12 | 12-12 | 12-12 | Beschikbaar op aanvraag* | |
| | | 032441 | 032451 | | | | |
| | | 032442 | 032452 | | | | |
| | | 032443 | 032453 | | | | |
| | | 032444 | 032454 | | | | |
| | | 032445 | 032455 | | | | |
| LCS ³ CORE NORMAL LOSS PRETERMINATED GLASVEZEL KABEL (blz. 1170) | | | | 12 vezels | | 24 vezels | |
| | Glasvezelverbinding OM3 tight buffered | | SC/SC | LC/LC | SC/SC | LC/LC | |
| | | 10 m | 132001 | 132041 | 132021 | 132061 | |
| | | 20 m | 132002 | 132042 | 132022 | 132062 | |
| | | 30 m | 132003 | 132043 | 132023 | 132063 | |
| | | 40 m | 132004 | 132044 | 132024 | 132064 | |
| | | 50 m | 132005 | 132045 | 132025 | 132065 | |
| | | 60 m | 132006 | 132046 | 132026 | 132066 | |
| | | 70 m | 132007 | 132047 | 132027 | 132067 | |
| | | 80 m | 132008 | 132048 | 132028 | 132068 | |
| | | 90 m | 132009 | 132049 | 132029 | 132069 | |
| | | 100 m | 132010 | 132050 | 132030 | 132070 | |
| | | 120 m | 132012 | 132052 | 132032 | 132072 | |
| | | 140 m | 132014 | 132054 | 132034 | 132074 | |
| | | 160 m | 132016 | 132056 | 132036 | 132076 | |
| | | 180 m | 132018 | 132058 | 132038 | 132078 | |
| 200 m | 132020 | 132060 | 132040 | 132080 | | | |
| LCS ³ GLASVEZEL OP HASPEL (blz. 1171) | | | | | | | |
| | Binnen/buiten | 4 vezels | Loose tube | 032502 | 032543 | 032537 | |
| | | 8 vezels | Loose tube | 032503 | 032544 | 032538 | |
| | | 6 vezels | Loose tube | 032512 | - | - | |
| | | | Tight buffer | - | 032665/66 | 032510 | |
| | | 12 vezels | Loose tube | 032514 | 032545 | 032539 | |
| | | | Tight buffer | 032550 | 032667 | 032511 | |
| | 24 vezels | Loose tube | 032551 | - | 032553 | | |
| | | Tight buffer | - | 032668 | 032552 | | |
| | Buiten, versterkt knaagdierbestendig staal, Loose tube | 4 vezels | | 032523 | 032546 | - | |
| | | 8 vezels | | 032524 | 032547 | 032540 | |
| | | 6 vezels | | 032513 | - | - | |
| | | 12 vezels | | 032515 | 032548 | 032541 | |
| 24 vezels | | | 032525 | - | 032542 | | |

1 : Lengte 10 meter, ook verkrijgbaar in lengtes van 20, 30, 40 en 50 m²

2 : MTP is een gedeponerd handelsmerk van US Conec Ltd

* : Contacteer sales.support@legrand.nl