


## Lastscheidingschakelaars keuzetabel

### DX<sup>3</sup>-IS met weergave van de onderbreking 16 tot 125 A (blz. 127)


	In (A)	Met uitschakeling, rode handgreep			Zonder uitschakeling, grijze handgreep						
		2P	3P	4P	1P		2P		3P	4P	
					Zonder lamp	Met lamp	Zonder lamp	Met lamp			
	16				406400		406431				
	20				406401	406404	406432	406436	406457	406477	
	32				406403	406406	406434	406438	406459	406479	
	40	406527	406535	406543	406411		406440		406460	406480	
	63	406528	406536	406544	406412		406441		406461	406481	
	100			406546					406469	406489	
	125			406547					406470	406490	

### VISTOP met zichtbare onderbreking 32 tot 160 A (blz. 128 en 129)

	In (A)	Zwarte handgreep						Rode handgreep/Gele afdekplaat			
		Frontale bediening			Laterale bediening			Frontale bediening		Laterale bediening	
		2P	3P	4P	2P	3P	4P	3P	4P	3P	4P
	32	022498	022500	022502	022503	022505	022507	022300	022302	022305	022307
	63 <sup>(1)</sup>		022512	022515		022516	022518	022312	022315	022316	022318
	100 <sup>(1)</sup>		022520	022522		022525	022527	022320	022322		022327
	125 <sup>(1)</sup>		022534	022539		022544	022546	022334	022339		
	160 <sup>(1)</sup>		022551	022553		022554	022556	022351	022353		


<sup>(1)</sup> Omkeerbare laterale bediening rechts/links

### DPX-IS met zichtbare onderbreking 63 tot 1600 A (blz. 130 tot 132)

	In (A)	Frontale bediening		Laterale bediening rechts		Laterale bediening links	
		3P	4P	3P	4P	3P	4P
			63	026600	026604		
	100	026601	026605				
	160	026602	026606	026612	026616	026622	026626
	250	026603	026607	026613	026617	026623	026627
	400	026660	026662	026664	026666	026668	026670
	630	026661	026663	026665	026667	026669	026671
	800 <sup>(1)</sup>	026591	026595				
	1000 <sup>(1)</sup>	026592	026596				
	1250 <sup>(1)</sup>	026593	026597				
	1600 <sup>(1)</sup>	026594	026598				

<sup>(1)</sup> Mogelijkheid voor uitschakeling op afstand

### DPX<sup>3</sup>-I met weergave van de onderbreking 160 tot 1600 A (blz. 133)

	In (A)	Behuizing	3P	4P	4P differentieel
			160	DPX <sup>3</sup> -I 160	420198
250	DPX <sup>3</sup> -I 250	420299	420300	420298	
125	DPX <sup>3</sup> -I 125 HP	423184	423185	423187	
250	DPX <sup>3</sup> -I 250 HP	423180	423181	423183	
400	DPX <sup>3</sup> -I 630	422216	422218		
630	DPX <sup>3</sup> -I 630	422217	422219		
630	DPX <sup>3</sup> -I 1600	422490	422494		
800	DPX <sup>3</sup> -I 1600	422491	422495		
1250	DPX <sup>3</sup> -I 1600	422492	422496		
1600	DPX <sup>3</sup> -I 1600	422493	422497		

Rood gedrukte referenties: nieuwe producten